

PHILIPS

sonicare

Sonic electric
toothbrush

ProtectiveClean
6100

Built-in pressure sensor

3 modes, 3 intensities

2 x BrushSync features

Travel case



HX6876/21



Whiter teeth. Gently does it.

Whitens teeth in just 1 week.

Feel the difference of a gentle clean with our Pressure Sensor while whitening your teeth in 1 week.

Proven to improve oral health

- Whitens teeth in just 1 week
- Gentle on sensitive areas, orthodontics & dental work

Optimize your brushing

- Choose from 3 modes
- Brush heads select the optimal mode and intensity

Innovative technology

- The Sonicare 6100 tells you when to change brush heads
- Lets you know if you're pressing too hard
- Sonic technology that pulses between teeth
- Connects smart brush handle and smart brush heads

Designed around you

- 2 minute brushing time recommended by dentists
- Makes traveling easier for you

Highlights

Makes teeth brighter



The soft, flexible bristles of the Philips Sonicare ProtectiveClean are designed to curve around the contours of your teeth, giving you 4x more surface contact** and up to 10x more plaque removal from hard-to-reach spots.

Safe brushing experience



A good electric toothbrush for braces. The Sonicare ProtectiveClean 6100 can also be used on fillings, crowns, veneers and other sensitive orthodontics.

Customize your brushing

Three modes. Three intensities. Customize your brushing to your cleaning preferences with the Sonicare ProtectiveClean 6100. Clean mode is standard for superior cleaning. White is the ideal mode for removing surface stains. And Gum Care mode adds an extra minute of reduced-power brushing, so you can gently massage your gums.

BrushSync for the right mode



Switching brush heads for a different style of brushing? No problem. The base of your Sonicare 6100 recognizes the type of head it is connected to and automatically adjusts to the correct intensity mode for the brush.

Prioritizes your oral hygiene

Your brush head and base will sync-up to remind you when it's time to replace the head with a simple short beep and a handle light.

Monitor your brushing pressure



Brushing too hard can damage your teeth and gums. To prevent this, your Philips Sonicare ProtectiveClean emits a gentle pulsing sound to remind you to ease off on the pressure.

Sonicare 6100 — a deeper clean

Sonic technology pulses water between your teeth and gums to break up and remove 3x as much plaque along the gumline than a manual toothbrush.

BrushSync technology



A microchip-enabled technology that detects and synchronizes the smart brush head with the smart handle. The smart handle and smart brush head pair is a powerful combination that enables Smart mode pairing and Smart replacement reminders.

Smart functionalities



With a gentle pulse reminds you to change to a new part of your mouth, and signals when 2 minutes of brushing time is up. This sonic electric toothbrush gives you the most optimal brush, every time.

Handy travel case and charger



Our premium travel case lets you store your toothbrush hygienically, while our compact charging base keeps you topped up when you're on the go. You do get two weeks of regular use from a single full charge, but the charger's just the ticket for longer trips.

Specifications

Modes

Clean: For exceptional everyday clean

Gum Care: Gently massages gums

White: Removes surface stains

3 intensities: Low, Medium, High

Items included

Handle: 1 ProtectiveClean

Brush heads: 1 W DiamondClean

Travel case: 1

Charger: 1

BrushSync Mode Pairing

C2 Optimal Plaque Control: Pairs with Clean mode

G2 Optimal Gum Care: Pairs with Gum Care mode

W DiamondClean: Pairs with White mode

Design and finishing

Color: Pastel pink

Cleaning performance

Speed: Up to 62000 brush movement/min

Health benefits: Improves gum health in only two weeks, Helps reduce cavities

Pressure feedback: Vibrates handle to alert user

Timer: Quadpacer and SmarTimer

Smart sensor technology

Pressure sensor: Alerts when brushing too hard

BrushSync Replacement Reminder: Always know when to, replace brush heads

BrushSync Technology: Connects smart handle and, smart brush head

Ease of use

Handle compatibility: Easy click-on brush heads

Brush head recognition: Syncs with optimal

mode

Replacement reminder: To always ensure best results, reminder icon lights up

Battery indicator: Light shows battery status

Handle: Slim ergonomic design

Brushing time: Up to 2 weeks

Technical specifications

Battery: Rechargeable

Battery type: Lithium ION

Operating time (full to empty): Up to 2 weeks

Power

Voltage: 110-220 V

Service

Warranty: 2-year limited warranty

