

PHILIPS

sonicare

Sonic electric
toothbrush

Elite

HX7351



Better reach for a better clean

The only angled Sonic brush that gives you better reach for a better clean. Sonicare's unique dynamic cleaning action reaches deep between teeth and into hard-to-reach areas, while massaging gums for a brushing experience unlike any other.

Better reach for a better clean

- Patented dynamic cleaning action
- Contoured bristles
- Slim, angled brush neck

Clinically proven benefits

- Naturally whiter teeth
- Clinically proven safe and gentle
- Improves gum health in only two weeks

Additional features

- SmartTimer encourages 2-minute brushing time
- Easy-start to acclimate to the Sonicare experience
- Quadpacer 30-second interval timer encourages even brushing
- Dual Speed Control

Highlights

Patented dynamic cleaning action

Gently and efficiently reaches between teeth and along the gumline.

Contoured bristles



Extra-soft end-rounded bristles are gentle on teeth and gums

Slim, angled brush neck

Helps clean hard to reach areas.

Naturally whiter teeth



Clinically proven to significantly reduce coffee, tea and tobacco stains for naturally whiter teeth.

Safe and gentle



Your Philips Sonicare Electric Toothbrush is safe to use on: braces (brush heads wear out sooner when used on braces), dental restorations (fillings, crowns, veneers) and periodontal pockets.

Improves gum health




This Philips Sonicare electric toothbrush provides optimal cleaning between teeth and along the gumline for improved gum health in just two weeks.

Easy-start


Gently increases power over first 12 uses, to ease into the Sonicare experience

Quadpacer



Quadpacer 30-second interval timer encourages even brushing

Dual Speed Control



Dual Speed Control

Specifications

Additional features

- Contoured brush head
- Smartimer
- Easy-Start
- Quadpacer
- Deluxe recharge gauge
- Ergonomic tapered handle
- Brush heads included: 1

Technical specifications

- Speed: 31,000 movements per minute
- Charging time: 24 hour(s)
- Battery rechargeable: NiCd
- Voltage: 230V, 50Hz (UK 240V, 50Hz)
- Power consumption: 3 W

Accessories

- Brush head holder

Cleaning performance

- Speed: Up to 31000 brush movement/min

