

PHILIPS

sonicare

Sonic electric
toothbrush

FlexCare Platinum

3 modes, 3 intensities

2 brush heads

With pressure sensor



HX9112/16



Deep, gentle cleaning

Removes up to 7x more plaque between teeth*

With nine unique brushing options, an intuitive pressure sensor and advanced brush head technology, Philips Sonicare FlexCare Platinum goes beyond traditional cleaning to deliver exceptional plaque removal and improved gum health.

Offers a customized brushing experience

- Three intensity settings and three cleaning modes
- New Deep Clean: Effortlessly tackle trouble spots

Provides an exceptional clean for teeth and gums

- Removes up to 7x more plaque between teeth
- Designed to reach deeper and go further
- Sonic technology for better oral health

Fits your lifestyle

- Long battery life and travel case
- Handy travel case and charger

Helps you meet recommended brushing guidelines

- Timers to help encourage thorough brushing
- Alerts you when you're brushing too hard



asimpleswitch.com

Highlights

Reaches deep between teeth




FlexCare Platinum reaches deep between teeth to provide superior plaque removal. It is clinically proven to remove 7x more plaque between teeth than a manual toothbrush.

Reach deeper and go further




Philips Sonicare InterCare toothbrush head features extra-long, high-density bristles to target hidden plaque caught deep between teeth and other hard-to-clean areas.

Quadpacer and SmarTimer



FlexCare Platinum offers two timers to help encourage thorough brushing. The Quadpacer interval timer indicates when it's time to move to another quadrant of the mouth, while the SmarTimer helps you reach the dentist recommended brushing time of two minutes.

Customized brushing experience



With three intensity settings and three cleaning modes, FlexCare Platinum offers optimal comfort as you get a truly deep clean. If you need to pay extra attention to trouble spots, the three-minute Deep Clean mode delivers exceptional results. Use Clean mode for a superb everyday clean, or White mode for stain removal. Set the intensity to Low, Medium or High according to your personal preference.

Intuitive pressure sensor



You might not notice if you're brushing too hard, but your FlexCare Platinum toothbrush will. If you apply too much pressure, the intuitive pressure sensor will make the toothbrush handle gently vibrate so you know exactly when to adopt a softer touch. In studies, 7 out of 10 aggressive brushers successfully reduced their brushing pressure thanks to the pressure sensor.

Designed to fit your lifestyle



Our premium travel case lets you store your toothbrush hygienically, while our compact travel charger keeps you topped up when you're on the go. You'll enjoy two weeks of regular use from a single full charge, so being on the move means you needn't miss out on that fresh feeling.

Deep Clean mode



Our all-new Deep Clean mode delivers an exceptional clean in hard-to-reach places. The unique motion of the brush head in this mode plus an extended three-minute brushing time makes it the ideal choice when you want to pay extra attention to trouble spots.

Sonic technology



Unlike a traditional electric or power toothbrush, Philips Sonicare features a patented sonic technology. Sonicare's unique dynamic cleaning action drives fluid between teeth, gently and effectively removing plaque interdentally and along the gum line.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Modes

Clean: For exceptional everyday clean

White: Removes surface stains

Deep Clean: For an invigorating deep clean

3 intensities: Low, Medium, High

Items included

Handles: 1 FlexCare Platinum

Brush heads: 2 InterCare standard

Charger: 1

UV sanitizer: No

Travel case: 1

Design and finishing

Color: Gray with brushed white panel

Cleaning performance

Speed: Up to 62000 brush movement/min

Performance: Removes up to 7x more plaque*

Health benefits: Improves gum health in only two weeks

Whitening benefits: Helps naturally remove stains

Timer: SmarTimer and Quadpacer

Pressure sensor: Vibrates handle to alert user

Ease of use

Brush head system: Easy click-on brush heads

Brushing time: Up to 3 weeks**

Battery indicator: Light shows battery status

Handle: Slim ergonomic design

Display: Illuminated display

Technical specifications

Battery: Rechargeable

Battery type: Lithium ION

Operating time (full to empty): Up to 3 weeks**

Power

Voltage: 110-220 V

Service

Warranty: 2-year limited warranty

