



Philips Sonicare FlexCare
Platinum
Sonic electric toothbrush -
Dispense

3 modes, 3 intensities

1 brush head
With pressure sensor

FlexCare Platinum

HX9181/26



Their techniques may vary, but their results won't

Our first brush with Adaptive Cleaning Technology

At the core of this technology are two components: the AdaptiveClean brush head and an intuitive pressure sensor. Both features help your patients to brush smarter.

Guides you to follow dental recommendations

- Intuitive pressure sensor

Proven to improve oral health

- Quadpacer
- Smarttimer

Provides a superior clean

- AdaptiveClean brush head
- Customizable brushing experiences
- Patented Sonicare toothbrush technology

PHILIPS

sonicare


Highlights

AdaptiveClean brush head



Soft, flexible sides made of rubber allow the bristles to conform to the unique shape of patients' teeth and gums to provide up to 4x more surface contact*. The brush head's flexibility helps the bristles gently track along the gumline and absorb excessive brushing pressure. Enhanced sweeping motion delivers a unique in-mouth feel and superior cleaning along the gumline and in hard-to-reach areas*. Proven to remove 10x more plaque than a manual toothbrush in hard-to-reach areas*.


Custom brushing experiences



Three intensity settings and three cleaning modes provide optimal comfort and performance for a more personalized brushing experience, encouraging better compliance. The


three-minute Deep Clean mode delivers an exceptional clean in hard-to-reach places. It's the perfect mode for patients who need to pay extra attention to trouble spots.

Intuitive pressure sensor



If too much pressure is applied, the handle gently pulsates to tell patients they are brushing too hard to guide proper technique. In a study of U.S. patients, 7 out of 10 aggressive brushers tested reduced their brushing pressure when using the pressure sensor.

Quadpacer



Thirty-second interval timer encourages thorough brushing of each quadrant of the mouth.

Smarttimer



Two-minute timer helps ensure dental professional recommended brushing time.

Sonic technology



Drives fluid between the teeth and along the gumline for a powerful yet gentle clean.

Specifications

Modes

- Clean: For exceptional everyday clean
- White: Removes surface stains
- Deep Clean: For an invigorating deep clean
- 3 intensities: Low, Medium, High

Items included

- Handles: 1 FlexCare Platinum
- Brush heads: 1 InterCare standard
- Charger: 1
- Travel case: 1

Design and finishing

- Color: Platinum gray

Cleaning performance

- Speed: Up to 62000 brush movement/min
- Performance: Removes up to 7x more plaque*
- Health benefits: Improves gum health in only two weeks
- Whitening benefits: Helps naturally remove stains

- Timer: SmarTimer and Quadpacer
- Pressure sensor: Vibrates handle to alert user

Ease of use

- Brush head system: Easy click-on brush heads
- Brushing time: Up to 3 weeks**
- Battery indicator: Light shows battery status
- Handle: Slim ergonomic design
- Display: Illuminated display

Technical specifications

- Battery: Rechargeable
- Operating time (full to empty): Up to 3 weeks**
- Battery type: Lithium ION

Power

- Voltage: 110-220 V

Service

- Warranty: 2-year limited warranty



Issue date 2018-12-02

Version: 8.0.1

EAN: 00 07502 00506 25

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Than a DiamondClean brush head

* Than a manual toothbrush

* Data on file

** based on two periods of two-minute brushings per day