

PHILIPS

sonicare

Sonic electric toothbrush - Dispense

FlexCare Platinum

3 modes, 3 intensities

2 brush heads

With pressure sensor

UV brush head sanitizer



HX9182/32



Their techniques may vary, but their results won't Our first brush with Adaptive Cleaning Technology

At the core of our Adaptive Cleaning Technology are two components - the innovative AdaptiveClean brush head and intuitive pressure sensor. Both features help your patients brush smarter, not harder.

Provides a superior clean

- AdaptiveClean brush head
- Customizable brushing experiences
- Patented Sonicare toothbrush technology

Guides you to follow dental recommendations

- Intuitive pressure sensor

Offers a customized brushing experience

- New Deep Clean: Effortlessly tackle trouble spots

Designed around you

- InterCare brush head

Proven to improve oral health

- UV sanitizer
- Smarttimer
- Quadpacer

Highlights

AdaptiveClean brush head



Soft, flexible sides made of rubber allow the bristles to conform to the unique shape of patients' teeth and gums to provide up to 4x more surface contact*. The brush head's flexibility helps the bristles gently track along the gumline and absorb excessive brushing pressure. Enhanced sweeping motion delivers a unique in-mouth feel and superior cleaning along the gumline and in hard-to-reach areas*. Proven to remove 10x more plaque than a manual toothbrush in hard-to-reach areas*.

Intuitive pressure sensor



If too much pressure is applied, the handle gently pulsates to tell patients they are brushing too hard to guide proper technique. In a study of U.S. patients, 7 out of 10 aggressive brushers tested reduced their brushing pressure when using the pressure sensor.


Deep Clean mode



Our all-new Deep Clean mode delivers an exceptional clean in hard-to-reach places. The unique motion of the brush head in this mode

plus an extended three-minute brushing time makes it the ideal choice when you want to pay extra attention to trouble spots.

Custom brushing experiences



Three intensity settings and three cleaning modes provide optimal comfort and performance for a more personalized brushing experience, encouraging better compliance. The three-minute Deep Clean mode delivers an exceptional clean in hard-to-reach places. It's the perfect mode for patients who need to pay extra attention to trouble spots.

InterCare brush head



Extra-long, high-density bristles reach deeper between teeth to help remove significantly more plaque* interproximally. Ideal for patients with bleeding gums or increased risk of gum inflammation.

UV sanitizer




Kills up to 99% of bacteria and viruses*. Can be available as an accessory in one of the dispensing SKUs.

Smarttimer



Two-minute timer helps ensure dental professional recommended brushing time.

Quadpacer



Thirty-second interval timer encourages thorough brushing of each quadrant of the mouth.

Sonic technology



Drives fluid between the teeth and along the gumline for a powerful yet gentle clean.

Specifications

Modes

Clean: For exceptional everyday clean
White: Removes surface stains
Deep Clean: For an invigorating deep clean
3 intensities: Low, Medium, High

Items included

Handles: 1 FlexCare Platinum
Brush heads: 1 AdaptiveClean, 1 InterCare standard
Charger: 1
Travel case: 1
UV sanitizer: 1

Design and finishing

Color: Platinum gray

Cleaning performance

Speed: Up to 62000 brush movement/min
Performance: Removes up to 10x more plaque*
Health benefits: Improves gum health in only two weeks
Whitening benefits: Helps naturally remove stains
Timer: Quadpacer and SmarTimer
Pressure sensor: Vibrates handle to alert user

Ease of use

Brush head system: Easy click-on brush heads
Brushing time: Up to 3 weeks***

Battery indicator: Light shows battery status

Handle: Slim ergonomic design
Display: Illuminated display

Technical specifications

Battery: Rechargeable
Operating time (full to empty): Up to 3 weeks**
Battery type: Lithium ION

Power

Voltage: 110-220 V

Service

Warranty: 2-year limited warranty



* Than a DiamondClean brush head

* Than a manual toothbrush

* Data on file

* After a single use of each toothbrush vs. Oral-B 3000/6000 CrossAction

* HSVI, H.A.