

PHILIPS

sonicare

Sonic electric
toothbrush - Dispense

FlexCare Platinum

3 modes, 3 intensities

2 brush heads

With pressure sensor

Tongue brush and tongue spray



HX9188/11



Deep, gentle cleaning

10x more plaque removal and healthier gums*

With FlexCare Platinum, even the deepest clean is gentle enough to protect your teeth and gums. Thanks to the AdaptiveClean brush head and intuitive pressure sensor, you get maximum plaque removal and a gentle experience however you brush.

Philips Sonicare's deep clean

- Adaptive cleaning technology for a deep yet gentle clean
- Follows the shape of your teeth and gums for a deeper clean
- Dynamic cleaning action for better oral health

Innovative technology

- Designed specifically for the tongue
- A powerful combination

Offers a customized brushing experience

- Three intensity settings and three cleaning modes
- New Deep Clean: Effortlessly tackle trouble spots

Helps you meet recommended brushing guidelines

- Alerts you when you're brushing to hard

Highlights

A deep clean however you brush



Old habits can be hard to break, except when you're brushing with next generation FlexCare Platinum. Thanks to the innovative AdaptiveClean brush head and intuitive pressure sensor that are at the core of our adaptive cleaning technology, even hard-to-reach trouble spots become easy to care for. The bristles of the AdaptiveClean brush head curve around your teeth and gums for up to 4x more surface contact** and up to 10x more plaque removal. If you're brushing too hard, the pressure sensor makes the toothbrush handle gently pulsate so you can be gentle to your gums while being tough on plaque.

AdaptiveClean brush head




Our AdaptiveClean brush head is the only electric toothbrush head that can follow the unique shape of your teeth and gums. With soft flexible sides made of rubber, this brush head can follow every curve. It offers up to 4x more surface contact and up to 10x more plaque removal along the gum line and between teeth. As the brush tracks along the gum line, it absorbs any excessive brushing pressure you might apply so you can be gentle on gums however you brush.

Intuitive pressure sensor



You might not notice if you're brushing too hard, but your FlexCare Platinum toothbrush will. If you apply too much pressure, the intuitive pressure sensor will make the toothbrush handle gently vibrate so you know exactly when to adopt a softer touch. In studies, 7 out of 10 aggressive brushers successfully reduced their brushing pressure thanks to the pressure sensor.

Customized brushing experience



With three intensity settings and three cleaning modes, FlexCare Platinum offers optimal comfort as you get a truly deep clean. If you need to pay extra attention to trouble spots, the three-minute Deep Clean mode delivers exceptional results. Use Clean mode for a superb everyday clean, or White mode for stain removal. Set the intensity to Low, Medium or High according to your personal preference.


Deep Clean mode



Our all-new Deep Clean mode delivers an exceptional clean in hard-to-reach places. The unique motion of the brush head in this mode

plus an extended three-minute brushing time makes it the ideal choice when you want to pay extra attention to trouble spots.

Design



In healthy patients, up to 80% of oral malodor comes from the tongue. But most patients don't clean it, and those who do typically use a manual toothbrush, which isn't designed to clean the tongue.

Dual-action technology



Philips Sonicare TongueCare+ pairs sonic technology and the antibacterial strength of Philips Sonicare BreathRx Tongue Spray to target the primary cause of oral malodor. Innovative tongue brush with 240 elastomer MicroBristles to clean deep around papillae. 31,000 vibrations per minute help break up tongue coating and sweep away debris and bacteria. Alcohol-free tongue spray with cetylpyridinium chloride (CPC) and Zytex™ to neutralize VSC gasses, in a thick, concentrated formula that lubricates the tongue for a gentle clean.

Specifications

Modes

3 intensities: High, Low, Medium

Clean: For exceptional everyday clean

Deep Clean: For an invigorating deep clean

White: Removes surface stains

Items included

Brush heads: 1 AdaptiveClean, 1 InterCare standard

Charger: 1

Handles: 1 FlexCare Platinum

Travel case: 1

Antibacterial tongue spray: 2oz

Tongue brush: 1

Design and finishing

Color: Platinum gray

Cleaning performance

Health benefits: Improves gum health in only two weeks

Performance: Removes up to 10x more plaque*

Speed: Up to 62000 brush movement/min

Timer: SmartTimer and Quadpacer

Whitening benefits: Helps naturally remove stains

Pressure sensor: Vibrates handle to alert user

Ease of use

Battery indicator: Light shows battery status

Brush head system: Easy click-on brush heads

Brushing time: Up to 3 weeks***

Display: Illuminated display

Handle: Slim ergonomic design

Ingredients

Antibacterial tongue spray: 0.09% CPC, Zytex

Expiration

After opened: 6 months

Shelf life: 36 months

Technical specifications

Battery: Rechargeable

Battery type: Lithium ION

Operating time (full to empty): 3 week battery life

Power

Voltage: 110-220 V

Service

Warranty: 2-year limited warranty

