

# PHILIPS

## sonicare

Sonic electric  
toothbrush

DiamondClean

5 modes

2 brush heads

Glass charger

USB travel charger



HX9332/04

## Whiter, healthier teeth for life

### Best Philips Sonicare whitening sonic toothbrush

Sonicare's best whitening in our most elegant Philips Sonicare electric toothbrush. Switch to Sonicare.

#### Proven to improve oral health

- Up to 7x more plaque removal than a manual toothbrush
- A whiter smile in 1 week with our DiamondClean brush head\*
- Improves gum health in just 2 weeks\*
- Choose from 5 modes including Polish and Sensitive
- Safe and gentle for your oral health needs

#### Provides a superior clean

- Our unique technology brings you a powerful yet gentle clean
- Angled neck to help tackle cleaning in tough areas

#### Designed around you

- USB charging travel case and charging glass
- Timers encourage thorough 2 minutes of brushing
- Easy start program builds your Philips Sonicare routine

# Specifications

## Modes

**Clean:** For exceptional everyday clean

**Gum Care:** Gently massages gums

**Polish:** Brighten and polish your teeth

**Sensitive:** Gentle teeth and gum cleaning

**White:** Removes surface stains

## Items included

**Handle:** 1 DiamondClean

**Brush heads:** 1 DiamondClean compact, 1 DiamondClean standard

**Glass charger:** 1

**Travel case:** USB travel charger

## Design and finishing

**Color:** Ceramic white

## Cleaning performance

**Speed:** Up to 62000 brush movement/min

**Performance:** Removes up to 7x more plaque\*

**Health benefits:** Improves gum health in only two weeks

**Whitening benefits:** Whitens teeth 2X better\*

**Timer:** Quadpacer and SmarTimer

## Ease of use

**Brush head system:** Easy click-on brush heads

**Brushing time:** Up to 3 weeks\*\*

**Battery indicator:** Illuminated icon indicates

battery life

**Handle:** Slim ergonomic design

**Display:** Illuminated display

## Technical specifications

**Battery:** Rechargeable

**Battery type:** Lithium ION

**Operating time (full to empty):** Up to 3 weeks\*\*

## Power

**Voltage:** 100-240 V, 50-60 Hz

## Service

**Warranty:** 2-year limited warranty

