

## 64MB Digital camera with 1.3 mega pixel output

### **Direct USB Plug-in – No software and no cable needed!**

- No software drivers required (except Windows 98)
- Direct battery recharging via USB
- No USB cable necessary. Direct USB connection to PC

### **Ready to Wear, Ready to Go**

- Ultra lightweight and durable magnesium body
- Stylish, small and compact - Weighing just 35g

### **64MB internal flash memory**

- Enjoy capacity for up to 400 pictures
- Store and carry data files up to 44 floppy disks



snap, share  
& wear

**PHILIPS**

# Wearable digital camera (Key Ring)



## Standard product information

### Picture

- Image resolution 307,200 Pixel (capture image: 640 x 480)
- Sensor image size 1/4", CMOS
- Optical Lens Fixed Focus length, F2.8
- Audio No
- Viewfinder 2 element optical view finder
- Image LCD No
- Status LCD No
- Status Indicator LED x 3 (Red, Yellow & Green)
- Digital zoom No
- Strobe No
- External battery pack No
- Storage 64MB internal flash memory
- Removable Memory Card No
- Focus distance 70 cm to infinite
- White Balance Auto
- Exposure range EV7-15
- Image file format JPEG
- Sensitivity ISO equivalent 100
- Image Capacity 800 images based on average file size of 80KB

### Connections

- USB connection USB1.1

### Power supply

- Battery Built-in 550 mAh Li-ion
- Rechargeable time via USB 2.5 hours (in charge mode only)

### Software

- Media management Photo Manager
- General data storage Directly accessible via Windows Explorer (Mass Storage Device Class compliant)

### General

- Encasing Die-cast molded magnesium
- Product dimensions 86 L x 28.6 W x 16-18 H (mm)
- Weight (g) 35
- D-box dimension 168 L x 91 W x 35 H (mm)
- Master carton 198 L x 123 W dimensions D-box (mm) x 194 H
- Master carton quantity 6

### Accessories

- Necklace strap (AY3292)
- CD-ROM with software and full user manual (AY3497)
- Quick-Start-Guide
- Safety & warranty booklet

### PC system requirements

- Processor Pentium MMX 166MHZ or better
- RAM memory 96RAM/ 50MB free hard disk space
- CD ROM drive
- OS Windows 98SE or later (excludes Windows NT)
- Mac G3 or better/ Mac OS 9-X
- Caution Computers that were upgraded from Windows 95, may not have USB compatibility

**Direct USB plug-in for 1.3 Mega Pixel pictures**  
Speedily and easily transfer any digital file on your PC via the direct USB connection.

### 64MB internal flash memory

A 64MB flash memory holds hundreds of photos, which can be viewed, shared and exchanged on any PC.

### Direct battery recharging via USB

Offers ultra convenience when recharging your Key Ring. No need to bother with separate chargers or cables, simply plug n' recharge your Key Ring directly on your PC.

### Durable magnesium body

Made from ultra lightweight and sturdy magnesium for ultimate product protection – No unexpected dents and chips!

**EAN: 87 10895 76771 2**

Printed in Hong Kong 2003-03-20  
Specifications subject to modification without notice  
2003 © Koninklijke Philips Electronics N.V.  
All rights reserved

[www.philips.com](http://www.philips.com)  
[www.audio.philips.com](http://www.audio.philips.com)

