

Multimedia Projector

bSure2
series

Maximum brilliance

- *Ultra high brightness*
- *Super Silent*
- *Remote control with laserpointer*
- *Brilliant picture quality*
- *Ultimate ease of use*



PHILIPS



bSure2 series

technical specifications



* bSure XG2
bSure SV2

* bSure XG2 Brilliance
bSure SV2 Brilliance



For optional* accessories please contact your dealer.

Technical specifications	LC3132 (bSure SV2)	LC3142 (bSure XG2)	LC3136 (bSure SV2-Brilliance)	LC3146 (bSure XG2-Brilliance)
	May'03 onwards			
LCD	3x 0.7" high-temperature poly-silicon active matrix LCDs			
Resolution	SVGA	XGA	SVGA	XGA
Brightness	1500 ANSI lumens	1500 ANSI lumens	2500 ANSI lumens	2200 ANSI lumens
Lamp	132W	150 W	200 W	200 W
Average lifetime	6000 hours	3000 hours	2000 hours	2000 hours
Contrast	300:1	300:1	300:1	300:1
Fan noise	27 dB	29 dB	34 dB	34 dB
Lens	F/1.8 - 2.2 ; f = 28.4 - 34 mm; 1.2x Manual Zoom; Manual Focus 1.2x Manual Zoom; Manual Focus Projection distance 1,1 - 10 m (Image diagonal 27.5" - 250")			
Input signals	NTSC 3.58, 4.43 ; PAL B,G,D,H,I,N,M ; SECAM S-video/S-VHS (Y/C) Component video input RGB-Y/CbCr, YPbPr (480p, 720p, 1080i)			
Computer	PC and MAC compatible, Multi scan VGA-SXGA Horizontal scan rate: 15 - 108 kHz Vertical refresh rate: 50 - 120 Hz Bandwidth: 140 MHz Display Data Channel DDC 1/2B Microsoft® Windows® 95/98/ME/2000/XP compatible			
Plug and play Compatibility	Microsoft® Windows® 95/98/ME/2000/XP compatible			
Input connectors	1 Component in R/Pr/Cr,G/Y,B/Pb/Cb (3x RCA) 2 1x S-Video (Y/C DIN) 3 1x CVBS Video (RCA) 4 1x Data in (15p D-sub) 5 Audio L/R (2x RCA) 6 1x Stereo Audio (3.5 mm stereo jack) 7 PS/2 (Mini Din) 8 USB (type A)			
Computer Audio Video Data Mouse	USB-audio USB-audio			
Features	SecurityMax™ Theft protection SmartSet™ automatic image quality optimisation SmartSave™ auto-standby mode to increase effective lamp usage Colour Tracking™ Digital Keystone correction horizontal +/- 32 degrees Digital Zoom (16x) and -Freeze YourLogo Connect an external monitor via Y-cable on the RGB connector			
Dimensions	235 x 335 x 108 mm (9.2" x 13.2" x 4.2") (WxDxH)			
Net weight	3.7 kg; 8.1 lbs			
Power consumption	100 - 240V, 50/60 Hz			
Operating voltage	170W	210W	255W	255W
Operation				
Standby	5W			
Temperature range				
Operational	+5 to +35 °C (+41 to +95 °F)			
Storage	-25 to +70 °C (-13 to +158 °F)			
EMC approbation	Class B			
Package	Compact remote control Laser pointer compact remote control Power cord Combined VGA-USB cable (1.5m) Audio/Video cable (2m) Scart adapter (scart to RCA audio/video)* Soft carrying bag Lenscap CD-ROM User Guide (UK, D, F, E, PT, NL, I), Chinese version printed in region. Quick Setup Card (UK, D, F, E, PT, NL, I) Warranty card + envelopes			
Optional accessories	replacement lamp 132W (LCA3116/00) 150W (LCA3118/00) 200W (LCA3123/00) 200W (LCA3124/00) Softbag (LCA 1120/00) Ceiling mount (LCA2211/00) VGA extension cable, 15 meters (LCA5300/00) Monitor Y-cable (LCA5310/00)			
Executions	LC3132/17 USA version LC3132/40 RoW version LC3132/45 UK version	LC3142/17 USA version LC3142/40 RoW version LC3142/45 UK version	LC3136/17 USA version LC3136/40 RoW version LC3136/45 UK version	LC3146/17 USA version LC3146/40 RoW version LC3146/45 UK version

* : depending on regional requirement



Image diagonal size	Projection distance					
	Tele zoom		Wide zoom			
[inch]	[metres]	[inch]	[metres]	[inch]	[metres]	[metres]
40	1,0	75	1,9	62	1,6	
60	1,5	114	2,9	93	2,4	
70	1,8	133	3,4	108	2,7	
80	2,0	153	3,9	123	3,1	
100	2,5	191	4,8	155	3,9	
150	3,8	286	7,3	233	5,9	
200	5,1	381	9,7	310	7,9	
250	6,4	477	12,1	388	9,8	

* See also interactive Projection Assistant on CDROM.

www.ce.philips.com

The Philips Guarantee

The Philips range of advanced multimedia projectors combines portability, reliability and unsurpassed performance with a host of technological innovations. All of which ensures that you enjoy impressive and hassle-free projection wherever you are. What else would you expect from the innovative world leader in sound and vision technology?

3-years warranty and free support

Every bSure projector comes with a full three-year warranty. In the first year this unique offer is backed up by the outstanding Philips First Choice** services, including a

toll-free helpline, that offers you assistance and advice seven days a week and in case you need servicing, you'll receive a temporary replacement with free delivery, within 48 hours. It's simply an unbeatable package.

Extreme compatibility

Philips projectors are extremely compatible with a whole range of data and video sources, thanks to their highly advanced scaling technology, which converts signals without any loss or deterioration. It's a serious advantage when you need to make an extra special impression with a mind-blowing multimedia experience.

