



Brilliant, Razor Sharp Images — Unmatched Versatility!

- Exceptional Brightness** *With 2600 ANSI lumens, Philips' cClear Series delivers the light output you need for big brilliant presentations even in full ambient light.*
- Quiet Operation** *Philips' unique PAST™ and SmartDimmer systems reduce fan noise to a whisper quiet 30dB.*
- Dual Window Display** *Integrated split screen processor allows simultaneous viewing of two different inputs – great for video conferencing applications.*
- Extended Connectivity** *Robust input panel array accommodates a wide range of Video / Data input signals and formats including DVI-I and RS232 control.*
- Exceptional Picture Quality** *Philips' advanced digital architecture delivers exceptional picture quality from any computer or video source.*
- Easy-to-Use** *Powerful SmartSet™ auto-alignment system and highly intuitive menus make setup extremely fast and easy.*
- Extend Lamp Life** *Philips' innovative SmartDimmer and SmartSave™ features help extend valuable lamp life.*
- Theft Deterrents** *SecurityMax™ theft deterrent system and integrated Kensington lock protect your investment in environments where security is a challenge.*



Philips Multimedia Projectors



PHILIPS

Model Name	cClear SV1 LC4731	cClear XG1 Brilliance LC4745
LCD	3x 0.79" high-temperature polysilicon active matrix LCD panels	
Native Resolution	SVGA (800x600)	XGA (1024x768)
Number of pixels	3x 480,000	3x 786,432
Brightness - Normal Mode	2600 ANSI lumens	
Brightness - SmartDimmer Mode	2000 ANSI lumens	
Contrast	400:1	
Audible Noise		
Normal Mode	33 dB	
SmartDimmer Mode	30 dB	
Lamp	200 watt Philips UHP™ lamp	
Average Lamp Life	2000 hours	
Lens	F/1.75 - 2.1 f = 26.7 - 31.8 mm Manual Focus, Manual Zoom, Short Throw (1.63 - 1.95 :1) Projection Distance 52" - 390" (for image diagonal 40" - 250")	
Input Compatibility		
Video	NTSC 3.58 / 4.43 / PAL / SECAM S-Video (Y/C) Component Video Input: YCbCr, YPbPr, RGB HDTV Compatible: (480i, 480p, 720p, 1080i) Compatible with: VGA, SVGA, XGA, SXGA, Mac/PC Horizontal Scan Rate: 15 - 108 kHz Vertical Refresh Rate: 50 - 120 Hz Bandwidth: 140 MHz	
Computer	Display Data Channel: DDC 1/2B Microsoft® Windows®, 95/98/ME/2000/XP compatible	
Plug and Play Compatibility		
Input Connectors		
Video	Component Video (R/Pri/Cr, G/Y, B/Pb/Cb: 3x RCA) 1x Composite Video (RCA) 1x S-Video (Y/C on 4 pin mini-DIN)	
Computer		
Data 1	1x RGB Data (D15 pin)	
Data 2	1x DVI-I (analog + digital)	
Audio		
Video	Stereo Audio (2x RCA)	
Data 1 / Data 2	2x Stereo Audio (3.5 mm stereo jack) 1x Digital Audio (via USB)	
Audio Output	3.5mm stereo jack	
Speaker	6 watts	
I/O Ports	Mouse Control, PC Audio, SecurityMax, ProjectorMax Mouse Control for external control of projector	
1x USB (type B)		
1x PS/2 (mini Din)		
1x RS232 (D9 pin)		
Features	Dual Window and Picture in Picture for multi-source display SecurityMax™ theft deterrent system, Kensington Lock YourLogo™ Start-Up Screen, ProjectorMax control software SmartSet™ automatic image quality optimization SmartSave™ auto-standby mode helps extend lamp life SmartDimmer (reduces lamp power to extend lamp life and minimize audible noise) ColorTracking™ provides superior colorimetry for Video display Keystone correction H: ±20 degrees, V: ±40 degrees Digital Zoom (16X) and Freeze An external computer monitor can be connected using supplied Y-Cable	
Physical Specifications		
Product Dimensions (HxWxD)	4.2" x 9.25" x 13.2" (108 x 235 x 335 mm)	
Product Weight	8.4 lbs (3.8 kg)	
Power Consumption		
Operating Voltage	100-240 VAC, 50/60Hz	
Power Consumption	250 watts	
Standby Power Consumption	2 watts	
Temperature Range		
Operational	+41 to +95 °F (+5 to +35 °C)	
Storage	-13 to +158 °F (-25 to +70 °C)	
FCC Rating	Class B	
Included Accessories	Compact Laser Pointer Remote Control, Power Cord, Lens Cap, Combined VGA+USB Cable (59" / 1.5m), DVI Cable (59"/1.5m), Audio+Video cable (79" / 2m), S-Video Cable (79" / 2m), D15-pin Y-Cable, Scart to RCA Adapter (audio/video), DVI-VGA Adapter, Soft Carrying Bag, CD-ROM User Guide, Quick Setup Card	
Optional Accessories	LCA3123 200 watt Replacement Lamp LCA2211 Ceiling Mount for bSure / cClear Series	
Model Number	LC4731	LC4745



Key Features


- High Brightness: 2600 ANSI Lumens
- Quiet Operation as low as 30dB
- SecurityMax™ Theft Deterrent System
- Dual Window Display

Projection Chart

Image Diagonal Size	Projection Distance					
	Tele Position		Wide Position			
[inch]	[meters]	[inch]	[meters]	[inch]	[meters]	
40	1.0	62	1.6	52	1.3	
60	1.5	94	2.4	78	2.0	
70	1.8	109	2.8	91	2.3	
80	2.0	125	3.2	104	2.6	
100	2.5	156	4.0	130	3.3	
150	3.8	234	5.9	195	5.0	
200	5.1	312	7.9	260	6.6	
250	6.4	390	9.9	325	8.3	

All values are estimates

Input Panel



Hassle-Free Service and Support

Philips' First Choice Warranty assures you that you'll always be ready to present even in case of equipment failure thanks to our toll-free technical support (1 year), 48-hour Roadside Assistance Program and 3-year Parts and Labor Warranty.**

INTERNET ADDRESS: <http://www.philipsusa.com>
TECHNICAL SUPPORT: Toll Free 1-888-873-4672
SALES INFORMATION: Toll Free 1-888-327-3636

Philips Consumer Electronics
64 Perimeter Center East
Atlanta, Georgia 30346

Design and specifications are subject to change without notice. Printed in the U.S.A., ©2003 Philips Consumer Electronics Co., a Division of Philips Electronics North America Corp.

* Available in the USA and Western Europe. Check with your dealer for similar coverage in other regions.

**Projector warranty is 3 years or 2500 hours, whichever comes first. Run time is kept by an internal clock.

Warranty on internal projection lamp is 12 months.

All trademarks are property of their respective owners.

CCM-186_10/03

Literature Order Number: cClear Series

