



# Brilliant, Razor Sharp Images — Superb Wireless Freedom!

## Advanced Wireless Connectivity

The cClear XG1 Wireless utilizes a highly advanced digital architecture and state-of-the-art compression algorithms to flawlessly display PC-based Data images over an IEEE802.11b (WiFi) compliant WLAN in near real-time with minimal latency.

## Exceptional Brightness

With 2600 ANSI lumens, the cClear XG1's brilliant images have the power to punch through even the highest ambient light environments.

## Dual Window Display

Integrated split screen processor allows simultaneous viewing of two different inputs – great for video conferencing applications.

## Quiet and Economical Operation

Innovative PAS™ and SmartDimmer systems reduce fan noise to a whisper quiet 30dB. Philips' SmartSave™ feature helps extend valuable lamp life.

## Extended Connectivity

Robust input panel array accommodates a wide range of Video / Data input signals and formats including DVI-I and RS232 control.

## Easy-to-Use

Powerful SmartSet™ auto-alignment system and highly intuitive menus make setup extremely fast and easy.

## Theft Deterrents

SecurityMax™ theft deterrent system and integrated Kensington lock protect your investment in environments where security is a challenge.



Philips Multimedia Projectors



# PHILIPS

Model Name	cClear XG1 Wireless	
Model Number	LC4746	
<b>LCD</b>	3x 0.79" high-temperature polysilicon active matrix LCD panels	
Native Resolution	XGA (1024x768)	
Number of pixels	3x 786,432	
Brightness - Normal Mode	2600 ANSI lumens	
Brightness - SmartDimmer Mode	2000 ANSI lumens	
Contrast	400:1	
<b>Audible Noise</b>		
Normal Mode	33 dB	
SmartDimmer Mode	30 dB	
<b>Lamp</b>	200 watt Philips UHP™ lamp	
Average Lamp Life	2000 hours	
<b>Lens</b>	F/1.75 - 2.1 f = 26.7 - 31.8 mm Manual Focus, Manual Zoom, Short Throw (1.63 - 1.95 :1) Projection Distance 52" - 390" (for image diagonal 40" - 250")	
<b>Input Compatibility</b>		
Video	NTSC 3.58 / 4.43 / PAL / SECAM S-Video (Y/C) Component Video Input: YCbCr, YPbPr, RGB HDTV Compatible: (480i, 480p, 720p, 1080i) Compatible with: VGA, SVGA, XGA, SXGA, Mac/PC Horizontal Scan Rate: 15 - 108 kHz Vertical Refresh Rate: 50 - 120 Hz Bandwidth: 140 MHz	
Computer	Display Data Channel: DDC 1/2B Microsoft® Windows®, 95/98/ME/2000/XP compatible Compatible with wireless LAN cards running on Microsoft Windows 98, Me, 2000, XP Supports 64-bit and 128-bit WEP encryption	
Plug and Play Compatibility		
WiFi (IEEE802.11b)		
WEP		
<b>Input Connectors</b>		
Video	Component Video (R/Pr/Cr, G/Y, B/Pb/Cb: 3x RCA) 1x Composite Video (RCA) 1x S-Video (Y/C on 4 pin mini-DIN)	
Computer		
Data1	1x RGB Data (D15 pin)	
Data 2	1x DVIH (analog + digital)	
<b>Audio</b>		
Video	Stereo Audio (2x RCA)	
Data 1 / Data 2	2x Stereo Audio (3.5 mm stereo jack) 1x Digital Audio (via USB)	
Audio Output	3.5mm stereo jack	
Speaker	6 watts	
<b>I/O Ports</b>		
1x USB (type B)	Mouse Control, PC Audio, SecurityMax, ProjectorMax	
1x PS/2 (mini Din)	Mouse Control	
1x RS232 (D9 pin)	for external control of projector	
1x Integrated WiFi Hub	In conjunction with Philips' PresenterMax software, allows PC-based images to be transmitted to the projector at near real-time speeds over a WiFi (IEEE802.11b) compliant WLAN	
<b>Features</b>	PresenterMax software controls all wireless functions Dual Window and Picture in Picture for multi-source display SecurityMax™ theft deterrent system, Kensington Lock YourLogo™ Start-Up Screen, ProjectorMax control software SmartSet™ automatic image quality optimization SmartSave™ auto-standby mode helps extend lamp life SmartDimmer (reduces lamp power to extend lamp life and minimize audible noise) ColorTracking™ provides superior colorimetry for Video display Keystone correction H: ±20 degrees, V: ±40 degrees Digital Zoom (16X) and Freeze An external computer monitor can be connected using supplied Y-Cable	
<b>Physical Specifications</b>		
Product Dimensions (HxWxD)	4.7" x 9.25" x 13.2" (121 x 235 x 335 mm)	
Product Weight	9.0 lbs (4.1 kg)	
<b>Power Consumption</b>		
Operating Voltage	100-240 VAC, 50/60Hz	
Power Consumption	250 watts	
Standby Power Consumption	2 watts	
<b>Temperature Range</b>		
Operational	+41 to +95 °F (+5 to +35 °C)	
Storage	-13 to +158 °F (-25 to +70 °C)	
<b>FCC Rating</b>	Class B	
<b>Included Accessories</b>	Compact Laser Pointer Remote Control, Power Cord, Lens Cap, Combined VGA+USB Cable (59" / 1.5m), DVI Cable (59"/1.5m), Audio+Video cable (79" / 2m), S-Video Cable (79" / 2m), D15-pin Y-Cable, Scart to RCA Adapter (audio/video), DVI-VGA Adapter, Soft Carrying Bag, CD-ROM User Guide, Quick Setup Card	
<b>Optional Accessories</b>	LCA3123 200 watt Replacement Lamp LCA2211 Ceiling Mount for bSure / cClear Series	
<b>Model Number</b>	LC4746	



## Key Features


- High Brightness: 2600 ANSI Lumens
- Fast Wireless Connectivity
- SecurityMax™ Theft Deterrent System
- Quiet Operation as low as 30dB

## Projection Chart

Image Diagonal Size		Projection Distance			
		Tele Position		Wide Position	
[inch]	[meters]	[inch]	[meters]	[inch]	[meters]
40	1.0	62	1.6	52	1.3
60	1.5	94	2.4	78	2.0
70	1.8	109	2.8	91	2.3
80	2.0	125	3.2	104	2.6
100	2.5	156	4.0	130	3.3
150	3.8	234	5.9	195	5.0
200	5.1	312	7.9	260	6.6
250	6.4	390	9.9	325	8.3

All values are estimates

## Input Panel



## Hassle-Free Service and Support

Philips' First Choice Warranty assures you that you'll always be ready to present even in case of equipment failure thanks to our toll-free technical support (1 year), 48-hour Roadside Assistance Program and 3-year Parts and Labor Warranty.\*\*

INTERNET ADDRESS: <http://www.philipsusa.com>  
TECHNICAL SUPPORT: Toll Free 1-888-873-4672  
SALES INFORMATION: Toll Free 1-888-327-3636

Philips Consumer Electronics  
64 Perimeter Center East  
Atlanta, Georgia 30346

Design and specifications are subject to change without notice. Printed in the U.S.A., ©2003 Philips Consumer Electronics Co., a Division of Philips Electronics North America Corp.

\* Available in the USA and Western Europe. Check with your dealer for similar coverage in other regions.

\*\*Projector warranty is 3 years or 2500 hours, whichever comes first. Run time is kept by an internal clock.

Warranty on internal projection lamp is 12 months.

All trademarks are property of their respective owners.

CCM-186\_10/03

Literature Order Number: cClear XG1 Wireless

