

Multimedia Projector




Show and go

- *Excellent picture quality (1400 ANSI Lumens)*
- *Extreme high contrast (2000:1)*
- *Ultimate ease of use*
- *Protected by SecurityMax™*
- *Suitable for meeting rooms for 2 to 20 people*



PHILIPS

bCool SV1



bCool SV1	
Type number	LC5331/00
Display device	0.55" DMD (DDR)
Brightness at normal mode	1400 ANSI lumen
Brightness at SmartDimmer mode	1200 ANSI lumen
Contrast	2000:1
Resolution	SVGA (800 x 600)
Lamp	180W lamp, end user replaceable
Lamp life at normal mode	1500 hours (average lifetime in use)
Lamp life at SmartDimmer mode	2000 hours (average lifetime in use)

Lens	F2.4-2.7, f = 19.7-23.6 mm Manual Zoom (x 1.2), manual focus Projection distance 1.2m (3' 9") ~ 12m (39' 4") Diagonal size 27" ~ 328"
------	--

Input compatibilities	PAL: B, D, G, H, I, M, N, NTSC: 3.58, 4.43, SECAM: B, D, G, K, K1, L S-Video (Y/C) Component video input (YCbCr, YPbPr, RGBsync) EDTV/HDTV video input (480p, 575p, 720/60p, 720/50p, 1035i, 1080/60i, 1080/50i) H-sync. 15-70 kHz, V-sync. 43-85 Hz
Data	
Input connectors	1 1 x CVBS (RCA) 2 1 x S-Video (Y/C DIN) 3 1 x Data in (15p D-sub) 4 USB (type B)
Mouse	34 dB(A) 32 dB(A)
Audible noise at normal mode	
Audible noise at SmartDimmer mode	

Features	SmartSet™ (automatic image quality optimisation) SmartSave™ (auto-standby mode to increase effective lamp usage) SmartDimmer (function to dim brightness and reduce audible noise) Digital zoom (1, 4, 9, 16 times), digital freeze, digital keystone correction (V +/-16°), PIP 258 x 81 x 204 mm (10' 2" x 3' 1" x 8' 0") (WxHxD) 1.9 kg (4.2 lbs)
Dimensions	
Net weight	

Power consumption	AC100-120/200-240V, 50/60 Hz
Operating voltage	220W
Power consumption at normal mode	190W
Power consumption at SmartDimmer mode	< 12W
Standby power	
Temperature range	
Operational	+5 to +35 °C (+41 to +95 °F)
Storage	-10 to +60 °C (14 to +140 °F)
EMC/EMI	Class B

Supplied accessories	Compact remote control Alkaline batteries for remote control Power cord (1.8 m) VGA cable (1.8 m) USB cable (1.8 m) Video cable (1.8 m) S-Video cable (1.8 m) Soft bag Cable pouch Lens cap CD-ROM user guide (8 languages, UK, D, F, E, PT, NL, I, Chinese) with SecurityMax™ software Quick Setup Card Warranty card + envelopes
Optional accessories	180W replacement lamp (LCA3126/00) Ceiling mount (LCA2218/00)

Image diagonal size		Projection distance			
		Tele zoom		Wide zoom	
[inch]	[metres]	[inch]	[metres]	[inch]	[metres]
40	1,0	68	1,7	56	1,4
60	1,5	102	2,6	84	2,1
70	1,8	119	3,0	98	2,5
80	2,0	136	3,5	112	2,8
100	2,5	170	4,3	140	3,6
150	3,8	254	6,5	210	5,3
200	5,1	339	8,6	280	7,1
250	6,4	424	10,8	350	8,9

*See also interactive Projection Assistant on CDROM.

www.ce.philips.com

The Philips Guarantee

The Philips range of advanced multimedia projectors combines portability, reliability and unsurpassed performance with a host of technological innovations. All of which ensures that you enjoy impressive and hassle-free projection wherever you are. What else would you expect from the innovative world leader in sound and vision technology?

3-years warranty and free support

Every bCool projector comes with a full three-year warranty. In the first year this unique offer is backed up by the outstanding Philips First Choice** services, including a

toll-free helpline, that offers you assistance and advice seven days a week and in case you need servicing, you'll receive a temporary replacement with free delivery, within 48 hours. It's simply an unbeatable package.

Extreme compatibility

Philips projectors are extremely compatible with a whole range of data and video sources. This compatibility is high compared to competitive projectors. All thanks to their highly advanced scaling technology. It's a serious advantage when you need to make an extra special impression with a mind-blowing multimedia experience.

