

Home Entertainment Projector

Larger than life!!



- 1000 ANSI Lumens
- SVGA resolution
- Excellent Video Performance (contrast ratio 350:1)
- Compact (H: 102mm W: 328mm D: 226mm)
- Stylish Design; Fits in every interior
- Easy plug&play
- Ultra Silent (32dB Philips Air System™)



Let's make things better.



PHILIPS



technical specifications



Monroe

1000 ANSI lumens



SVGA resolution



Excellent Video Performance
(contrast ratio 350:1)



Compact; Fits in every interior!
(H: 102mm W: 328mm D: 226mm)



Stylish Design



Easy plug&play



Ultra Silent (32dB Philips Air System™
for silent operation)

- SmartSet (Auto-image for trouble-free operation and optimal image quality)
- Smart Save (Auto standby mode to increase effective lamp usage)
- 120W long-lasting UHP™ lamp for uniform images, rich colours and brightness over time
- Advanced compatibility for both data and video
- Kensington lock
- Ceiling mountable
- 3 year warranty

Standard accessories

Every Monroe projector package comes with the following as standard:

- Compact Remote control
- Power cord
- Audio/video cable, S-video cable
- Audio converter plug (3.5 mm jack to 2x RCA)
- Scart adapter (scart to RCA audio/video)
- Soft carrying bag
- Lens cap
- Printed User Guide
- CD-ROM User Guide
- Quick Set-up Card

For optional accessories please contact your dealer.

	Monroe LC6131
LCD	3x 0.9" high-temperature poly-silicon active matrix LCDs
Resolution	SVGA (800x600)
Number of pixels	1.440.000
Brightness	1000 ANSI lumens
Contrast	350:1
Lamp	UHP™-compact 120W, end user replaceable
Average lifetime	6000 hours of use
Lens	F/1.8 - 2.2 ; f = 37 - 47 mm 1.3x Manual Zoom; Manual Focus Projection distance 1,1 - 12 m (image diagonal 20" - 300")
Input compatibility	
Video	NTSC 3.58, 4.43 ; PAL N, M, B/G ; SECAM S-video/S-VHS (Y/C) Component video input (RGB-Y, YUV, YPbPr) HDTVReady™-HDTV video input (480p, 720p, 1080i)
Computer	PC and MAC compatible, Multi scan VGA-SXGA Horizontal scan rate: 50 - 108 kHz Vertical refresh rate: 50 - 120 Hz Bandwidth: 140 MHz
Input connectors	
Video	1x CVBS Video (RCA) 1x S-Video (Y/C DIN)
Computer	1x Data in (15p D-sub)
Audio	
Video	1x Stereo Audio (3.5 mm stereo jack)
Data	1x Stereo Audio (3.5 mm stereo jack)
Output connectors	
Audio	1x Stereo Audio (3.5 mm stereo jack)
Features	SmartSet™ automatic image quality optimisation SmartSave™ auto-standby mode to increase effective lamp usage Digital Keystone correction Digital Zoom and Freeze 32dB Philips Air System for silent operation
Dimensions	
Net weight	102 x 328 x 226 mm (4.0" x 12.9" x 8.9") (HxWxD) 3.6 kg; 7.9 lbs
Power consumption	
Operating voltage	100 - 240V, 50/60 Hz
Operation	180W
Standby	5W
Temperature range	
Operational	+5 to +35 °C (+41 to +95 °F)
Storage	-25 to +70 °C (-13 to +158 °F)
Package	Monroe Compact remote control Power cord VGA cable (2m) Audio/Video cable (2m) S-video cable (2m) Audio-Out converter plug (3.5mm stereo jack to 2x RCA) Scart adapter (scart to RCA audio/video)* Soft carrying bag Lenscap CD-ROM User Guide (YK, D, F, E, PT, NL, I) + Printed user guide Quick Setup Card (UK, D, F, E, PT, NL, I) Ceiling mount (LCA2210/00)
Optional accessories	UHP™ 120W replacement lamp (LCA3115/00) Ergonomic trackerball remote control (LCA4117/00) RS-232 Mouse Receiver (LCA4119/00) VGA extension cable, 15 metres (LCA5300/00) RCA/VGA Component video cable (LCA5311/00) Scart/RCA Component video adapter (LCA5312/00) Composite video extension cable, 15 metres (LCA5313/00)
Executions	LC6131/40 EU version LC6131/45 UK version

* : depending on regional requirement

Image diagonal size		Projection distance			
		Tele zoom		Wide zoom	
[inch]	[metres]	[inch]	[metres]	[inch]	[metres]
40	1,0	79	2,0	61	1,6
60	1,5	120	3,0	92	2,3
70	1,8	140	3,6	108	2,7
80	2,0	160	4,1	123	3,1
100	2,5	201	5,1	154	3,9
150	3,8	302	7,7	232	5,9
200	5,1	403	10,2	310	7,9
250	6,4	504	12,8	388	9,8

www.pcstuff.philips.com/projectors

