

Philips Multimedia Projectors In a silent way.



Hopper XG20 Impact	Hopper XG20	Hopper SV20 Impact	ProScreen PXG10	
xxxx	xxxx	xxx	xxxx	resolution
xxx	xx	xxx	xxxx	brightness
xxxx	xxxx	xxxx	xxx	silence
xxxx	xxxx	xxxx	xxx	portability
xxxx	xxxx	xxxx	xxxx	lamp life
xxx	xxx	xxx	xxxx	colour/contrast
xxx	xxxx	xxxx	xxx	work meetings
xxxx	xxx	xx	xxxx	management presentations
xx	xxx	xxxx	xx	video conference
xxxx	xxxx	xxx	xxxx	graphics/CAD/CAM
xxxx	xxx	xxx	xxxx	POS/trade fairs
xxx	xxxx	xxxx	xx	home cinema



- UHP™ lamp
- Widest compatibility
- Easy plug&play
- Free support

www.pcstuff.philips.com/projectors

Let's make things better.



PHILIPS

The power to impress.
 With a pin-sharp, high contrast picture the new XG20 Impact gives you the power to impress - anytime, anywhere.



1250 ANSI lumens



XGA resolution



33dB PAS™ (Philips Air System) for silent operation



Ultra-lightweight - just 4.9 kg

- Auto Image
- Digital keystone correction
- USB
- Long lasting - up to 2000 hours - 150W UHP™ lamp
- Easy plug&play
- Ceiling mountable

Ultra high performance projector

Hopper XG20 Impact



Ready for impact.
 The new SV20 Impact: stylish, compact, silent, lightweight, easy to operate, and available at an affordable price - what more can you ask for in a projector?



1250 ANSI lumens



SVGA resolution



33dB PAS™ (Philips Air System) for silent operation



Ultra-lightweight - just 4.9 kg

- Auto Image
- Digital keystone correction
- USB
- Long lasting - up to 2000 hours - 150W UHP™ lamp
- Easy plug&play
- Ceiling mountable

Advanced SVGA projector

Hopper SV20 Impact



Pumped-up performance.
 The new enhanced Hopper XG20 offers pumped-up performance for power presenters and XGA notebook users. The modern digital replacement for overhead projectors and flip charts.



1000 ANSI lumens



XGA resolution



33dB PAS™ (Philips Air System) for silent operation



Ultra-lightweight - just 4.9 kg

- Auto Image
- Digital keystone correction
- USB
- Long lasting - up to 2000 hours - 150W UHP™ lamp
- Easy plug&play
- Ceiling mountable

High performance XGA projector

Hopper XG20



Super high bright XGA performance.
 The professional projector, for professional presentations.



2200 ANSI lumens



XGA resolution



High advanced compatibility



Motorised Zoom and Focus lens system

- Long lasting - up to 2000 hours - 150W UHP™ lamp
- Easy plug&play
- Ceiling mountable
- Optional easy fit Tele and Wide lenses for increased applications

High-end projector

ProScreen PXG10



3122 435 64780

Let's make things better.



PHILIPS