#### features: **ProScreen PXG10**

Super High Bright XGA performance



• 2200 ANSI Lumens



True XGA resolution

#### **ProScreen**



High Advanced compatibility



Motorised Zoom and Focus Lens system



Low Acoustical Fan Noise (35 dBA)



Easy Plug & Play

- Long-lasting up to 2000 hours 150 Watt UHP  $^{\rm TM}$  (Ultra High Performance) lamp for uniform images, rich colours and brightness over time, without hot spots
- High Advanced Full- and Semi- Automatic scaling technology, guarantees compatibility with all
- video and PC/Mac data sources up to UXGA

  High degree on compatibility via multiple Inputs for Computer, Standard and High Definition (HD) Video applications
- HDTV Compatible 480i / 480p / 720p / 1080i (4:3 & 16:9 aspect ratios)
- Component Video Input
- Superior Video Quality: 3D Y/C circuitry, Digital comb filter, 3D Noise reduction, Interlaced (I) or Progressive (P) scan, Digital motion correction
- Motorised Lens functions (1:1.3x), by Power Zoom / Focus also operating in combination with the optional available snap-off Wide & Tele
- Multiple projection application; Ceiling and Desk operation in front- as well in rear projection.
- $\bullet \ \mathsf{Digital} \ \mathsf{picture} \ \mathsf{enhance} \ \mathsf{technologies}; \mathsf{Digital}$ Zoom, Digital Freeze, Digital Keystones
- Auto voltage for safe usage around the globe
  Audience size up to over 300 people (board-
- room, lecture hall or auditorium)
- Portable weight (7,2 kg), compact design with integrated carrying handle, which makes the product also suitable for portable use
- Slot for optional Kensington lock
   Free remote control included
- Full wired remote control possible via RS-232C port for fixed installation operation

- First Choice\* support
- Free toll-free support\*

Standard mode (4:3)

	Image diagonal size		Projection distance			
			Tele zoom		Wide zoom	
	[inch]	[meters]	[inch]	[meters]	[inch]	[meters]
Minimum	40	1,02	55	1,4	75	1,9
	60	1,52	87	2,2	114	2,9
	72	1,83	102	2,6	134	3,4
	84	2,13	122	3,1	157	4,0
	100	2,54	146	3,7	193	4,9
	150	3,81	220	5,6	283	7,2
	200	5,08	291	7,4	386	9,8
Maximum	300	7,62	433	11,0	563	14,3

For wide mode (16:9) different projection distances are applicable

Big picture...

eye for detail



#### main target specifications

3x 1.3" HT Poly Silicon Active Matrix with u-lenses 2.359,296 pixels, RGB stripe (1024x768)

Brightness 2200 ANSI lumens with 90% uniformity (CCR)

Contrast

Lamp UHP 150; End user replaceable

2000 hours

F1.7 - 2.3; f= 49.1 - 63.8 mm 1.3x Motor Zoom / Focus

Proj. Dist. 1.4 – 1.9 (40"), 3,7 – 4,9m (100"), 11 – 14,3m (300") Diagonal 40 - 300"

Input signals NTSC 3.85, 4.43 /PAL-CCIR, Secam Video

DTV/HDTV (1080i, 720p,480p with 4:3 and 16:9 aspect ratios)

and DVD compatible.

PC and Mac compatible, Multi scan VGA, S-VGA, XGA, SXGA UXGA via LIMESCO kind full screen <u>true XGA display</u>; Auto Data 1 and 2

Identification; Plug & Play VESA, DDC 1/2b
Hor. scan rate: 15 – 125 kHz; Vert. Refresh rate 43 – 200 Hz;

120 - 120 V / 220 - 240 V; 50/60 Hz; 265 W Power in

S-Video (Y/C DIN)/Video (RCA)/ Stereo Audio (2x RCA) Video Mini D-sub data (15 pin)/PC, RGBHV, PbPrY Csync (via BNC)

Stereo Audio (M3)

Mini D-sub data (15 pin)/PC Stereo Audio (M3) RS232C 9-pin mini DIN

Mains Mains input socket (3 pin) Outbut connections

Data out Mini D-sub data (15pin) Stereo Audio (M3) Audio

Multi Input projector for Data as well for Video applications (3D Y/C separation, 3 line Digital comb filter, 3D Noise reduction, Colour transient and Y delay) Specialities Long life and almost constant light output over entire lamp life projection lamp Automatic perfect Multi Scan data input handling, VGA up to UXGA resolutions.

Low Acoustical Noise (35dBA)

Intuitive Graphic User Interface for Ease of Use Auto Source and Interlaced/Progressive (I/P)scan conversion

Power save modes (4)

Auto Image; Phase, Clock, Position H/V

Optional lenses: Tele and Wide lenses which can be fit in combination with the

261 x 129 x 356 mm (WxHxD); 12 dm3 **Dimensions** 

7,2 kg; <16 lbs ProScreen PXG10 + lenscap Net weight **Package** 

2x Power cord; USA version plus Continental Europe version

Remote Control + 3x AA batteries + USB Mouse receiver RCA cable (Video/Audio stereo) + RCA - BNC adapters (3x)

Scart - RCA adapter

DIN-D sub RS232C cable
User Guide (CD-ROM) plus Quick Reference, Registration card

LC 1041/00 Global version **Executions** 

UHP 150 Projection lamp

soft carrying bag Exchangeable lenses; Tele and Wide lenses Ceiling mount brackets (High, Low ceilings)

ીણો

More information

www.pcstuff.philips.com/projectors tel:

Belgium fax: +800 30 30 06 00 ō 3500 , without , 435 64720 Creative Display Solutions: P.O. Box 364 and specifications are subject to change Check US, Western 3122 4 Philips Design











Let's make things better.



**PHILIPS** 



PXG10 LEAFLET 20-03-2000 12:14 Pagina 5



## The Philips Guarantee

# The Philips range of advanced multimedia projectors.

Combining portability, reliability, and unsurpassed performance with a host of technological innovations. All of which guarantees you impressive and hassle-free projection wherever you are. Just what you'd expect from the innovative world leader in sound and vision technology.

#### UHP™ lamp

All of our projectors contain the unique Philips  $UHP^{TM}$  (Ultra High Performance) lamp. The first lamp to retain rich colours

and brightness without creating hot spots over its amazingly long life. Cutting costs and hassle.

#### Extremely compatible

Philips projectors are extremely compatible with a whole range of data and video sources, thanks to their highly advanced scaling technology. And it always converts information without any loss or deterioration. A serious advantage when you need to make a good impression.

#### Free support

The whole unique Philips projector package is backed up by the outstanding Philips First Choice service. A Toll-Free Helpline\* offers you help and advice, seven days a week, while the Philips First Choice\* service is there for more difficult problems - guaranteeing you a temporary replacement, with free delivery, within 48hrs. A truly unbeatable package.

\* Currently only available in the US and Western Europe. Check with your Philips dealer for more details.



### The professional projector, for professional presentations

The new ProScreen PXG10 is one of the most powerful and compatible projectors on the market today. Reliable, versatile, and easy to use, it is the ultimate solution to the problems of presenting in large conference rooms and lecture theatres.





2200 ANSI lumens



High compatibility (UXGA/HDTV)



**XGA** resolution



Motorised zoom and focus lenses

- 150W long-lasting UHP™ (Ultra High Performance) lamp
- Ceiling mountable for perfect installation
- Low Accoustical Fan Noise (35 dBA)
- Easy Plug & Play
- Digital keystone correction compensates for extreme vertical angles
- User guide on CD-ROM

#### A truly bright idea

The total picture performance of the new PXG10 is simply breathtaking. With 2200 ANSI lumens, it is more than twice as bright as its predecessor, thanks to a new 150W UHP™ lamp, and LCD panels equipped with micro-lenses. And with this much power you don't have to worry about the traditional problem of distortion from daylight. You can even present in glaring sunlight - an important benefit in larger rooms where the light cannot always be blocked out completely.

This increase in power though, has not been at the expense of reliability. The UHP™ lamp has a useable life of 2,000hrs, and the projector's durable design and robust construction, backed by the Philips free worldwide support package, guarantees you trouble-free ownership.

#### **Outstanding compatibility**

Another major advantage of the PXG10 is its highly advanced compatibility, which enables you to use any video or data source up to CAD/CAM level to enhance your presentation.

It is also tremendously versatile, thanks to the digital keystone correction feature, which enables you to set it up virtually anywhere in the presentation room, and still enjoy the same high image quality. This is enhanced still further with a choice of optional zoom lenses, which can be easily and quickly changed by the presenter before a presentation.

And once in position, it is remarkably easy to set up and run your presentation, because of features such as auto-imaging, simple plug-in connections, and motorised lens adjustment. Yet more examples of the power and versatility that has made the ProScreen PXG10 the first choice of the professional.





# The accessories

Helping you get the most out of your projector

The ProScreen PXG10 comes with a free wireless remote control, featuring illuminated buttons for ease of use, as well as a USB mouse receiver.

There's also a smart range of optional accessories to help you get the most out of your projector, including:

- A selection of ceiling mounts (for high or low ceilings)
- 'Easy-fit' Tele and Wide zoom lenses for increased applications

- Soft carrying bag
- Spare UHP™ lamps
- Projection screens

#### Philips projectors

The ProScreen PXG10 is part of an award-winning range of Philips projectors. Projectors with different strengths and features, to meet the different needs of different applications. So whatever your demands, Philips projectors can more than match them.

For more information check our website.







#### The full Philips portfolio

A selection of additional presentation aids are also available, including monitors, TVs, PC cameras, and DVD players. Visit our website for the complete list.

www.pcstuff.philips.com/projectors