




Philips
Hands-free headset

LFH0331



Record your conversations

Ideal for digital recorders

The hands-free headset is ideal for people on the move who desire good-quality sound and clear voice recording. Its in-cord mini-microphone is discreet and the tie clip ensures that the microphone is always in the perfect position for optimal recording.

Superior audio quality

- A tie clip keeps the microphone always in place
- Condenser microphone for superb recording quality
- Unidirectional design picks up speaker's voice only

For optimal results

- Achieve optimal results with a total Philips solution
- Durable materials enhance quality for extended use
- Lightweight solution for the mobile dictation user

PHILIPS
sense and simplicity

Specifications

Microphone

- Connector: 3.5 mm, mono, right-angled
- Connector finish: Gold-plated
- Directivity: unidirectional
- Frequency response: 20–20,000 Hz
- Impedance: approx. 2.2 kOhm @ 1 kHz
- Standard operating voltage: 3 V–10 V
- Type: electret condenser microphone
- Sensitivity: -60 dB ± 2 dB

Earphone

- Cable length: 1.1 m/3.6 ft.
- Connector: 3.5 mm, mono, right-angled
- Connector finish: Gold-plated
- Frequency response: 20–20,000 Hz
- Impedance: 32 Ohm

- Sensitivity: 108 dB
- Sound modus: mono
- Technology: dynamic
- Type: earphone
- Maximum power output: 10 mW

Green specifications

- Compliant to 2002/95/EC (RoHS)
- Lead-free soldered product

Accessories

- Tie clip

Design and finishing

- Colour(s): black/silver

Highlights

Always in place

With the handy clip, the microphone can easily be attached to collars, ties or other clothing. Just plug it into your Digital Pocket Memo or Voice Tracer. No other installation is necessary.

Achieve optimal results

The total Philips solution will produce outstanding results in all situations.

Condenser microphone

The sensitive electret condenser picks up every acoustic detail for perfect sound reproduction and studio quality.

Lightweight solution

Lightweight and easy to attach, this solution is perfect for mobile and stationary use.

Unidirectional design

Recording the speaker's voice only, the unidirectional microphone is ideal for capturing good quality sound and clear voice.

Highly durable

Durable and premium quality materials make the hands-free headset suitable for extended use.



Issue date 2013-01-10

Version: 3.1.8

12 NC: 8735 033 10011
UPC: 0 37849 98402 4

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com