



Philips Pocket Memo  
Meeting recorder

360° recording

POCKET MEMO

LFH0955



## Get your meeting going

Make every meeting a success!

Designed to capture your meetings, the professional meeting recorder provides excellent sound quality combined with easy-to-use technology. The extendibility of components lets the system grow with the needs of your business.

### Supreme user-friendliness

- Easy to use out-of-the-box solution for instant use
- Elegant metal carrying case for portability
- Quick set-up with innovative conference microphones

### Simply smart

- 360-degree sound pick-up for optimal recording
- Innovative meeting microphones for superb recording quality
- Built-in wire storage for adjusting cable length
- Extendable solution for increased recording range

### Designed for professionals

- Automatic file download via USB for quick transcription
- Exchangeable memory card for unlimited recording
- High recording quality in DSS, MP3 and PCM format

# PHILIPS

# Highlights

## Out-of-the-box solution



The Pocket Memo meeting recorder delivers excellent sound quality combined with easy-to-use technology right out of the box.

## Quick set-up

Quick, easy and convenient set up with the innovative meeting microphones.

## DSS, PCM and MP3 recording



The DSS format was developed for use in digital voice recorders, permitting a high compression ratio with little loss of quality while enabling you to store additional information in the file header. The PCM format allows stereo recording in CD-like audio quality and the MP3 format is the common audio format for consumer audio storage, as well as a de facto standard encoding for the transfer and playback of music on digital audio players.

## Exchangeable memory card



Virtually unlimited recording capacity thanks to an exchangeable memory card.

## 360-degree sound pick-up




Sound pick-up from a 360-degree radius for a perfect recording experience.

## Innovative meeting microphones



The innovative boundary layer design of the included meeting microphones uses the sound pressure of the table to provide excellent sound and recording quality with a 360 degree sound-pick up radius.

## Extendable solution




Easily extend the recording range of your Pocket Memo meeting recorder by simply connecting up to six meeting microphones.

## Built-in wire storage



The innovative meeting microphones offer built-in wire storage and length adaption for a clean and tidy conference table.

## Automatic download via USB



When plugged in, the Pocket Memo dictation recorder automatically downloads your audio files directly onto the computer.

## Elegant metal carrying case



The elegant metal carrying case guarantees highest mobility and safe transportation.

# Specifications

## What is included?

- Meeting microphones: 2
- USB docking station
- Click-on interview microphone
- Pocket Memo meeting recorder

## Connectivity

- Headphones: 3.5 mm
- Microphone: 3.5 mm
- USB: High-speed USB 2.0
- Docking connector
- Memory card slot

## Display

- Type: LCD
- Diagonal screen size: 44 mm/1.7 in.
- Backlight: white

## Storage media

- Exchangeable memory card
- Memory card types: Secure Digital (SD), Secure Digital (SDHC)
- Mass storage class compliant

## Audio recording

- Recording formats: Digital speech standard (DSS), MPEG1 layer 3 (MP3), PCM (WAV)
- Built-in microphone: mono
- Recording modes: PCM (WAV/stereo), XHQ (MP3/stereo), HQ (MP3/stereo), QP (DSS/mono), SP (DSS/mono)
- Bit rate: 13.5, 27, 64, 128, 1411 kbps
- Recording time (2 GB card): 349 hours (SP), 170 hours (QP), 72 hours (HQ), 36 hours (XHQ)
- Sample rate: 44.1 kHz (PCM/SHQ), 32 kHz (HQ), 16 kHz (QP), 12 kHz (SP)

## Sound

- Speaker type: built-in round dynamic speaker
- Speaker diameter: 30 mm
- Speaker output power: 200 mW
- Frequency response: 300–8,000 / 50–20,000 (PCM/XHQ), 300–8,000 / 50–15,500 (HQ), 300–7,000 (QP), 300–5,700 (SP) Hz

## Meeting microphone

- Design: boundary layer microphone
- Type: electret condenser microphone
- Impedance: approx. 2.2 kOhm @ 1 kHz
- Sensitivity: -38 dBV
- Frequency response: 30–18,000 Hz
- Phantom supply voltage: 1.5–5 V/0.5 mA
- Connector: 3.5 mm
- Audio jack (for cascading): 3.5 mm
- Cable length: 2 m/6.5 ft.
- Product dimensions (W x D x H): 13 x 13 x 1.8 cm/5.1 x 5.1 x 0.7 in.
- Net weight: 0.108 kg/0.238 lb.

## Clip-on interview microphone

- Connector: 3.5 mm
- Type: electret condenser microphone

- Impedance: approx. 2.2 kOhm @ 1 kHz
- Sensitivity: -42 dBV
- Frequency response: 40–18,000 Hz
- Phantom supply voltage: 1.5–5 V/0.5mA per channel

## Convenience

- Expandable through cascading
- 360 degree sound pick-up
- Control via remote control
- USB powered recording
- Multiple language support: 4 languages
- Author ID setting
- File lock
- Priority setting
- Exchangeable memory card
- Voice-activated recording
- Automatic software updates

## Power

- Battery type: AAA/LR03 Alkaline, Philips AAA Ni-MH LFH9154
- Number of batteries: 2
- Rechargeable: yes, via USB
- Battery lifetime: up to 23 hours in SP recording mode
- Batteries included: rechargeable

## System requirements

- Processor: Pentium III 500 Mhz, Pentium IV 1GHz recommended
- RAM memory: 256 MB (1 GB recommended)
- Hard disk space: 100 MB for SpeechExec, 250MB for Microsoft .NET
- Headphone output or speakers
- Operating system: Windows 7/Vista/XP
- Free USB port
- DVD-ROM drive
- Sound card

## Green specifications

- Compliant to 2002/95/EC (RoHS)
- Lead-free soldered product

## Accessories

- SpeechExec Dictate software
- Click-on interview microphone
- Remote control
- Metal carry case
- USB cable
- Power supply
- Splitter cable
- Secure Digital memory card
- USB dock
- 2 x AAA Ni-MH batteries
- Quick start guide
- User manual
- 2 meeting microphones

## Design and finishing

- Color(s): aluminum
- Material: full metal body



Issue date 2014-02-12

Version: 2.1.2

12 NC: 8735 095 51011  
UPC: 6 05342 03330 5

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)