



Philips Pocket Memo
Meeting recorder

360° recording

POCKET MEMO

LFH0955



Get your meeting going

Make every meeting a success!

Designed to capture your meetings, the professional meeting recorder provides excellent sound quality combined with easy-to-use technology. The extendibility of components lets the system grow with the needs of your business.

Supreme user-friendliness

- Easy to use out-of-the-box solution for instant use
- Elegant metal carrying case for portability
- Quick set-up with innovative conference microphones

Simply smart

- 360-degree sound pick-up for optimal recording
- Innovative meeting microphones for superb recording quality
- Built-in wire storage for adjusting cable length
- Extendable solution for increased recording range

Designed for professionals

- Automatic file download via USB for quick transcription
- Exchangeable memory card for unlimited recording
- High recording quality in DSS, MP3 and PCM format

PHILIPS

Highlights

Out-of-the-box solution



The Pocket Memo meeting recorder delivers excellent sound quality combined with easy-to-use technology right out of the box.

Quick set-up

Quick, easy and convenient set up with the innovative meeting microphones.

DSS, PCM and MP3 recording



The DSS format was developed for use in digital voice recorders, permitting a high compression ratio with little loss of quality while enabling you to store additional information in the file header. The PCM format allows stereo recording in CD-like audio quality and the MP3 format is the common audio format for consumer audio storage, as well as a de facto standard encoding for the transfer and playback of music on digital audio players.

Exchangeable memory card



Virtually unlimited recording capacity thanks to an exchangeable memory card.

360-degree sound pick-up




Sound pick-up from a 360-degree radius for a perfect recording experience.

Innovative meeting microphones



The innovative boundary layer design of the included meeting microphones uses the sound pressure of the table to provide excellent sound and recording quality with a 360 degree sound-pick up radius.

Extendable solution




Easily extend the recording range of your Pocket Memo meeting recorder by simply connecting up to six meeting microphones.

Built-in wire storage



The innovative meeting microphones offer built-in wire storage and length adaption for a clean and tidy conference table.

Automatic download via USB



When plugged in, the Pocket Memo dictation recorder automatically downloads your audio files directly onto the computer.

Elegant metal carrying case



The elegant metal carrying case guarantees highest mobility and safe transportation.

Specifications

What is included?

- Meeting microphones: 2
- USB docking station
- Click-on interview microphone
- Pocket Memo meeting recorder

Connectivity

- Headphones: 3.5 mm
- Microphone: 3.5 mm
- USB: High-speed USB 2.0
- Docking connector
- Memory card slot

Display

- Type: LCD
- Diagonal screen size: 44 mm/1.7 in.
- Backlight: white

Storage media

- Exchangeable memory card
- Memory card types: Secure Digital (SD), Secure Digital (SDHC)
- Mass storage class compliant

Audio recording

- Recording formats: Digital speech standard (DSS), MPEG1 layer 3 (MP3), PCM (WAV)
- Built-in microphone: mono
- Recording modes: PCM (WAV/stereo), XHQ (MP3/stereo), HQ (MP3/stereo), QP (DSS/mono), SP (DSS/mono)
- Bit rate: 13.5, 27, 64, 128, 1411 kbps
- Recording time (2 GB card): 349 hours (SP), 170 hours (QP), 72 hours (HQ), 36 hours (XHQ)
- Sample rate: 44.1 kHz (PCM/SHQ), 32 kHz (HQ), 16 kHz (QP), 12 kHz (SP)

Sound

- Speaker type: built-in round dynamic speaker
- Speaker diameter: 30 mm
- Speaker output power: 200 mW
- Frequency response: 300–8,000 / 50–20,000 (PCM/XHQ), 300–8,000 / 50–15,500 (HQ), 300–7,000 (QP), 300–5,700 (SP) Hz

Meeting microphone

- Design: boundary layer microphone
- Type: electret condenser microphone
- Impedance: approx. 2.2 kOhm @ 1 kHz
- Sensitivity: -38 dBV
- Frequency response: 30–18,000 Hz
- Phantom supply voltage: 1.5–5 V/0.5 mA
- Connector: 3.5 mm
- Audio jack (for cascading): 3.5 mm
- Cable length: 2 m/6.5 ft.
- Product dimensions (W x D x H): 13 x 13 x 1.8 cm/5.1 x 5.1 x 0.7 in.
- Net weight: 0.108 kg/0.238 lb.

Clip-on interview microphone

- Connector: 3.5 mm
- Type: electret condenser microphone

- Impedance: approx. 2.2 kOhm @ 1 kHz
- Sensitivity: -42 dBV
- Frequency response: 40–18,000 Hz
- Phantom supply voltage: 1.5–5 V/0.5mA per channel

Convenience

- Expandable through cascading
- 360 degree sound pick-up
- Control via remote control
- USB powered recording
- Multiple language support: 4 languages
- Author ID setting
- File lock
- Priority setting
- Exchangeable memory card
- Voice-activated recording
- Automatic software updates

Power

- Battery type: AAA/LR03 Alkaline, Philips AAA Ni-MH LFH9154
- Number of batteries: 2
- Rechargeable: yes, via USB
- Battery lifetime: up to 23 hours in SP recording mode
- Batteries included: rechargeable

System requirements

- Processor: Pentium III 500 Mhz, Pentium IV 1GHz recommended
- RAM memory: 256 MB (1 GB recommended)
- Hard disk space: 100 MB for SpeechExec, 250MB for Microsoft .NET
- Headphone output or speakers
- Operating system: Windows 7/Vista/XP
- Free USB port
- DVD-ROM drive
- Sound card

Green specifications

- Compliant to 2002/95/EC (RoHS)
- Lead-free soldered product

Accessories

- SpeechExec Dictate software
- Click-on interview microphone
- Remote control
- Metal carry case
- USB cable
- Power supply
- Splitter cable
- Secure Digital memory card
- USB dock
- 2 x AAA Ni-MH batteries
- Quick start guide
- User manual
- 2 meeting microphones

Design and finishing

- Color(s): aluminum
- Material: full metal body



Issue date 2014-03-14

Version: 2.1.2

12 NC: 8735 095 51011
UPC: 6 05342 03330 5

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com