



Philips Pocket Memo
digital dictation recorder

Slide-switch operation

POCKET MEMO

LFH9380



Get set for digital

Professional dictation with slide switch operation

You grew fond of your tape-based recorder but want to increase efficiency? This is where the Pocket Memo 9380 comes into play. With the professional slide switch you can hold on to your working habits and enhance your dictation workflow.

Quick control

- Slide-switch operation for professional recording control
- Intuitive control with 'Smart buttons'
- Professional editing functions
- Ten individual author IDs for organization of dictations

Easy file handling

- Automatic file download via USB for quick transcription
- Efficient handling of sound files for fast job retrieval
- Job status information allows work to be tracked
- Priority setting for getting urgent jobs processed first

Designed for professionals

- Exchangeable memory card for unlimited recording
- High recording quality in DSS format
- Voice-activation function for hands-free recording

PHILIPS

Highlights

Slide-switch operation



Professional recording control with slide-switch operation.

Professional editing functions




Professional editing functions like overwrite/insert/partial delete/lock available for an optimal workflow.

Intuitive control

Smart buttons let you scroll through menu options and quickly make selections. This makes navigating through the menu to assign work types and other commands fast and intuitive.

Exchangeable memory card



Virtually unlimited recording capacity thanks to an exchangeable memory card.

High recording quality in DSS



The DSS format was developed for the use in digital voice recorders, achieving a high compression ratio with little loss of quality. The DSS format also allows you to store additional information in the file header, which facilitates the organization and the transcription of dictation files.


Track work through job status

The professional SpeechExec software allows you to track your job status information. It grants you a clear view over your work in progress.

Ten individual author IDs

The organisation of your dictations now gets even easier with ten individual author IDs.

Automatic download via USB



When plugged in, the Pocket Memo dictation recorder automatically downloads your audio files directly onto the computer.

Efficient handling

The SpeechExec software enables you to efficiently handle your sound files which makes retrieving your jobs fast, easy and convenient.

Priority setting



With the included priority setting option, urgent recordings get processed first.

Voice-activation function



Voice-activated recording is a convenience feature for hands-free recording. When enabled, recording will start automatically when you start speaking. Recording stop automatically after you stop speaking and restart automatically when you start speaking again.

Specifications

Connectivity

- Headphones: 3.5 mm
- Microphone: 3.5 mm
- USB: High-speed USB 2.0
- Docking connector
- Memory card slot

Display

- Type: LCD
- Diagonal screen size: 44 mm/1.7 in.
- Backlight: white

Storage media

- Exchangeable memory card
- Memory card types: Secure Digital (SD), Secure Digital (SDHC)
- Mass storage class compliant

Audio recording

- Recording formats: Digital speech standard (DSS)
- Built-in microphone: mono
- Recording modes: QP (DSS/mono), SP (DSS/mono)
- Bit rate: 13.5, 27 kbps
- Recording time (2 GB card): 349 hours (SP), 170 hours (QP)
- Sample rate: 16 kHz (QP), 12 kHz (SP)

Sound

- Speaker type: built-in round dynamic speaker
- Speaker diameter: 30 mm
- Speaker output power: 200 mW
- Frequency response: 300–7,000 Hz (QP), 300–5,700 Hz (SP) Hz

Convenience

- Professional editing functions
- Multiple language support: 4 languages (EN, FR, DE, ES)
- 2 smart buttons
- Author ID setting
- Control via slide switch

- File lock
- One-thumb operation
- Priority setting
- Voice-activated recording
- Automatic software updates

Power

- Battery type: AAA/LR03 Alkaline, Philips AAA Ni-MH LFH9154
- Number of batteries: 2
- Rechargeable: yes, via USB
- Battery lifetime: up to 23 hours in SP recording mode
- Batteries included

System requirements

- Processor: Pentium III 500 Mhz, Pentium IV 1GHz recommended
- RAM memory: 256 MB (1 GB recommended)
- Hard disk space: 100 MB for SpeechExec, 250MB for Microsoft .NET
- Headphone output or speakers
- Operating system: Windows 7/Vista/XP
- Free USB port
- DVD-ROM drive
- Sound card

Green specifications

- Compliant to 2002/95/EC (RoHS)
- Lead-free soldered product

Accessories

- SpeechExec Dictate software
- USB cable
- Secure Digital memory card
- Pouch
- Quick start guide
- 2 × AAA batteries

Design and finishing

- Color(s): silver/black
- Material: full metal body



Issue date 2014-02-12

Version: 1.2.4

12 NC: 8735 838 00011
UPC: 0 37849 98794 0

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com