



Philips Pocket Memo
digital dictation recorder
with SpeechExec workflow
software

Slide-switch operation

POCKET MEMO

LFH9380



Get more done in less time

with digital dictation

You grew fond of your tape-based recorder but want to increase efficiency? This is where the Pocket Memo 9380 comes into play. With the professional slide switch you can hold on to your working habits and enhance your dictation workflow.

Superior audio quality

- High recording quality in DSS format
- High-quality built-in microphone for excellent sound quality

Enhance your productivity

- SpeechExec workflow software for easy data management
- Professional editing via slide-switch operation
- Priority setting for getting urgent jobs processed first
- Automatic file download via USB for quick transcription

Designed for professionals

- Exchangeable memory card for unlimited recording
- Lightweight metal body for convenient working
- Direct charging via USB for economical recording
- Voice-activation function for hands-free recording

PHILIPS

Highlights

Exchangeable memory card



Virtually unlimited recording capacity thanks to an exchangeable memory card.

High-quality microphone




The high-quality microphone delivers increased recording sensitivity and excellent sound quality.

Professional editing functions



Easy and fast file editing (insert, overwrite, append) via convenient slide switch.

Automatic download via USB



When plugged in, the Pocket Memo dictation recorder automatically downloads your audio files directly onto the computer.

Lightweight metal body



The ergonomically shaped light weight metal body is ideal for convenient working over longer periods of time.

SpeechExec workflow software



SpeechExec sends your recordings to your assistant for transcription and allows you to monitor the status of your work.

High recording quality in DSS




The DSS format was developed for the use in digital voice recorders, achieving a high compression ratio with little loss of quality. The DSS format also allows you to store additional information in the file header, which facilitates the organization and the transcription of dictation files.

Priority setting



With the included priority setting option, urgent recordings get processed first.

Direct charging via USB



Help protect the environment by simply recharging the batteries of your device using USB instead of buying new batteries.

Specifications

Connectivity

- Headphones: 3.5 mm
- Microphone: 3.5 mm
- USB: High-speed USB 2.0
- Docking connector
- Memory card slot

Display

- Type: LCD
- Diagonal screen size: 44 mm/1.7 in.
- Backlight: white

Storage media

- Exchangeable memory card
- Memory card types: Secure Digital (SD), Secure Digital (SDHC)
- Mass storage class compliant

Audio recording

- Recording formats: Digital speech standard (DSS)
- Built-in microphone: mono
- Recording modes: QP (DSS/mono), SP (DSS/mono)
- Bit rate: 13.5 kbps (SP), 28 kbps (QP)
- Recording time (2 GB card): 349 hours (SP), 170 hours (QP)
- Sample rate: 16 kHz (QP), 12 kHz (SP)

Sound

- Speaker type: built-in round dynamic speaker
- Speaker diameter: 30 mm
- Speaker output power: 200 mW
- Frequency response: 300–7,000 Hz (QP), 300–5,700 Hz (SP) Hz

Convenience

- Professional editing functions
- Multiple language support: 4 languages (EN, FR, DE, ES)
- 2 smart buttons
- Author ID setting
- Control via slide switch
- File lock

- One-thumb operation
- Priority setting
- Voice-activated recording
- Automatic software updates

Power

- Battery type: AAA/LR03 Alkaline, Philips AAA Ni-MH LFH9154
- Number of batteries: 2
- Rechargeable: yes, via USB
- Battery lifetime: up to 23 hours in SP recording mode
- Batteries included

System requirements

- Processor: Pentium IV 1GHz recommended
- RAM memory: 1 GB (2 GB recommended)
- Hard disk space: 100 MB for SpeechExec, 850 MB for Microsoft .NET 4
- Headphone output or speakers
- Operating system: Windows 7 (32/64-bit), Windows Vista (32/64-bit), Windows XP (32 bit)
- Free USB port
- DVD-ROM drive
- Graphics card: DirectX-compliant graphics card with hardware acceleration recommended
- Sound device: Windows-compatible sound device

Green specifications

- Compliant to 2002/95/EC (RoHS)
- Lead-free soldered product

Accessories

- SpeechExec Dictate software
- USB cable
- Secure Digital memory card
- Pouch
- Quick start guide
- 2 × AAA batteries

Design and finishing

- Color(s): silver/black
- Material: full metal body



Issue date 2014-02-13

Version: 3.0.3

12 NC: 8735 938 00111
UPC: 6 09585 20546 8

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com