



Philips Pocket Memo
Dictation and transcription
set

Slide-switch operation

POCKET MEMO

LFH9398

Get set for digital

With professional dictation and transcription

The versatile Digital Starter Kit guarantees high digital recording quality from dictation to transcription. Ergonomically designed hardware with elaborate software makes your dictation workflow as convenient as never before.

Professional recording solution

- Slide-switch operation for professional recording control
- Exchangeable memory card for unlimited recording
- Intuitive control with 'Smart buttons'
- Professional editing functions
- Ten individual author IDs for organization of dictations
- High recording quality in DSS format

Professional transcription solution

- Automatic file download via USB for quick transcription
- Efficient handling of sound files for fast job retrieval
- Ergonomic foot control and headphones for professional use
- Job status information allows work to be tracked
- Priority setting for getting urgent jobs processed first

PHILIPS

Highlights

Slide-switch operation



Professional recording control with slide-switch operation.

Professional editing functions



Professional editing functions like overwrite/insert/partial delete/lock available for an optimal workflow.

Intuitive control

Smart buttons let you scroll through menu options and quickly make selections. This makes navigating through the menu to assign work types and other commands fast and intuitive.

Exchangeable memory card



Virtually unlimited recording capacity thanks to an exchangeable memory card.

High recording quality in DSS



The DSS format was developed for the use in digital voice recorders, achieving a high compression ratio with little loss of quality. The DSS format also allows you to store additional information in the file header, which facilitates the organization and the transcription of dictation files.

Professional transcription

The ergonomic design of the Philips foot control and headphones sets new standards in terms of usability in the professional dictation arena. Transcriptionists can stop and start dictations with only a slight movement of the heel, without lifting the foot unnecessarily, which both increases efficiency and makes the device a pleasure to work with.


Track work through job status

The professional SpeechExec software allows you to track your job status information. It grants you a clear view over your work in progress.

Ten individual author IDs

The organisation of your dictations now gets even easier with ten individual author IDs.

Automatic download via USB



When plugged in, the Pocket Memo dictation recorder automatically downloads your audio files directly onto the computer.

Efficient handling

The SpeechExec software enables you to efficiently handle your sound files which makes retrieving your jobs fast, easy and convenient.

Priority setting



With the included priority setting option, urgent recordings get processed first.

Specifications

What is included?

- Digital recorder LFH9380
- USB foot control
- Stereo headphones LFH0334
- SpeechExec Transcribe software
- SpeechExec Dictate software

Connectivity

- Headphones: 3.5 mm
- Microphone: 3.5 mm
- USB: Mini-USB 2.0
- Docking connector
- Memory card slot

Display

- Type: LCD
- Diagonal screen size: 44 mm/1.7 in.
- Backlight: white

Storage media

- Exchangeable memory card
- Memory card types: Secure Digital (SD), Secure Digital (SDHC)
- Mass storage class compliant

Audio recording

- Recording formats: Digital speech standard (DSS)
- Built-in microphone: mono
- Recording modes: QP (DSS/mono), SP (DSS/mono)
- Bit rate: 13.5, 27 kbps
- Recording time (2 GB card): 349 hours (SP), 170 hours (QP)
- Sample rate: 16 kHz (QP), 12 kHz (SP)

Sound

- Speaker type: built-in round dynamic speaker
- Speaker diameter: 30 mm
- Speaker output power: 200 mW
- Frequency response: 300–7,000 Hz (QP), 300–5,700 Hz (SP) Hz

Convenience

- Professional editing functions
- Multiple language support: 4 languages (EN, FR, DE, ES)
- 2 smart buttons
- Author ID setting
- Control via slide switch
- File lock
- One-thumb operation
- Priority setting
- Voice-activated recording
- Automatic software updates

Power

- Battery type: AAA/LR03 Alkaline, Philips AAA Ni-MH LFH9154
- Number of batteries: 2

- Rechargeable: yes, via USB
- Battery lifetime: up to 23 hours in SP recording mode
- Batteries included

Foot pedal

- Connectivity: USB plug
- Product dimensions (W × H × D): 19.5 × 13 × 3.5 cm/7.7 × 5.1 × 1.4 in.
- Weight: 0.660 kg/1.5 lb.

Headphones

- Style: under chin
- Acoustic system: open
- Magnet type: neodymium
- Diaphragm: PET dome
- Voice coil: copper
- Sound quality: optimized for voice playback
- Impedance: 2 × 32 Ohm
- Maximum power input: 2 × 10 mW
- Sensitivity: 103 dB
- Speaker diameter: 14 mm/0.6 in.
- Cable connection: one-sided
- Cable length: 3.0 m/10 ft.
- Connector: 3.5 mm, right angled, stereo
- Connector finish: gold-plated
- Product dimensions (W × H × D): 16 × 15 × 1.8 cm/6.3 × 5.9 × 0.7 in.
- Weight: 0.660 kg/1.5 lb.

System requirements

- Processor: Pentium III 500 Mhz, Pentium IV 1GHz recommended
- RAM memory: 256 MB (1 GB recommended)
- Hard disk space: 100 MB for SpeechExec, 250MB for Microsoft .NET
- Headphone output or speakers
- Operating system: Windows 7/Vista/XP
- Free USB port
- DVD-ROM drive
- Sound card

Green specifications

- Compliant to 2002/95/EC (RoHS)
- Lead-free soldered product

Accessories

- SpeechExec Dictate software
- SpeechExec Transcribe software
- USB cable
- Secure Digital memory card
- Pouch
- Quick start guide
- 2 × AAA batteries

Design and finishing

- Color(s): silver/black
- Material: full metal body



Issue date 2016-03-16

Version: 1.2.4

12 NC: 8735 939 80011
UPC: 0 37849 98792 6

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com