



Philips LED Inspection lamps
RCH20 Rechargeable Lamp with Docking

High Quality LED

200 lm
360° Retractable Hook and Magnet
Compact design



LPL13X1

See better, work better

Cordless compact professional lighting tool

The rechargeable Philips LED inspection lamp with docking station is the cordless professional lighting tool. Its strip LED gives a strong and homogeneous beam that illuminates every area abundantly.

High-power compact white LED light

- Defeat the darkness with soft natural light
- Wide beam angle: up to 70°
- High-power LED light up to 200 lumens

High resistance

- Strong impact resistance -IK07
- Water and dust protected -IP65
- Resistant to chemicals and workshop solvents

Hands-free lighting

- 360° versatile clipping and magnet hook

PHILIPS

Specifications

Outer Carton

- Number of consumer packages: 6
- Outer carton (L x W x H): 26.9 x 16.5 x 12.1 cm
- Gross weight: 1.19 kg
- GTIN: 1 87 27900 38948 4

Ordering information

- Order entry: LPL13X1
- Ordering code: 38948731

Electrical characteristics

- Battery charging time: 4 hrs
- Battery run time: Up to 3 hours
- Battery type: Li-Ion
- Plug type: UK
- Power source: Rechargeable
- Voltage: 100–240 V
- Wattage: 2.4 W

Light characteristics

- Beam angle: 70 degree
- Colour temperature: 6000 K K
- LED lifetime: 10,000 hrs
- Light intensity (Boost): 350 lux at 0.5 m
- Light output: 200 lumen

Outer pack information

- Gross weight per piece: 2870 g

- Height: 17.3 cm
- Length: 28.9 cm
- Width: 26.9 cm

Packaging Data

- EAN1: 8727900389487
- EAN3: 8727900389470

Packed product information


- Height: 3.8 cm
- Length: 19 cm
- Pack Quantity / MOQ: 6
- Weight with batteries: 360 g
- Width: 6.3 cm
- Weight without batteries: 210 g

Product description

- Hook: Versatile clip hook
- Impact protection rating (IK): IK07
- Ingress protection rating (IP): IP65
- Magnet
- Materials and finishing: Robust rubber and polycarbonate
- Number of LEDs: 1
- Operating Temperature: -10 to 40 °C
- Resistant to: grease, oil, workshop solvents
- Technology: LED
- Range: RCH

Highlights

Wide beam angle



The wide beam angle of 70° will enable you to focus on specific parts and to deliver the right amount of light you need.

Water and dust protected -IP65



The LED inspection lamp is water resistant and conforms to IP65.

Strong impact resistance -IK07



Strong impact resistance -IK07

Resistant to chemicals

As well as resisting knocks, the inspection lamp cases are resistant to water, chemicals and workshop solvents.

360° versatile clip and magnet

The adjustable, retractable, multi-angle hook allows you to hang this professional lighting tool on any surface, leaving both your hands free for the job.

High-power LED light

The high-power white LEDs provide 200 lumens of light output to ensure that you are not left in the dark when trying to spot even the smallest details.

Defeat the darkness

Philips professional workshop lamps feature powerful LEDs for an intense white light and a bright wide beam to defeat the darkness. Designed to optimise clarity and vision, the 6000 K white light also improves visual comfort for fatigue-free working.



Issue date 2016-12-26

Version: 6.1.4

12 NC: 9237 956 30202
EAN: 87 27900 38948 7

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com