

PHILIPS

Penlight Compact
Lamp

LED Inspection
lamps

High Quality LED x 5

85 lm +20 lm pointer

Up to 8 h Autonomy

Powered with 3 AAA batteries



LPL18B1



See better, work better

Portable inspection tool

The Philips LED Inspection lamp Penlight is the perfect tool for quick inspection work, combining high-quality LEDs and user-friendliness in a small form factor.

Brighter and longer lasting

- High-quality LED light up to 85 lumens
- Defeat the darkness with soft natural light
- Focus light: 20 lm

High resistance

- drop test: 12 times free drop from 1.5 m

Highlights

Focus light: 20 lm

The focus light will enable you to see what remains hidden for others; thanks to its ultra-slim design, the lamp can be manoeuvred into very small cavities and the strong LED source will illuminate all.

drop test: 12 times free drop



drop test: 12 times free drop from 1.5 m.

High quality LED light



As the international market leader in car lighting, we have years of experience and know-how in light. Philips LED inspection lamps are equipped with high-quality LEDs. Our LEDs combine strong light performance with natural colour rendering for fatigue-free work.

Defeat the darkness

Philips professional workshop lamps feature powerful LEDs for an intense white light and a bright wide beam to defeat the darkness. Designed to optimise clarity and vision, the 6000 K white light also improves visual comfort for fatigue-free working.

Specifications

Outer Carton

Number of consumer packages: 20
Outer carton (L x W x H): 29.8 x 18.6 x 26 cm
Gross weight: 1.9 kg
GTIN: 1 87 27900 38821 0

Ordering information

Order entry: LPL18B1
Ordering code: 38821340

Electrical characteristics

Battery run time: Up to 8 hours
Battery type: 3 x AAA
Power source: Battery
Voltage: 4.5 V
Wattage: 1.6 W

Light characteristics

Colour temperature: Up to 6000 K
LED lifetime: 10,000 hrs
Light output: 85 lumen
Light output (pointer): 20 lumen

Outer pack information

Gross weight per piece: 1515 g
Height: 26 cm
Length: 29.5 cm
Width: 18.6 cm

Packaging Data

EAN1: 8727900388213
EAN3: 8727900388220

Packed product information

Height: 3.3 cm
Length: 17.2 cm
Pack Quantity / MOQ: 20
Weight with batteries: 80 g
Width: 1.8 cm
Weight without batteries: 47 g
Size: Compact

Product description

Hook: Standard clip
Magnet: No
Number of LEDs: 6
Operating Temperature: 0 to 40 °C
Technology: LED
Range: Penlight

