

PHILIPS

Penlight Premium Gen2
Rechargeable Light

LED Inspection lamps

High Quality LED

145 lm + 120 lm pointer

Robust Aluminium Housing

Rechargeable with USB

LPL28RECHX1



See better, work better

Compact, USB-rechargeable LED worker's companion

Philips Penlight Premium Gen2 offers an unprecedented combination of high-quality light in both an inspection and pointer light, with new aluminium housing and chemical/water/dust-resistance in one slim pen. A real all-in-one choice!

See what remains hidden for others

- Powerful focus light: 120 lumens
- High quality LED light up to 145 lm
- Wide beam angle: up to 90°
- Defeat the darkness with soft natural light

Hands-free lighting

- Ready for use within two hours
- 80° swivel hook with magnet

Never lose your lamp again

- Improved colour scheme for easy relocation

High resistance

- Strong impact resistance -IK07
- Resistant to chemicals and workshop solvents
- Water and dust-protected -IP54

Highlights

Strong impact resistance -IK07



Strong impact resistance -IK07

Resistant to chemicals

As well as resisting knocks, the inspection lamp cases are resistant to water, chemicals and workshop solvents.

Wide beam angle

"Philips Penlight Premium Gen2 has a beam angle of up to 90°, illuminating a large area to make your quick inspections more simple."

Focus light: 120 lumens

Annoyed by the low quality of focus light? Don't worry. The upgraded Penlight Premium Gen2 pointer offers a powerful 120 lm of focus light that enables you to see what remains hidden for others. Thanks to its ultra-slim design, Philips Penlight Gen2 can be manoeuvred through very small spaces, and its strong LED source will illuminate everything.

High quality LED light

Don't miss out! Small and energetic, Philips Penlight Premium Gen2 provides an amazing light output of 145 lm with its high-quality white LEDs. This slim companion ensures that you are not left in the dark when trying to spot even the smallest details.

Water and dust-protected

Philips Penlight Premium Gen2 conforms to the IP54 standard. This slim inspection tool is fully protected against water, humidity and dust from both inside and outside of your workshop.

Fast-charging battery

Philips Penlight Premium Gen2 is the only compact tool which is equipped with a fast-charging battery. Your pen tool is charged in 2 hours and ready for up to 6 hours of work. Philips Penlight Premium Gen2, your reliable hard-working tool companion which only needs a small recharge each day.

Hands-free for work

With the 80° swivel hook with magnet, you can place this penlight on any surface, leaving your hands free to do your work.

Never lose your light again

"Thanks to its new colour scheme, the light has an improved visual design and can be spotted more easily. You'll never need to worry about losing your best inspection pen tool ever again!"

Defeat the darkness

Philips Penlight Premium Gen2 features powerful LEDs for an intense white light and a bright wide beam to defeat darkness. The wide beam of bright light is distributed evenly over the illuminated area, giving you the best possible overview and lighting up every detail with pinpoint precision. With a colour temperature of 6000 K, our LEDs produce a natural white light that's easy on the eye, improving visual comfort and reducing eye strain for fatigue-free working.

Specifications

Outer Carton

Number of consumer packages: 4
Gross weight: 1.344 kg
GTIN: 1 87 27900 39220 0

Ordering information

Order entry: LPL28RECHX1
Ordering code: 39220394

Electrical characteristics

Battery capacity: 1200 mAh
Battery charging time: 2 hrs
Battery run time: Up to 6 hours
Battery type: Lithium
Charging cable type: Micro-USB port
Plug type: EU
Power source: Rechargeable
Voltage: 100–240 V
Wattage: 5 W

Light characteristics

Beam angle: 80 degree
Beam angle (pointer): 15 degree
Colour temperature: 6000 K
LED lifetime: Up to 10,000 hrs
Light output: 145 lumen
Light output (pointer): 120 lumen

Outer pack information

Gross weight per piece: 1344 g

Packaging Data

EAN1: 8727900392203
EAN3: 8727900392210

Packed product information

Pack Quantity / MOQ: 4
Weight with batteries: 107 g
Size: Compact

Product description

Hook: 80° swivel clip
Impact protection rating (IK): IK07
Ingress protection rating (IP): IP54
Magnet
Materials and finishing: Robust metal housing
Number of LEDs: 5
Operating Temperature: -10 to 50 °C
Resistant to: grease, oil, workshop solvents
Technology: LED
Range: Penlight

