

PHILIPS

CBL10 Cabled Lamp

LED Inspection
lamps

High Quality LED

330 lm

5 metre cable

360° Retractable Hook



LPL35X1



See better, work better

Cabled and compact professional lighting tool

Our compact, cabled LED professional work light has been designed for all maintenance jobs. Its powerful LEDs give a strong and homogenous 330 lumen beam, while its 360° rotating hook provides a hands-free working environment.

High quality white LED light

- Defeat the darkness with soft natural light
- High quality LED light: 330 lm
- Wide beam angle: up to 120°

High resistance

- Resistant to chemicals and workshop solvents
- Strong impact resistance -IK07
- Water and dust protected -IP54

Compact and hands-free lighting

- 5 m cable and 360° retractable hook

Highlights

Resistant to chemicals

As well as resisting knocks, the inspection lamp cases are resistant to water, chemicals and workshop solvents.

Defeat the darkness

Philips professional workshop lamps feature powerful LEDs for an intense white light and a bright wide beam to defeat the darkness. Designed to optimise clarity and vision, the 6000 K white light also improves visual comfort for fatigue-free working.

Strong impact resistance -IK07

Strong impact resistance -IK07

5 m cable and rotating hook

The 360° adjustable and retractable hook, along with a 5-metre cable, makes it possible to hang this LED inspection lamp on any surface, leaving both of your hands free for the job.

High quality LED light

The high quality white LEDs provide 330 lm of light output to ensure that you are not left in the dark when trying to spot even the smallest details.

Wide beam angle: up to 120°

With a wide beam angle of 120°, this LED inspection lamp will enable you to focus on a specific part and deliver the right amount of light that you need.

Water and dust protected -IP54

Our CBL10 LED inspection lamp is water-resistant and dust-resistant and conforms to IP54 standard.

Specifications

Ordering information

Order entry: LPL35X1

Ordering code: 39421431

Electrical characteristics

Charging cable type: 220 V AC plug-in power supply

Plug type: EU

Power source: Cable

Voltage: 100–240 V

Wattage: 5 W

Light characteristics

Beam angle: 120 degree

Colour temperature: 6000 K

LED lifetime: Up to 10,000 hrs

Light output: 330 lumen

Packaging Data

EAN1: 8727900394214

EAN3: 8727900394221

Packed product information

Cable length: 5 m

Height: 6 cm

Length: 39.7 cm

Pack Quantity / MOQ: 6

Weight with cable: 545 g

Weight without cable: 195 g

Width: 10.2 cm

Size: Compact

Product description

Hook: 360° retractable hook

Impact protection rating (IK): IK07

Ingress protection rating (IP): IP54

Magnet: No

Materials and finishing: Robust rubber and polycarbonate

Number of LEDs: 12

Operating Temperature: -10 to 50 °C

Resistant to: grease, oil, workshop solvents

Technology: LED

Range: CBL

Power consumption

Energy efficiency label: A+

Power consumption per 1000h: 3.5 kW·h

