

PHILIPS

10 Double Row LED Lightbar

Ultinon Drive 5015L

Sturdy one-piece body
IP69K waterproof
Corrosion-free stainless steel
Trouble-free operation



LUMUD5015LX1

Brilliant LED lighting for off-road adventures Built for where you want to go

For drivers who demand the maximum of themselves and their machines, we offer Philips Ultinon Drive 5000 series LED lightbars. Exceptionally rugged, with unsurpassed illumination and beam focus, that can light the way.

Powerful brightness, Rugged performance

- Bright, long beam for superior visibility

Durable equipment for challenging conditions

- Sturdy one-piece body for tough environments
- IP69K waterproof to master the elements
- Corrosion-free, stainless-steel mounting brackets

Off-road auxiliary lights

- Trouble-free operation

Highlights

Superior visibility

The Philips Ultinon Drive 5000 series provides outstanding beam performance with brilliant illumination that extends up to 423 yards. With high lumen output coming from the powerful LEDs, the Ultinon Drive series provides ample visibility for faster reactions. Cool light color of 6500 Kelvin keep you focused without straining your eyes.

Sturdy one-piece body

Philips Ultinon Drive 5000 series lightbars are built with single-piece assemblies to withstand the toughest conditions. This also allows for excellent heat management and consistently high light output throughout your journey. Ultinon Drive 5000 series has an impact protection rating of IK07, to ensure it can withstand the hazards of aggressive offroading. Rugged polycarbonate lenses resist damage and scratches and the convenient DT connector guarantees a perfect connection.

Waterproof for durable light

With its ingenious screwless design, the Ultinon Drive 5000 series is rated IP68 and IP69K against dust, high temperature, and high pressure water. These lights will perform, wherever your road leads and whatever the weather. And they will be more than a match for any powerwasher you use to clean your ride after your adventures.

Corrosion-free brackets

Ultinon Drive 5000 series mounting brackets are made of highly corrosion resistant stainless steel. Built to withstand years of exposure in snow, ice, and salt air environments, these brackets and the entire lightbar will provide years of reliable service.

Trouble-free

Philips Ultinon Drive 5000 series lightbars are designed and tested to ensure they will function smoothly with your vehicle's electrical systems. They will not create electrical interference that might interfere with other vehicle functions.

Specifications

Electrical characteristics

Voltage: 9-30 Volt DC

Product description

Accessories (optional): additional wiring kit

Impact protection rating (IK): IK07

Ingress protection rating (IP): IP68 & IP69K

One-piece body design

Range: Ultinon Drive 5000

Scratch resistant lens

Technology: LED

corrosion-free brackets: yes, included

Heat sink: 13-piece .06 in

Material: Aluminum die-cast

Operating Temperature: -40° F to 176° F

Light characteristics

Color temperature: 6500 K K

Effective lumen output: 3500 lumens

Ordering information

GOC: 78002637

Order entry: UD5015LX1

Packaging Data

EAN1: 46678002632

EAN3: 50046678002637

