

PHILIPS

Xperion 6000 UV Pillar

Work light

500 lm Boost / 250 lm Eco

180 lm Spotlight + UV

Battery life: 4,5h (Eco: 10h)

High CRI and UV leak-detector



LUMX60UVPIX1

Preliminary



Designed with you in mind

Advanced lighting performance that lasts

Our premium work light, the Philips Xperion 6000 UV Pillar, is a multi-purpose work light with several powerful light sources, UV light, high CRI, and long-lasting battery.

See where others can't

- Premium LED light with multiple outputs
- Spot leaks with UV light
- Reveals objects in their true colors (CRI95)
- Long running time in different light modes

Smart, ergonomic design

- Smart rotatable hook with magnet and ergonomic body
- Easily retrieve your device

Handles tough conditions easily


- Resistant to impacts, water and solvents (IP65/IK07)

Accessories available to upgrade your work lamp

- Smart solutions for charging your device

Highlights

Multiple light modes



The premium, homogenous LED illuminates with 100% reliability, ideal for multiple uses. It helps you see clearly in dark environments, easily revealing discoloration and damaged components. The Philips Xperion 6000 UV Pillar is a top-quality, trustworthy light for all types of inspection and repair work.

Unique UV leak-detector



This premium work lamp comes with an additional UV light to help you easily spot leakages. Direct the UV light over any area to identify where leak repairs are necessary. The Philips Xperion 6000 UV Pillar has all your illumination needs covered.

Reveal colors accurately



The higher the Color Rendering Index (CRI), the easier it is to perform a quick and accurate inspection of car bodywork. You can inspect your paint, polish, clean, or prep zone as if you were working outdoors on a bright sunny day. Lamps with a low CRI value cause some colors to appear unnatural. Light

sources with a CRI of 90 or above will let you easily and quickly spot color differences such as paint scratches.

Light modes for multiple needs



The Philips Xperion 6000 UV Pillar is designed to be ready for action. A single charge provides enough energy for a full day's work: up to 10 hours in Eco mode, 4,5 hours in Boost mode, and 12 hours with the torch beam. Powered by a powerful Li-ion battery, the Philips Xperion 6000 UV Pillar can be fully charged within 4,5 hours via USB-C, ensuring maximum usage of its bright LED light.

Enables hands-free working



Designed with you in mind, the ergonomically shaped handle with anti-slip coating allows you to hold this work light securely. If you need both hands free for work, position the light securely thanks to the 360° rotatable, retractable hook and a strong magnet. The power button is located on the back to ensure the light does not glare directly at your eyes when you turn it on.

Designed for resistance



Designed to handle tough work environments with IK07 shock resistance, water-resistant to IP65 standards, and a surface to withstand chemicals and workshop solvents, the Philips Xperion 6000 UV Pillar is built to last because we know that even the steadiest hands need the extra support.

Upgrade your work light



To keep your work light to hand and ready to use, try the Philips Dock station. Placed on a table, it provides cordless charging for your lamp. Find out more: [Philips.com/Xperion-6000](https://www.philips.com/Xperion-6000)

"Find My Device" function



Don't worry about losing your device anymore. You can find it easily with the "Find My Device" function. Use the remote control to trigger an audible buzzer and flashing light to locate your device. The lime-green body will help you spot your device even in dark settings.

Specifications

Electrical characteristics

Battery charging time: Up to 4.5 hours
Battery run time (boost): Up to 4,5 hours
Battery run time (eco): Up to 10 hours
Battery run time (Pointer): Up to 12 hrs
Battery type: Lithium battery
Charging cable type: Type C USB
Voltage: 3.7 V
Wattage: 5W
Power source: Rechargeable battery

Light characteristics

Beam angle: 100 degree
Beam angle (pointer): 15°
Color temperature: 6000 K

Light output (boost): 500 lumens
Light output (eco): 250 lumens
Light output (pointer): 180 lumens

Marketing specifications

Expected benefits: Designed with you in mind
Product highlight: High CRI and UV leak-detector

Ordering information

Order entry: X60UVPIX1
Ordering code: 78002170

Packaging Data

EAN1: 46678002175
EAN3: 50046678002170

Product description

Hands free options: Rotatable hook, strong magnet
Hook: 360° rotatable
Impact protection rating (IK): IK07
Magnet: 2 magnets
Materials & finishing: Robust ABS + Soft rubber
Range: Xperion 6000
Resistant to: Grease, oil, workshop solvents
Technology: COB LED
UV leak detector
Ingress protection rating (IP): IP65

