

## MAS139

### Magnavox Audio

Set your sights on the attractive MAS139 Mini Hi-Fi System, which delivers superbly rich sound. You'll appreciate how easy it is to operate and control, just sit back, relax and enjoy your music all day, your way!

- **2x15W RMS / 1200W PMPO**
- **Full range Bass Reflex Speaker System**
- **Play CD, CD-R and CD-RW discs**
- **AM/ FM tuner for radio enjoyment**
- **Stereo cassette deck**
- **Dynamic Bass Boost for deep and dramatic sound**
- **Digital Sound Control for optimized music style settings**



## MAS139/78 Magnavox Audio

### Product specifications

#### Sound

- Output power (RMS): 2x15W RMS / 1200W PMPO
- Sound Enhancement: Dynamic Bass Boost, Digital Sound Control

#### Loudspeakers

- Main Speaker: 4" woofer, Full range, Bass Reflex Speaker System
- Number of Loudspeakers: 2

#### Audio Playback

- Loader Type: Tray
- Number of Discs: 1
- Playback Media: CD, CD-R, CD-RW
- Disc Playback Modes: Fast Forward/Backward, Next/Previous Track Search, Repeat Play, Shuffle Play
- Programmable Tracks: 20
- Cassette Deck Technology: Mechanical
- Number of decks: 1

#### Audio Recording

- Recording Media: Tape
- Tape Recording Enhancement: CD Synchro Start Recording

#### Tuner/Reception/Transmission

- Tuner Bands: FM, FM Stereo, MW

#### Connectivity

- Headphone: 2.5 mm
- Other connections: AUX in

#### Convenience

- Display Type: LCD
- Clock: On main display
- Alarms: CD Alarm, Radio Alarm, Sleep timer

#### Accessories

- Remote control: 20-key
- User Manual: English, Brazilian-Portuguese, Spanish
- Included accessories: Quick Use Guide

#### Dimensions

- Set dimensions (W x H x D): 220 x 292 x 285 mm
- Speaker Width: 182 mm
- Speaker Height: 292 mm
- Speaker Depth: 190 mm
- Packaging dimensions (W x H x D): 510 x 350 x 416 mm
- Weight incl. Packaging: 9.3Kg kg

#### Power

- Power supply: 100-240VAC, 50/60Hz

### 2x15W RMS / 1200W PMPO

#### Full range Bass Reflex Speaker

Bass Reflex Speakers delivers a deep bass experience. Differ from conventional loudspeakers, the addition of a bass pipe that is acoustically aligned to the woofer optimizes the low frequency roll-off. The result is a deep controlled bass and low distortion. Combined with the response of the woofer, it extends the overall low frequency sounds to create a whole new dimension of deep bass.

#### Play CDs, CD-R and CD-RW

Philips is known for making products which are compatible with many discs available in the market. This audio system lets you enjoy music from CD, CD-R and CD-RW. CD-RW (CD-Rewritable Compatible) means that your audio system can play both CD-Recordable (CD-R) and CD-Rewritable (CD-RW) discs. CD-R discs are recordable once and can be played on any audio CD player while CD-RW discs can be recorded and rewritten multiple times and can only be played back on compatible audio CD players.

#### AM/ FM tuner

#### Stereo cassette deck

#### Dynamic Bass Boost

Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

#### Digital Sound Control

Digital Sound Control offers you a choice of pre-set Jazz, Rock, Pop and Classic controls you can use to optimise the frequency ranges for different musical styles. Each mode uses graphic equalizing technology to automatically adjust the sound balance and enhance the most important sound frequencies in your chosen music style. Ultimately, Digital Sound Control makes it easy for you get the most out of your music by precisely adjusting the sound balance to match the type of music you are playing.