


Digital Power Amplifier



Micro HIFI System with 3 CD Changer

- 2500 watts PMPO + 1250 watts PMPO Acoustic Bass Energy
- 2 x 160 watts Music Power + 160 watts Acoustic Bass Energy
- 2 x 80 watts RMS Stereo + 80 watts Acoustic Bass Energy
- wOOx Technology Speaker System for deeper bass
- Incredible Surround™
- Treble & Bass Control
- 2 way Bass Reflex Speaker System with Detachable grilles
- Flat metal cone woofers for greater sound clarity
- FM/MW/LW Digital Tuning with 40 presets (LW /22 only)
- RDS including 'NEWS' (/22)
- Plug and Play for easy installation of radio stations
- Logic tape deck with Auto Reverse
- Digital out for perfect CD recording
- Subwoofer out
- Bedroom Clock with Wake-up Alarm and Sleep-Timer
- Eco power standby (<1 watt)
- 35-key Remote Control



Let's make things better.



PHILIPS



Micro HI-FI System with 3 CD Changer

standard product information

amplifier

- 2500 watts PMPO + 1250 watts PMPO Acoustic Bass Energy
- 2 x 160 watts Music Power + 160 watts Acoustic Bass Energy
- 2 x 80 watts RMS Stereo + 80 watts Acoustic Bass Energy
- 3 level wOOx Dynamic Amplification Control
- Incredible Surround™
- Bass and Treble control
- Signal depth bass control

compact disc player

- 3 CD Changer - Change 2 discs while playing 1
- Plays CD, CD-R and CD-RW discs
- 40-Track CD Random Program
- CD repeat (track/disc/all)
- Play modes (repeat/shuffle/program)

tuner

- FM/MW/LW Digital Tuning with 40 presets (LW /22 only)
- Plug and play for easy installation of radio stations
- RDS station name, programme type, RDS text, clock set, 'NEWS'

tape deck

- Full Logic Tape Deck
- Auto Reverse
- Automatic recording level control
- CD synchro recording

loudspeaker boxes

- 2 way Bass Reflex speaker system
- 5.25" woofer
- Cone dome tweeter
- 5" Top firing wOOx bass radiator
- Detachable Grilles
- Wood style finish


connections

- Stereo headphones : 3.5mm stereo jack
- Aux : cinch socket
- Digital out : cinch socket
- Subwoofer out : cinch socket

general

- 3 display modes including dim mode
- Demo mode
- 2 timer modes (wake-up/sleep)
- Wake-up with CD or Tape deck
- 35-key Remote Control
- Clock/Timer
- Eco power standby mode (<1 watt)

	/21	/21M	/22	/29	/30	/33	/34
AP/Middle East/Africa			•				
Australia/NZ							
Korea						•	
Latam	•						
W Europe				•			
E Europe							
tuner							
FM87.5-108MHz	•	•	•				•
MW522-1602kHz	•	•	•				•
LW153-279kHz							
FM75 Ohm coaxial	•	•	•				•
mains supply							
120/230V 50-60Hz	•	•					
230V/50Hz				•			•
general							
made in sticker	•	•					•



EAN: 87 10895 71922 3 (/21)
 EAN: 87 10895 71924 7 (/21M)
 EAN: 87 10895 71923 0 (/22)
 EAN: 87 10895 72803 4 (/33)

Product Dimensions:
 175 mm W x 244 mm H x 322 mm D (center unit)
 130 mm W x 264 mm H x 215 mm D (speakers)

Package Dimensions:
 524 mm W x 363 mm H x 416 mm D
 Product weight: 12.5 kg

Carton contains: 3 CD Micro System, Multi-Function Remote Control, Batteries (2 x AA), Operating instructions, Warranty information, FM antenna, AM antenna

Printed in Singapore
 Date Printed : June 2001
 Specifications subject to change without notice.
 © 2001 Royal Philips Electronics N.V.
 All rights reserved.

Incredible Surround™ is a Trademark of Philips Consumer Electronics Company

<http://www.audio.philips.com>

Let's make things better.



PHILIPS