

Philips  
Micro Hi-Fi System



MC147

## Obsessed with sound

Relax with great music

Tune in to superb sound from a surprisingly compact design. The Philips micro hi-fi system will enhance your living space while enriching your music listening experience. Just press Play to enjoy room-filling, dynamic bass sounds.

### **Enrich your sound experience**

- Play CD, CD-R and CD-RW
- Dynamic Bass Boost for deep and dramatic sound
- Autostop cassette deck
- 4W RMS total output power

### **Start the day your way**

- Wake up and sleep timer functions
- Digital tuning with preset stations for extra convenience

### **Fits any space, any lifestyle**

- Handy remote control for extra convenience

# PHILIPS

# Highlights

## Play CD, CD-R and CD-RW




Philips is known for making products which are compatible with many discs available in the market. This audio system lets you enjoy music from CD, CD-R and CD-RW. CD-RW (CD-Rewritable Compatible) means that your audio system can play both CD-Recordable (CD-R) and CD-Rewritable (CD-RW) discs. CD-R discs are recordable once and can be played on any audio CD player while CD-RW discs can be recorded and rewritten multiple times and can only be played back on compatible audio CD players.

## Dynamic Bass Boost



Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high – at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

## Autostop cassette deck



Autostop cassette deck

## 4W RMS



This system has 4W RMS total output power. RMS refers to Root Mean Square which is a typical measurement of audio power, or rather, the electrical power transferred from an audio amplifier to a loudspeaker, which is measured in watts. The amount of electrical power delivered to the loudspeaker and its sensitivity determines the sound power that is generated. The higher the wattage, the better the sound power emitted by the speaker.

## Wake up and sleep timer



Many of alarm clocks feature a variety of alarm choices. This Philips Clock radio awakens you to radio or the traditional alarm buzzer. The

Sleep Timer allows you to program the required length of time for music to coincide with how long you normally take to fall asleep. No matter what your alarm clock needs, whether it's a morning buzzer that produces a steady tone, or listening to your favorite music as you go to sleep, this clock radio has it all.

## Digital tuning with presets



Simply tune into the station that you want to preset, press and hold the preset button to memorize the frequency. With preset radio stations that can be stored, you can quickly access your favorite radio station without having to manually tune the frequencies each time.

## Handy remote control



With a handy remote control for greater convenience at your fingertips, all you have to do is sit back and relax.



# Specifications

## Sound

- Output power: 2 x 2 W RMS
- Volume control: up/down
- Sound enhancement: Dynamic Bass Boost

## Loudspeakers

- Speaker drivers: 3" woofer

## Audio playback

- Playback media: CD, CD-R, CD-RW
- Disc playback modes: repeat/shuffle/program
- Cassette deck technology: mechanical

## Audio recording

- Recording media: tape
- Tape recording enhancement: CD synchro start recording

## Tuner/Reception/Transmission

- Tuner bands: FM stereo, MW
- Station presets: 20
- Antenna: FM fixed pigtail antenna, MW antenna
- Tuner enhancement: auto digital tuning

## Connectivity

- Audio/Video output: Headphone (3.5mm)
- MP3 Link: 3.5mm stereo line in

## Convenience

- Loader type: top
- Clock: on main display, sleep timer
- Display type: LCD display
- Backlight color: blue

## Accessories

- Remote control
- Others: FM/MW antenna, User Manual
- Warranty: World Wide Guarantee booklet

## Dimensions

- Gross weight: 4.75 kg
- Main speaker dimensions (W x D): 134 x 152 mm
- Main speaker height: 230 mm
- Main unit depth: 216 mm
- Packaging width: 370 mm
- Main unit height: 233 mm
- Packaging height: 270 mm
- Main unit width: 148 mm
- Packaging depth: 326 mm



Issue date 2014-02-11

Version: 1.0.3

12 NC: 8670 000 33206  
EAN: 87 12581 35833 4

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)