

Compact audio system

MC165

## Compact audio system

- **Contemporary design**

A combination of bright anodised aluminium and clear lacquered MDF on the loudspeakers give a fresh and light appearance blending in smoothly with a modern interior design.

- **Incredible surround**

Feature unique to Philips that creates the illusion of the speakers being much further apart than they actually are, resulting in an enhanced, room-filled stereo effect.

- **Dynamic bass boost**

Enhances bass tone frequencies to give deep, rich sounds.

- **Digital sound control (optimal, jazz, classic, pop)**

- **Bass reflex speaker system**

- **Digital tuner with 30 presets**

- **RDS Radio data system with news function (Europe only)**

- **Clock/timer with sleep function**

- **Remote control with mute function**

- **CD Rewritable compatible**



Let's make things better.



PHILIPS

**Standard product information****Amplifier**

- 2 x 18W RMS,  $\pm 10\%$  THD, 4 Ohm, 1 KHz
- 2 x 36W music power
- Incredible surround
- Digital sound control (optimal, jazz, classic, pop)
- Dynamic bass boost
- Volume control with 50 steps encoder
- Mute function

**CD player**

- Motorised front loading
- Digital servo technology
- Bit-check D/A convertor
- 20 track CD random programme
- Play mode (repeat/shuffle/programme)
- CD rewritable compatible

**Tuner**

- LW/MW/FM stereo digital tuner with 30 presets (LW europe only)
- RDS - station name, programme type, RDS text, clock set and news (europe only)
- Autostore

**Loudspeaker boxes**

- Bass reflex system
- 3" Specially designed woofer
- Detachable speaker grilles
- Click-fit connectors

**Connections**

- Stereo headphone : 3.5 mm stereo jack
- Aux in : cinch type sockets
- Loudspeakers : click-fit connections
- Antenna : FM coaxial socket 75 $\Omega$   
AM JST2pM
- Subwoofer output : cinch type socket for active subwoofer

**General**

- Fluorescent tube display
- Clock/timer with sleep function
- Wake up with CD or tuner
- 23 Key remote control
- Demo mode for trade demonstration

**Weights and Dimensions**

- Centre unit : 140 mm W x 163 mm H x 255 mm D
- Speaker box : 130 mm W x 158 mm H x 185 mm D
- Packaging dimensions : 416 mm W x 242 mm H x 328 mm D
- Weight of product : 5.3 Kg
- Packaged weight : 6.5 Kg

**Product highlights**

- **Digital sound control**  
Provides preset sound settings that enhance various types of music for personal preference.
- **Rotary encoder**  
The encoder determines the speed at which the volume rotation takes place, faster rotations mean larger volume increments, slower rotations make small gains in volume level.
- **3" Full range speakers**  
For excellent sound performance across the entire audio frequency spectrum. The copper sleeve and unique direct-driven dome in these speakers improve the high notes and give you truly transparent sound.
- **Bass reflex speaker system**  
Acoustic system that enhances the upper bass tones to provide a warmer, punchier bass sound.
- **Cloth speaker grilles**  
Grilles covered with acoustically neutral cloth to protect the speaker.
- **Subwoofer ready**  
Affords easy access to greater dimensions in sound with output signal available for connection to an active subwoofer
- **Stereo headphone socket**  
Enables stereo headphones to be used for private listening pleasure. Automatically switches off speakers when used.
- **Digital tuner with 30 presets**  
Provides fast, accurate tuning to your favourite stations. You can store up to 30 stations in memory for fast, easy access.
- **Autostore**  
Automatically stores up to 30 preset stations
- **RDS Radio Data System (Europe only)**  
For RDS stations the frequency as well as the station name, radio text messages and the programme type can be displayed.
- **News (Europe only)**  
The tuner can be set in such a way that listening to a CD is interrupted by the news broadcast of a RDS station.
- **Compact disc digital audio player**  
Compact Disc technology that combines superb digital sound quality with the convenience of random track access and CD functions like CD programme, Shuffle Play and Repeat.
- **CD-Rewritable playback**  
The CD player is capable of playing normal, CD-Recordable and CD-Rewritable discs.
- **Motorised CD tray**  
For convenient, safe loading of your CD.
- **20-Track programmable**  
Stores up to 20 of your favourite CD tracks for playing back in your order of preference.
- **Shuffle play**  
Plays disc selection randomly, giving you a new sequence of tracks each time.
- **Clock/timer**  
Set the alarm portion of a built-in digital clock to wake you to music from your favourite CD or radio station at any desired time of the day.
- **Sleeptimer**  
The set will automatically switch off the chosen function after a preset period of time with a choice of 60, 45, 30, 15 or 10 minutes setting.
- **Mute**  
This feature allows you to switch off the volume instantly to allow for interruptions. The CD or radio will continue playing in silence until you are ready to resume listening.

1999-01-11  
Printed in Hong Kong  
Subject to modification without notice  
© 1998 Koninklijke Philips Electronics N.V.  
All Rights Reserved

<http://www.philips.com>