

Personalized Sound Settings

Time to get personal! The elegant wood-finished MC260 delivers dynamic sound performance, plus the essential functionalities and the freedom to personalize your sound settings according to your tastes. Enjoy music just the way you like it.

Rich sound experience

- Incredible Surround™ for an enhanced sound dimension
- Digital Sound Control for optimized music style settings (Rock, Pop, Jazz, Classic)
- Dynamic Bass Boost for a deeper bass experience
- 2 x 10W RMS/2 x 20W Music Power/400W PMPO

Start the day your way

- Wake-Up and Sleep Timer
- Full logic tape deck with Auto Reverse
- Digital tuning with 40 preset stations

Refined in sound and look

- Elegant wood-finished speakers



Technical specifications

Sound

- Output power:
2 x 10 watts RMS, 2 x 20 watts music power,
400 watts PMPO
- Sound enhancement technology:
Incredible Surround™
Digital Sound Control
(Rock, Pop, Jazz, Classic)
Dynamic Bass Boost

Loudspeakers

- Main speaker type:
2-Way Bass Reflex Speaker System
4" Woofer
Piezo Tweeter
Speaker grills detachable

Audio Playback

- Cassette deck technology: Full logic
- Cassette playback modes:
Auto reverse
Electronic speed control
Full auto stop
Tape counter
- Disc playback media:
CD, CD-R and CD-RW compatible
- Disc playback mode:
20-Track programmable
Repeat one/all/program
Shuffle play
- CD loader type: Top

Audio Recording

- Recording media: Tape
- Tape recording enhancement:
CD synchro start recording
Timer for automatic recording from tuner
Automatic recording level control

Tuner / Reception

- Auto digital tuning
- RDS:
Station name, Program type, Radio text,
RDS clock set, News and Traffic
Announcement (/22/25 only)
- Station presets: 40
- Tuner bands:
FM
MW
LW (/22/25 only)
- Tuner enhancement: Autostore

Connectivity

- Audio input analog: Aux in (cinch)
- Headphone: 3.5mm stereo jack
- Rear connections:
FM coaxial antenna
MW loop antenna

Convenience

- Alarm enhancement technology:
CD, radio or tape alarm timer
Sleep Timer
- Clock display
- Display type: LCD
- Backlight: Blue

Accessories

- FM and MW antennas
- 21-Key remote control

Dimensions

- Center unit dimensions (WxHxD):
140 x 231 x 280 mm
- Main speakers dimensions (WxHxD):
156 x 231 x 190 mm
- Packaging dimensions (WxHxD):
434 x 314 x 349 mm
- Product weight: 7.5 kg

Product highlights

Bass Reflex Speaker System

Bass Reflex Speaker System delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimize the low frequency roll-off of the system. The result is deeper controlled bass and lower distortion. The system works by resonating the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a whole new dimension of deep bass.

Incredible Surround™

Incredible Surround™ is an audio technology from Philips that dramatically magnifies the sound field to immerse you in the audio. Using state-of-the-art electronic phase shifting, Incredible Surround™ mixes sounds from left and right in such a way that it expands the virtual distance between the two speakers. This wider spread greatly enhances the stereo effect and creates a more natural sound dimension. Incredible Surround™ allows you to experience total surround with greater depth and width of sound, without the use of additional speakers.

Digital Sound Control

Digital Sound Control lets you select from pre-set modes that control the frequency bands of sound to optimize certain musical styles. You can choose between different sound settings - Optimal, Jazz, Rock, Techno, Pop or Classic. Each mode uses graphic equalizing technology to automatically adjust the sound balance and enhance the most important sound frequencies in your chosen music style. Digital Sound Control lets you get the most out of your music by adjusting the sound balance to match the music type you are playing.

Dynamic Bass Boost

Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

EAN 87 10895 79365 0 (/22)
87 10895 79366 7 (/25)
87 10895 79367 4 (/30)
87 10895 79368 1 (/33)
87 10895 79364 3 (/21M)
87 10895 82936 6 (/21T)
87 10895 79363 6 (/21)
87 10895 79362 9 (/19)

