

Philips
DVD Micro Theater

DivX playback
component design

MCD177



Turn any room into a theater

plus USB Direct playback

You're in touch with the latest and the coolest - now get a load of the hot 2-in-1 Micro Hi-Fi with DVD, WMA-CD, MP3-CD and USB Direct playback! Relax to your fave movies and music. Home entertainment will never be the same again!

Enrich your movie experience

- Play DVD, DivX®, (S)VCD, MP3-CD, WMA-CD, CD(RW) & Picture CD
- Dolby Digital for ultimate movie experience
- Progressive Scan component video for optimized image quality

Enrich your sound experience

- USB Direct for music and photo playback
- Digital Sound Control for optimized music style settings
- Dynamic Bass Boost for deep and dramatic sound
- Loudness for bass and treble enhancement
- 800W PMPO/40W RMS total power

Easy to use

- FM digital tuning with presets
- Wake up and sleep timer functions

Refined in sound and look

- Elegant wood-finished speakers

PHILIPS

Highlights

USB Direct

Simply plug in your USB device on the system and share your stored digital music and photos with your family and friends.

Digital Sound Control

Digital Sound Control offers you a choice of pre-set Jazz, Rock, Pop and Classic controls you can use to optimise the frequency ranges for different musical styles. Each mode uses graphic equalizing technology to automatically adjust the sound balance and enhance the most important sound frequencies in your chosen music style. Ultimately, Digital Sound Control makes it easy for you get the most out of your music by precisely adjusting the sound balance to match the type of music you are playing.

Dynamic Bass Boost

Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high – at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

Loudness

In the sound spectrum, high and low frequencies are relatively less audible to human ears - especially at low volumes. By activating the Loudness feature, the bass and treble will be amplified so you can savor a more balanced sound perception overall.

Dolby Digital

Because Dolby Digital, the world's leading digital multi-channel audio standards, make use of the way the human ear naturally processes sound, you experience superb quality surround sound audio with realistic spatial cues.

Progressive Scan

Progressive Scan doubles the vertical resolution of the image resulting in a noticeably sharper picture. Instead of sending a field comprising the odd lines to the screen first, followed by the field with the even lines, both fields are written at one time. A full image is created instantaneously, using the maximum resolution. At such a speed, your eye perceives a sharper picture with no line structure.



Specifications

Sound

- Sound Enhancement: Digital Sound Control 4 modes, Dynamic Bass Boost, Loudness
- Sound System: Dolby Digital
- Output Power: 2x20W RMS / 800W PMPO

Loudspeakers

- Main Speaker: 4" woofer, Bass Reflex Speaker System

Video Playback

- Playback Media: DVD-Video, Picture CD, Video CD/SVCD, DivX, DVD+R/+RW, DVD-R/-RW
- Disc Playback Modes: A-B Repeat, Angle, PBC, Slow Motion, Zoom, Parental control, Disc Menu, Fast Backward, Fast Forward, OSD
- Video Enhancement: Progressive Scan
- DVD Region.: 4

Still Picture Playback

- Picture Compression Format: JPEG
- Picture Enhancement: Slideshow with MP3 playback
- Playback Media: CD-R/RW, DVD+R/+RW, Picture CD

Audio Playback

- Playback Media: WMA-CD, MP3-CD, CD, CD-R, CD-RW
- Disc Playback Modes: 20-Track Programmable, Repeat/one/all/program, Shuffle Play, Fast Forward/Backward, Next/Previous Track Search
- Loader Type: Top
- USB Direct Modes: Fast Backward/Fast Forward, Play/Pause, Previous/Next, Program Play, Repeat, Shuffle, Stop

Tuner/Reception/Transmission

- Auto digital tuning
- Tuner Bands: FM Stereo

- Tuner Enhancements: Auto Store
- Station presets: 20

Connectivity

- Video Output - Analog: Component Y Pb Pr (cinch), Composite CVBS (yellow cinch), S-Video (on Hosiden)
- Other connections: Digital audio coaxial out, FM Antenna
- Headphone: 3.5 mm
- Audio Connections: 3.5mm Line in, Analogue Audio Out (L/R)
- USB: USB host

Convenience

- Display Type: LCD
- OSD Languages: English, Traditional Chinese
- Alarms: CD Alarm, Radio Alarm, Sleep timer, USB alarm
- Clock: On main display
- Backlight color: Blue

Accessories

- Included accessories: Composite video cable (Y), FM antenna, World Wide Warranty leaflet
- User Manual: English
- AC/DC Adaptor: Switching power supply
- Quick start guide: English
- Remote control: 40-key with Lithium batteries

Dimensions

- Main speaker dimensions (W x H x D): 160 x 250 x 180 mm
- Packaging dimensions (W x H x D): 554 x 405 x 225 mm
- Set dimensions (W x H x D): 232 x 85 x 275 mm
- Weight incl. Packaging: 7.3 kg

Power

- Power supply: 100-240VAC, 50/60Hz



Issue date 2014-02-11

Version: 2.0.7

12 NC: 8670 000 38469
EAN: 87 12581 40788 9

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com