



Philips
Micro music system

CD, MP3-CD, USB, FM



MCM3150

Rich and powerful sound

Obsessed with sound

The trendy Philips MCM3150 Micro music system sets the pace with sound that is detailed and full of powerful bass - thanks to the wOOx technology.

Unlimited listening pleasure

- Audio-in for portable music playback
- Play MP3-CD, CD and CD-R/RW
- USB Direct for easy MP3 music playback

Enrich your sound experience

- wOOx™ loudspeaker Technology for deep and powerful bass
- Dome tweeter for detailed and natural sound
- Digital Sound Control for optimized music style settings
- 120W RMS total output power

Easy to use

- Motorized CD loader for convenience access
- Radio Data System for station information and data services
- Wake up and sleep timer functions

PHILIPS

Micro music system
CD, MP3-CD, USB, FM

Highlights

wOOx™ Technology



wOOx technology is a revolutionary loudspeaker concept that allows you to hear and feel profoundly deep bass that is richer than any other audio system. Special speaker drivers work in harmony with the wOOx bass radiator, and precise tuning between the main driver and the tweeter ensures smooth transitions from low-mid to high frequencies. Dual suspension and a totally symmetrical sandwich construction deliver low and precise base without noticeable distortion. wOOx produces exceptionally deep and dynamic bass by using the speaker box full volume to truly magnify the impact of the music.

Radio Data System (RDS)

The Radio Data System (RDS) lets you tune into radio stations without having to remember the frequencies. In standard mode, RDS displays the station name instead of the transmission frequency, facilitating quick and easy tuning. RDS also allows stations to send text messages such as news and station information directly to the radio display. Commonly used in Europe, RDS text is sent out on the same frequency the radio station

broadcasts on. You can choose either the basic RDS display (station name) or subscribe to additional text-based services.

Dome tweeter

Dome tweeters reproduce clear high and mid-range frequencies that enhance the overall sound clarity coming from the speakers. Delivering a harmonious blend of undistorted and uncolored wide-ranging sound, they offer detailed vocal clarity and instruments tone purity, thereby balancing the overall sound when paired with a combination of woofers.

Digital Sound Control



Digital Sound Control offers you a choice of pre-set Jazz, Rock, Pop and Classic controls you can use to optimise the frequency ranges for different musical styles. Each mode uses graphic equalizing technology to automatically adjust the sound balance and enhance the most important sound frequencies in your chosen music style. Ultimately, Digital Sound Control makes it easy for you get the most out of your music by precisely adjusting the sound balance to match the type of music you are playing.

MCM3150/55

USB Direct for easy MP3 music



Thanks to the complete file transferability, you can easily enjoy the convenience and fun of accessing more digital music via the built-in USB Direct.

Play MP3-CD, CD and CD-R/RW



MP3 stands for "MPEG 1 Audio layer-7.6 cm (3") .MP3 is a revolutionary compression technology by which large digital music files can be made up to 10 times smaller without radically degrading their audio quality. MP3 has become the standard audio compression format used on the world wide web, allowing quick and easy audio file transfer.



Specifications

Sound

- Sound Enhancement: Digital Sound Control
- Maximum output power (RMS): 120W

Loudspeakers

- Loudspeaker types: Dome tweeter
- Main Speaker: wOOx Bass Radiator, 2 way

Audio Playback

- Playback Media: CD, CD-R, CD-RW, MP3-CD
- Disc Playback Modes: 20-Track Programmable, Repeat/one/all/program, Shuffle Play, Fast Forward/Backward, Next/Previous Track Search
- Loader Type: Tray, Motorised
- USB Direct Modes: Fast Backward/Fast Forward, Play/Pause, Previous/Next, Program Play, Repeat, Shuffle, Stop

Tuner/Reception/Transmission

- Auto digital tuning
- RDS: Station Name, Program Type
- Station presets: 20
- Tuner Enhancements: Auto Store
- Tuner Bands: FM Stereo
- Antenna: FM antenna (75 ohm)

Connectivity

- USB: USB host

- Headphone: 3.5 mm
- 3.5mm stereo line in: Audio in
- Other connections: FM Antenna

Convenience

- Alarms: CD Alarm, Radio Alarm, USB alarm
- Clock: On main display
- Display Type: VFD display
- Sleep timer

Accessories

- Included accessories: FM antenna, AC Power Cord, World Wide Warranty leaflet
- Remote control
- User Manual: Multi-language

Power

- Power supply: 110-240V, 50/60 Hz

Dimensions

- Set dimensions (W x H x D): 230 x 145 x 237 mm
- Main speaker dimensions (W x H x D): 139 x 259 x 210 mm
- Packaging dimensions (W x H x D): 510 x 314 x 280 mm
- Weight incl. Packaging: 7.4 kg
- Set weight: 6.2 kg



Issue date 2014-07-30

Version: 2.0.2

12 NC: 8670 001 02404
EAN: 87 12581 68532 4

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com