

Philips  
Micro Hi-Fi System

MP3

MCM530



## Remote Control MP3 Music from Your PC

Enjoy the freedom of remote controlling your MP3 Music from your PC and savoring it through the MCM530's powerful, dynamic speakers. With USB PC Link for MP3 streaming and Max Sound, music lovers will appreciate this complete audio solution

### **MP3 music at your fingertips**

- USB PC link turns your PC into a massive MP3 music jukebox
- Song title and playlist name display for easy navigation

### **Longer listening, greater enjoyment**

- Playback 50 hours of MP3 music from 5 CDs

### **Power and performance**

- Class 'D' digital amplifier for quality sound performance
- MAX Sound for instant power boost
- 2-Way Bass Reflex Speaker System for powerful sound
- 2500W PMPO / 150W RMS total power

# PHILIPS

# Specifications

## Sound

- Output Power: 2500 watts PMPO
- Sound Enhancement: MAX Sound, Digital Sound Control 4 modes, Virtual Environment Control, Class "D" Digital Amplifier

## Loudspeakers

- Main Speaker: 2 way, Bass Reflex Speaker System, 5.25" woofer, 2" tweeter, Speaker grilles detachable

## Audio Playback

- Playback Media: CD, CD-R, CD-RW, MP3-CD
- Disc Playback Modes: 99-Track Programmable, Repeat/one/disk/program, Shuffle Play
- Loader Type: Motorised, Tray
- Number of Discs: 5
- PC Link playback mode: USB connection, By-pack Musicmatch software, Navigate MP3 music via RC, Track + playlist info display
- PC Link sound enhancement: By-pack Sound Agent Software

## Tuner/Reception/Transmission

- Auto digital tuning
- Station presets: 40
- Tuner Bands: FM Stereo, MW
- Tuner Enhancements: Easy Set (Plug & Play), Auto Store

## Connectivity

- Aux in: Line in
- PC Link: USB 2.0
- Headphone: 3.5 mm
- Other connections: FM Antenna, MW Antenna

## Convenience

- Alarms: CD Alarm, Radio Alarm, Sleep timer
- Clock: On main display
- Display Type: Green FTD
- Indications: DIM mode
- Eco Power Standby: 0.6 watt

## Accessories

- Included accessories: FM/MW Antenna, AC Power Cord
- USB cable: 3-meter
- Remote control: 32-key with 2xAA Batteries
- CD-ROM: installation disc

## Software

- USB PC Link driver
- Music Match Jukebox: Music Match Jukebox
- Philips Sound Agent 2: Yes, for Windows 2000/XP

## System Requirements

- CD-ROM drive
- USB: Free USB port
- Processor: Intel Pentium MMX200 or higher
- PC OS: Windows 98 SE, 2000, ME, XP
- Hard disk space: 80 MB

## Dimensions

- Set dimensions (W x H x D): 175 x 268 x 316 mm
- Main speaker dimensions (W x H x D): 180 x 268 x 220 mm
- Packaging dimensions (W x H x D): 521 x 374 x 410 mm
- Weight incl. Packaging: 12.9 kg

# Highlights

## USB PC Link

USB PC Link lets you playback your MP3 music through the powerful speakers of Philips sound systems instead of your PC speakers. By connecting a PC directly to your audio system with a USB cable, you can stream MP3 music directly to your sound system, transforming your PC into a 'massive MP3 music jukebox'. The control buttons on the sound system and remote control provide easy navigation and control of the MP3 music stored in the MusicMatch Playlist. You can also view song title information as well as elapsed play time on the sound system's display.

## Song title display

Song title and playlist name display for easy navigation

## 50 hours of MP3-CD playback

MP3 is a revolutionary compression technology by which large digital music files can be made up to 10 times smaller without radically degrading their audio quality. A single CD can store up to 10 hrs of music. With 5 CD-tray, it allows you to play 50 hours of music. MP3 has become the standard audio compression format, allowing quick and easy audio file transfer.

## Class 'D' Amplifier

Class 'D' Digital Amplifier takes an analog signal, converts it into a digital signal and then amplifies the signal digitally. The signal then enters a demodulation filter to give the final output. The amplified digital output delivers all the advantages of digital audio, including improved sound quality. In addition, Class 'D' Digital Amplifier has greater than 90% efficiency compared to traditional AB amplifiers. This high efficiency translates into a powerful amplifier with a small footprint.

## MAX Sound

MAX Sound technology produces an instant boost in bass, maximizing volume performance and instantly creating the most impressive listening experience with just the touch of a button. Its sophisticated electronic circuitry calibrates existing sound and volume settings, instantly boosting bass and volume to maximum levels without distortion. The end result is a noticeable amplifying of both sound spectrum and volume and a potent audio boost that will add mileage to any music.

## 2-Way Bass Reflex System

2-Way Bass Reflex Speaker System for powerful sound

## 2500W PMPO / 150W RMS

This system has 2500W PMPO / 150W RMS total output power. RMS refers to Root Mean Square which is a typical measurement of audio power, or rather, the electrical power transferred from an audio amplifier to a loudspeaker, which is measured in watts. The amount of electrical power delivered to the loudspeaker and its sensitivity determines the sound power that is generated. The higher the wattage, the better the sound power emitted by the speaker.



Issue date 2014-02-05

Version: 4.0.5

12 NC: 9073 100 11651  
EAN: 87 10895 78923 3

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)