

## Play MP3-CD

in Sophisticated Style with Great Sound

Specifically designed for one who appreciates the ultimate in technology and style, the MCM7 exudes finesse and quality. Unleash the audiophile in you and savor the enhanced sounds from your MP3-CD through powerful, dynamic speakers.

### Rich sound experience

- 2 x 50W RMS/2 x 100W music power
- Ferro Fluid Cone Dome Tweeters
- Flat metal cone woofer
- 2-Way Bass Reflex Speaker System with detachable grilles

### Unlimited listening pleasure

- 10 hours of MP3-CD music

### Personalized sound settings

- Incredible Surround™ for an enhanced sound dimension
- Bass and Treble Control for easy high and low tone settings

### Refined in sound and looks

- Elegant design with wood-finished speakers



# PHILIPS

## Technical specifications

### Sound

- Output power:  
2 x 50 watts RMS/  
2 x 100 watts music power
- Sound enhancement technology:  
Incredible Surround™,  
Treble and Bass Control

### Loudspeakers

- Main speaker:  
2-Way Bass Reflex Speaker System,  
5.25" Woofer, 2" Tweeter,  
Speaker grilles detachable

### Audio Playback

- Disc playback media:  
CD, CD-R, CD-RW, MP3-CD
- Disc playback mode:  
Repeat one/disc/program, Shuffle play,  
99-Track programmable
- Loader type: Tray, Motorized
- Cassette deck technology: Full logic
- Cassette playback mode:  
Auto reverse, Electronic speed control,  
Full auto stop, Tape counter

### Audio Recording

- Recording media: Tape
- Tape recording enhancement:  
Automatic recording level,  
CD synchro start recording,  
One-touch recording

### Tuner / Reception

- Auto digital tuning
- RDS:  
News, Program type, Radio text,  
RDS clock set, station name
- Tuner band: FM, MW
- Tuner enhancement:  
Autostore, Easy setup (Plug & Play)

### Connectivity

- Audio input analog: Aux in (cinch)
- Headphone 3.5 mm
- Rear connections:  
FM coaxial antenna  
MW loop antenna

### Convenience

- Alarm enhancement technology:  
CD, radio, tape alarm timer, snooze,  
Sleep timer
- Clock display
- Display type: FTD
- Indication: DIM mode
- Eco power standby: <0.5W

### Accessories

- FM and MW antennas
- Remote control:  
32 keys with 2 x AA batteries
- AC power cord

### Dimensions

- Center unit dimensions (WxHxD):  
175 x 252 x 350 mm
- Main speakers dimensions (WxHxD):  
175 x 252 x 215 mm
- Packaging dimensions (WxHxD):  
524 x 353 x 408 mm
- Weight incl packaging: 12.9 kg

## Product highlights

### MP3-CD Playback

The MP3-CD format combines the advantages of MP3 digital audio compression with the affordable and widely accepted CD storage format. The end result is that a tiny 8cm MP3-CD can hold over 3 hours of MP3 music, while a normal 12cm disc can hold over 10 hours. Using readily available software, you can rip music from your audio CDs or download MP3 music legally from the internet and burn it to a recordable or rewritable 12cm or 8cm CD. The resulting MP3-CD can be played back as though it were a normal audio CD.

### Treble and Bass Control for easy high and low tone settings

Treble and bass are equalizer features that control the high and low frequency sound levels of your audio respectively. Treble specifically regulates the amplification of the high tones in the music while bass controls the amplification level of the low tones. Using the up and down keys, the listener can conveniently place more or less emphasis on the low and high tones, or leave treble and bass flat to playback music according to its original recorded setting. Treble and Bass Control lets you listen to your music the way you like it.

### Bass Reflex Speaker System for powerful sound experience

Bass Reflex Speaker System delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimize the low frequency roll-off of the system. The result is deeper controlled bass and lower distortion. The system works by resonating the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a whole new dimension of deep bass.

EAN 87 10895 80132 4 (/22)  
87 10895 82410 1 (/25)



Printed in Hong Kong 2004-02-17  
Specifications are subject to change without notice  
2004 © Royal Philips Electronics - All rights reserved  
[www.philips.com](http://www.philips.com)