

MWA2522

1.5m Fiber optic cable

Depend on this cable to take your components to optimum performance. It offers the best connection for transferring audio signals between components.

- *High quality fiber optics*
- *Non-slip ergonomic grip for easy use*
- *Molded plug for secure connections*
- *Flexible PVC jacket*
- *Rubber strain relief*



MWA2522/10 1.5m Fiber optic cable

Product specifications

Packaging dimensions

- Packaging dimensions (W x H x D):
9.5 x 23.5 x 2.2 cm
- Nett weight: .008 kg
- Gross weight: .03 kg
- Tare weight: .022 kg

Outer Carton

- Outer carton (L x W x H): 32.1 x 26 x 30.8 cm

- Nett weight: .288 kg
- Gross weight: 2.126 kg
- Tare weight: 1.838 kg

Inner Carton

- Inner carton (L x W x H): 24.5 x 10.2 x 14 cm
- Nett weight: .048 kg
- Gross weight: .27 kg
- Tare weight: .222 kg

Fiber Optics

Optically pure light tube carries digital information to your components for uncompromised Hi-definition sound.

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Molded plug

Molded plugs ensure secure connections between components and offer extended durability.

Flexible PVC Jacket

Flexible PVC jacket provided protection to the delicate core of the cable. It also offers extended durability and ease of installation.

Rubber strain relief

Rubber strain relief provides a secure, yet flexible juncture between the cable and the plug.