

## MWA2523

### 3.0m Stereo audio cable

Depend on this cable to provide you with a reliable audio connection between components.

- ***High purity copper conductor for reliable signal transfer***
- ***Nickel-plated connectors for reliable contact***
- ***Bare copper shielding***
- ***Color coded connectors for instant recognition***
- ***Non-slip ergonomic grip for easy use***
- ***Molded plug for secure connections***
- ***Flexible PVC jacket***
- ***Rubber strain relief***



## MWA2523/10 3.0m Stereo audio cable

### Product specifications

#### Packaging dimensions

- Packaging dimensions (W x H x D): 9.5 x 23.5 x 2.2 cm
- Nett weight: 0.06 kg
- Gross weight: 0.08 kg
- Tare weight: 0.02 kg
- EAN: 87 12581 41450 4
- Number of products included: 1
- Packaging type: Blister

#### Outer Carton

- Outer carton (L x W x H): 34 x 26.5 x 23 cm
- Nett weight: 1.44 kg

- Gross weight: 2.8 kg
- Tare weight: 1.36 kg
- EAN: 87 12581 41456 6
- Number of consumer packagings: 24

#### Inner Carton

- Inner carton (L x W x H): 24.5 x 10.5 x 10.2 cm
- Nett weight: 0.24 kg
- Gross weight: 0.4 kg
- Tare weight: 0.16 kg
- EAN: 87 12581 41453 5
- Number of consumer packagings: 4

#### **High purity copper**

This copper conductor provides high accuracy in signal transfer with minimal resistance.

#### **Bare copper shielding**

Bare copper shielding protects against signal loss.

#### **Color-coded connectors**

Color coded connections make it easy to install your cable into the correct inputs and outputs

#### **Easy grip**

This non-slip grip makes connecting your components easy and ergonomically comfortable.

#### **Molded plug**

Molded plugs ensure secure connections between components and offer extended durability.

#### **Flexible PVC Jacket**

Flexible PVC jacket provided protection to the delicate core of the cable. It also offers extended durability and ease of installation.

#### **Rubber strain relief**

Rubber strain relief provides a secure, yet flexible juncture between the cable and the plug.

#### **Nickel-plated connectors**

Nickel-plated connectors establish a clean contact between the cable and connector for a reliable connection.