

MWV2902

3.0m White PAL coax cable M to F

Depend on this cable to provide you with a reliable audio/video connection between components.

- ***Nickel-plated connectors for reliable contact***
- ***High purity copper conductor for reliable signal transfer***
- ***Bare copper shielding***
- ***Non-slip ergonomic grip for easy use***
- ***Molded plug for secure connections***
- ***Flexible PVC jacket***
- ***Rubber strain relief***



MWV2902/10 3.0m White PAL coax cable M to F

Product specifications

Inner Carton

- Gross weight: 0.5 kg
- Inner carton (L x W x H): 24.3 x 15.6 x 10.5 cm
- Nett weight: 0.32 kg
- Tare weight: 0.18 kg
- EAN: 87 12581 41489 4
- Number of consumer packagings: 4

Outer Carton

- Gross weight: 3.48 kg
- Outer carton (L x W x H): 35 x 33.6 x 26.2 cm
- Nett weight: 1.92 kg
- Tare weight: 1.56 kg

- EAN: 87 12581 41490 0
- Number of consumer packagings: 24

Packaging dimensions

- Packaging dimensions (W x H x D):
9.6 x 23.5 x 2.1 cm
- Gross weight: 0.1 kg
- Nett weight: 0.08 kg
- Tare weight: 0.02 kg
- EAN: 87 12581 41486 3
- Number of products included: 1
- Packaging type: Blister

Nickel-plated connectors

Nickel-plated connectors establish a clean contact between the cable and connector for a reliable connection.

High purity copper

This copper conductor provides high accuracy in signal transfer with minimal resistance.

Bare copper shielding

Bare copper shielding protects against signal loss.

Easy grip

This non-slip grip makes connecting your components easy and ergonomically comfortable.

Molded plug

Molded plugs ensure secure connections between components and offer extended durability.

Flexible PVC Jacket

Flexible PVC jacket provided protection to the delicate core of the cable. It also offers extended durability and ease of installation.

Rubber strain relief

Rubber strain relief provides a secure, yet flexible juncture between the cable and the plug.