

# 700watts Total Power



## 3 DVD-Digital Home Cinema System

- 6 Speaker Package with 700 Watts Total Power
- All-in-one Integrated 3 DVD/CD changer, Digital Surround Sound Receiver
- Dolby Digital 5.1, Dolby Prologic & DTS channel decoder
- 5 3-way MTM (Mid-range tweeters & Mid-range drivers) satellite speakers
- 5 x 115 Watts equal power output
- 125 Watts Twin Port subwoofer for deeper bass
- Digital tuning with 40 presets for hook-up to external (5.1 sound) sources
- Digital Audio output for perfect CD recording
- CVBS, S-Video output & Component (R/G/B) video output
- Digital Audio input
- 5 analogue audio inputs & 3 audio output connections
- 2 video input and 3 video output connections
- DVD, DVD+RW, CD, CD-R, CD-RW and CD-MP3 playback
- Full function remote control, also controls Philips TV
- Cables for TV hook-up and quick installation card included



Let's make things better.



PHILIPS



### Sound Enhancement

**Dolby Digital Surround Sound** - Available on DVD, Laserdisc\*, satellite broadcasts, Cable and as the standard for HDTV, Dolby Digital® offers the ultimate experience in home theater surround with six discrete channels of digital CD sound. Discrete means that each channel carries its own sound and depending on what happens on screen each speaker plays its own unique role in providing the right sound. Front left, center and right join two surround speakers to reproduce highs, mid and bass frequencies in five full-range channels of surround. Bass rumble, explosions and low frequency effects you feel are delivered through a dedicated sixth, subwoofer channel. Also known as AC-3 and Dolby 5.1, Dolby Digital® delivers the expanded sense of depth, localization and overall realism which was formerly only known from digital surround sound equipped cinemas.

**DTS** - DTS surround sound is a cinema surround sound audio format that offers superior digital audio performance than other available surround sound formats. DTS offer more clarity and definition especially for higher tones. The better sound quality is a direct result of the limited sound compression (3:1 instead of 11:1 for Dolby Digital) and the 20-bit resolution. DTS movie and music software is available on various DVD and CD titles.

**MP3-CD Playback** - Download MP3 songs from the internet on a PC and record them on a CD. This special "MP3-CD" can now be played on the Philips FV-M355 Mini System. One MP3-CD can carry up to 12 hours of music. As the CD changer can be loaded with 3 CD's, one can enjoy 36 hours of uninterrupted music listening!

**6-speaker package** - No less than 5 3-way MTM (Mid-range tweeters & Mid-range drivers) satellite loudspeakers to build your personal cinema. The five speakers are acoustically specially designed to match the tonal characteristics of the receiver. Front left, right and center speaker are magnetically protected to prevent any interference with television picture tube purity. The sixth speaker is a 120 watt subwoofer.

**700W surround power output** - The five, 3x115W (left, right, center) and 2x115W (rear), receiver amplifiers together with the 125W subwoofer deliver 700 Watts of home theater power. The stereo output power of 115W per channel is specified at 6 Ohm, 1 kHz and 10% total harmonic distortion (THD). The amplifiers have been designed with special attention to a short 'rise' and 'fall' time, so characteristic for the frequent and sudden drastic changes in dynamics of movie sound in general. Furthermore, the amplification reserves are designed such that they are more than sufficient to follow sudden needs for more sound pressure.

**125W Twinport subwoofer** - Twinport Subwoofers add dynamism to normal music and motion pictures. It sets the stage for a more intense sensation. The 125W Philips subwoofer features a front-firing 6 1/2" woofer and twinport bass tubes to reflect sound waves off the floor, thereby adding impact. In all, the subwoofer is sufficiently power packed to generate that cinema essential sonic sound boom.

### Convenience

**Digital inputs and output** - (3) digital inputs (2 coax, 1 optical) are foreseen to connect digital sound sources. A digital output connection (coax) is foreseen to enable digital (CD) recordings from any of the digital inputs. The output can provide a down-mixed (stereo) DVD multi-channel sound signal in order to record from DVD to e.g. CD-R.

**Digital output** - A digital output connection (coax) is foreseen to enable digital (CD) recordings to eg. CDR.

**Night mode** - Establishes dynamic range compression of digital sound to reduce the volume differences between the loud and soft passages in source material with digital surround sound where sound level differences can be so dramatic. This feature is especially useful at night when you don't want to disturb the neighbors or wake up the kids!

**Video Connections** - 3 video input connections and 2 outputs (incl. monitor) are foreseen to hook up video sources. As these video inputs switch simultaneously with the audio inputs, correct picture with correct sound is guaranteed.

**Easy hook up** - With color coded speaker connections for quick and easy connection of all loudspeakers. By using distinct colors for each of the speaker connection terminal on the speaker and on the set, and using the same color for the cable, the chance of faulty connection (and customer complaints) are practically zero!

**30 tuner presets with station name display** - The available tuner presets can be randomly used to store AM and FM stations (30 in total).

**Display brightness adjustment** - Conveniently adjusts the brightness of the display in 2 steps.

**Standby power <1W** - To help save energy consumption, the standby transformer of this set has been designed not to consume more than 1 Watt in standby mode.

**DVD Playback** - The DVD drive plays DVD, DVD+RW and Video CD discs as well as CD, CDR, CD-MP3 and CDRW discs recorded on a CD recorder. The system has a full on screen display for easy set-up and operation. Other video features are zoom, multi-angle and parental lock.

### Connections

- Audio inputs/outputs
  - TV : 5 analogue input sources,
  - VCR : 3 analogue output connection
  - CDR : :in
  - Headphone : in/out
  - Monitor : in/out
- Digital audio in/output : 6.3mm
- Digital audio in/output : 2 digital output connection (optical)
- Video inputs/outputs : 2 input sources, 3 output connections (1 S-Video)
- TV : in/out
- VCR : in/out
- Monitor : out
- Speaker Connections suitable for speakers ≥ 6 Ohm
  - left, right, center : click-fit connection
  - rear left, right : click-fit connection
- Miscellaneous connections
  - subwoofer pre-out : 1
  - AM antenna : loop type
  - FM antenna : click-fit 300 Ohm

UPC Code : 0 37849 91871 5

Product Dimensions:

- 17.1" W x 5.9" H x 14.2" D (receiver)
- 3.7" W x 10.0" H x 3.3" D (l/r, center + surround)
- 10.0" W x 3.7" H x 3.3" D (center speaker)
- 7.7" W x 17.0" H x 15.4" D (subwoofer)
- DVD/Receiver weight : t.b.c.

Package Dimension: 24.5" W x 19.5" H x 20.4" D

Total package weight: t.b.c.

Container loading: 320 pcs (40' container)

Country of origin: China

Carton contains: DVD/Receiver MX5000D, remote control, batteries, instruction for use, AM + FM antenna, quick installation card, warranty information, 6 loudspeakers (incl. subwoofer), loudspeaker cable (L/R: 2x9ft, C: 1x9ft, S: 2x33ft.), subwoofer + connection cable, digital audio cable, video cable

Printed in Singapore

Date printed : Mar 2002

©2002 Royal Philips Electronics N.V.

\* Dolby Digital laserdisc use requires optional AC-3 RF demodulator

<http://www.philipsusa.com>

Let's make things better.



PHILIPS