

Philips Power w00x Speaker technology Powerful/Deep Bass!



Digital Audio Surround Sound Receiver Package

- Upgrade your DVD player into a complete Digital Home Cinema System
- 6-Speaker Package with 100W w00x Subwoofer and 5 compact 2-way Satellite speakers (customized acoustical speaker design!)
- 600 Watts Surround Power Output
- 5 x 100 Watts equal power per channel
- 100 Watts Powered w00x Subwoofer
- Digital Sound Processing via DUET CORE
- 10 Audio Input connections in total
- 3 Digital Inputs (2 coax, 1 optical) and a Digital Output (coax) for Digital (CD) Recordings from multiple analogue or digital sources including DVD!
- 3 Video Input Connections and 2 Outputs
- 5 S-Video connections
- 6 Channel Input terminal (DVD Audio and Super-Audio CD prepared)
- Virtual 3D Surround for Simulated Surround Sound without Rear Speakers
- 'Hall' feature for normal stereo with rear speaker sound
- All Dolby surround Modes and Delay Times
- Equalizer smart sound modes : Personal, Speech, Music, Movie, Multi-Media
- Screw terminals for Left, Right and Center speaker connections
- 51-key Audio/Video MultiBrand Universal Remote Control



Let's make things better.



PHILIPS



Sound Enhancement

Dolby Digital Surround Sound - Available on DVD, Laserdisc®, satellite broadcasts, Cable and as the standard for HDTV, Dolby Digital® offers the ultimate experience in home theater surround with six discrete channels of digital CD sound. Discrete means that each channel carries its own sound and depending on what happens on screen each speaker plays its own unique role in providing the right sound. Front left, center and right join two surround speakers to reproduce highs, mid and bass frequencies in five full-range channels of surround. Bass rumble, explosions and low frequency effects you feel are delivered through a dedicated sixth subwoofer channel. Also known as AC-3 and Dolby 5.1, Dolby Digital® delivers the expanded sense of depth, localization and overall realism which was formerly only known from digital surround sound equipped cinemas.

6-speaker package - No less than 5 compact 2-way satellite loudspeakers to build your personal cinema on a stand or wall-mounted with the enclosed wall-brackets. The five speakers are acoustically specially designed to match the tonal characteristics of the receiver. Front left, right and center speaker are magnetically protected to prevent any interference with television picture tube purity. The sixth speaker is a 50 watt powered subwoofer.

600W surround power output - The five, 3x100W (left, right, center) and 2x100W (rear), receiver amplifiers together with the 100W wOoX subwoofer amplifier deliver 600Watts of home theater power. The stereo output power of 80W per channel is specified at 6 Ohm, 40Hz-20KHz and 0.7% total harmonic distortion (THD). The amplifiers have been designed with special attention to a short 'rise' and 'fall' time, so characteristic for the frequent and sudden drastic changes in dynamics of movie sound in general. Furthermore, the amplification reserves are designed such that they are more than sufficient to follow sudden needs for more sound pressure.

100W powered wOoX subwoofer - Subwoofers add dynamism to normal music and motion pictures. It sets the stage for a more intense sensation. The 100W Philips wOoX subwoofer features a down firing 6 1/2" active woofer to reflect sound wave of the floor. Additionally a 6 1/2" wOoX base radiator adds even more punchy bass. In all, the subwoofer is sufficiently power packed to generate that cinema essential sonic sound boom.

wOoX Technology

Philips patented wOoX Technology ensures superior bass results. The dual suspension bass radiator, together with dedicated amplifier circuitry is especially designed to produce and handle high dynamic sound signals at very low frequencies. Because of the dual suspension, the excursion of the membrane can be extreme (see illustration). This, in combination with the symmetrical sandwich construction, provides for very low and precise bass without noticeable distortion. The net effect of using wOoX Technology is a tight bass sound that is significantly "lower and louder" than conventional mini shelf systems.

Digital Sound Processing via DUET CORE - Philips Semiconductors is highly specialized in digital sound processing. One of their crown DSP (digital sound processing) ICs is the 'DUET'. The DUET's huge processing power of 80 MIPS (million instructions per second) assures the highest possible accuracy in digital audio processing. Other characteristics are automatic detection of source (AC-3, MPEG or PCM audio) and smooth (clicking free) automatic switching between coding formats. Furthermore DUET carries digital bass cross-over filters (for subwoofer signal) and 3rd generation virtualizer algorithms for highly realistic virtual Dolby. Lastly, DUET has the unique capability of translating Dolby Digital multi-channel sound into a stereo signal suitable for digital recording onto e.g. CD-R.

Virtual 3D Surround / Virtual Dolby® Surround - A Dolby Surround playback system delivers amazingly rich and convincing surround sound from only the two (or three) front speakers. The Pro-Logic or Dolby Digital® surround channel is processed by a 'virtualizer' DSP to add the surround effect from just the front speakers. The Philips virtualizer algorithm on the 'DUET' DSP is the current state of the art reference for virtual surround sound processing.

'Hall' feature - For use with non-surround sound sources in order to create a cinema effect through normal stereo with rear speaker sound. This 'simulated' surround provides an extra musical ('live') ambience to stereo sound.

Equalizer Smart Sound - Has 5 modes, specially designed to match the sound of various TV (and Audio) programs. 'Speech' is used for news, discussions and talk 'show programs. 'Music' is used for music programs. 'Movie' is used for movies or TV-series or soaps. 'Multi-Media' is used when video games are connected to the TV. 'Personal' corresponds with the bass and treble setting chosen by the user.

Screw terminals - For left, right and center speaker connection ensures a loss-less flow of electrical signals from the set to all main loudspeakers.

Convenience

Digital inputs and output - 3 digital inputs (2 coax, 1 optical) are foreseen to connect digital sound sources (e.g. DVD player, CD player and Digital TV). A digital output connection (coax) is foreseen to enable digital (CD) recordings from any of the digital inputs. The output can provide a down-mixed (stereo) DVD multi-channel sound signal in order to record from DVD to e.g. CD-R.

Stereo Downmix - The digital output will automatically provide a stereo downmix in case a multichannel signal is detected at any of the digital input connectors. In that way digital audio recordings can be made from movie DVD's (e.g. Live concerts from music DVD's)

Night mode - Establishes dynamic range compression of digital sound to reduce the volume differences between the loud and soft passages in source material with digital surround sound where sound level differences can be so dramatic. This feature is especially useful at night when you don't want to disturb the neighbors or wake up the kids!

Video Connections - 3 video input connections and 2 outputs (incl. monitor) are foreseen to hook up video sources. As these video inputs switch simultaneously with the audio inputs, correct picture with correct sound is guaranteed. All video connections are both S-Video and composite video.

6 Channel input - Six input selectors at the back of the set allow to connect to any type of multichannel decoder. Be it DTS, DVD Audio or Super Audio CD. The 6 Channel input makes your system future proof!

Easy hook up - With color coded speaker connections for quick and easy connection of all loudspeakers. By using distinct colors for each of the speaker connection terminal on the speaker and on the set, and using the same color for the cable, the chance of faulty connection (and customer complaints) are practically zero!

51-key Audio/Video Multi Brand Universal remote control - To operate all main receiver functions and Philips, Magnavox or any other mainstream branded CD player, tape deck, VCR, television and DVD player, Satellite or cable box! The remote will operate your Philips equipment by simply entering a code from the instruction manual in the remote control. The remote has a clear ergonomically designed layout (see picture)

30 tuner presets with station name display - The available tuner presets can be set to high and low. In case of low, only the 'strong' stations will be picked up during a search. When even some of the weaker stations are of interest, the 'low' option will pick up every station the tuner can possibly receive.

Tuner sensitivity adjustment - The tuner sensitivity to pick up radio stations can be set to high and low. In case of low, only the 'strong' stations will be picked up during a search. When even some of the weaker stations are of interest, the 'low' option will pick up every station the tuner can possibly receive.

2 switched mains outlets - Allows to connect another HiFi component. Switching the receiver to standby will automatically switch off the connected set.

Standby power <2W - To help save energy consumption, the standby transformer of this set has been designed not to consume more than 2Watt in standby mode.

Design

Display - Color and graphic/character size are defined such that at visibility remains clear even at large distances.

Connections

- Audio inputs/outputs
 - Phono : in
 - CD : in
 - CDR/Tape : in/out
 - TV : in
 - SAT : in
 - VCR : in/out
 - 6 CH/DVD : in
 - DVD : see digital audio inputs/outputs
 - Headphone : 6.3mm
- Digital audio in/output
 - 2 digital coax connections : in
 - 1 optical slink to connection : in
 - 1 digital coax connection : out
- Video inputs/outputs
 - 3 input sources, 2 output connections
 - in (S-VHS + CVBS)
 - in (S-VHS + CVBS)
 - in/out (2 x S-VHS + CVBS)
 - out (S-VHS + CVBS)
 - Speaker Connections suitable for speakers ≥ 6 Ohm
 - left, right, center : screw type connection
 - rear left, right : click-fit connection
 - Miscellaneous connections
 - Cinema Link System control bus
 - subwoofer pre-out : 1
 - center pre-out : 2
 - mains outlet : switched 2x
 - AM antenna : loop type
 - FM antenna : click-fit 300 Ohm

UPC Code : t.b.c.

Product Dimensions:

- 17.2" W x 5.3" H x 13.8" D (receiver)
- 3.8" W x 6.2" H x 3.5" D (l/r, center + surround)
- 10.0" W x 3.8" H x 3.5" D (center speaker)
- 7.9" W x 12.2" H x 14.6" D (subwoofer)

Product weight: 45 lbs(receiver)

Package Dimension: 16.3" W x 15.4" H x 17.7" D

Container loading: 480 pieces

Country of origin: China

Carton contains: receiver FR966/17S, remote control, batteries, instruction for use, AM + FM antenna, quick installation card, warranty information, 6 loudspeakers (incl. subwoofer), loudspeaker cable (L/R: 2x9ft, C: 1x9ft, S: 2x33ft), subwoofer mains + connection cable, 'Cinema Link' cable, digital audio cable for DVD connection

Printed in Singapore

Date printed : Aug 2000


©2000 Royal Philips Electronics N.V.

All rights reserved.

A Division of Philips Electronics North America Corp. Specifications subject to change without notice. Dolby, Dolby Digital®, Dolby ProLogic®, and the double-D symbol are trademarks of Dolby Laboratories

As an ENERGY STAR® Partner, Philips has determined that this product meets the ENERGY STAR® guidelines for energy efficiency.

* Dolby Digital laserdisc: use requires optional AC-3 RF demodulator



Let's make things better.



PHILIPS