


# Technical & Rugged



## GLOSS

Transparent 40-tonne high pressure injection moulded casing - 8mm thick, encases the chassis. The high gloss, hybrid shell is solidly bolted on with hardened carbon steel alloy bolts. The wrap-around speaker guard is constructed from high impact polystyrene in the latest shade of cool. Luminous in looks and sound.



Let's make things better.



PHILIPS



# Emotive Micro

## standard product information

### amplifier

- 1000 watts PMPO
- 2 x 50 watts Music Power
- 2 x 25 watts RMS Stereo

### sound

- Incredible Surround™
- Bass & Treble Control

### disc player

- MP3-CD playback
- Plays CD, CD-R, CD-RW & MP3 discs
- CD repeat (track/disc)
- Play modes (repeat/program)

### tuner

- FM/MW Digital tuning with 40 presets
- Plug & play for easy installation of radio stations
- RDS station name (/22)

### loudspeaker boxes

- 2-way Bass Reflex Speaker System
- 3" full range woofers
- Detachable grilles

### connections

- Stereo headphones : 3.5mm stereo jack
- Aux : Cinch type socket
- Line out : Cinch type socket
- Antenna : FM coaxial, MW Loop

### general

- 2 Dim Display modes
- LCD Display
- Clock/Timer
- Wake-up with CD or Tuner
- Eco power standby mode (<1 watt)

### Unique

- 8mm thick transparent injection moulded acrylic casing
- Limited edition
- Pocket size remote control

### Personal

- Digital Sound Presets
- Individual Bass & Treble
- MP3-CD and CD-RW playback

### Incredible Surround™

An exciting, new, psycho-acoustic method of widening the stereo spatial image especially suited for applications with limited separation of left and right speakers.

### Bass & Treble Control

Bass & Treble control allows sound adjustment of high and low frequencies to personal preferences.

### MP3-CD Playback

Download MP3 songs from the Internet on a PC and record them on a CD. This special "MP3-CD" can now be played on this Audio CD Player. One MP3-CD can carry up to 12 hours of music. Our sets are designed to playback MP3-CDs recorded with a bit-rate (quality level) between 32 kbps and 320 kbps. The set will also handle variable bit-rate recordings

### Plays CD, CD-R, CD-RW and MP3 discs


The player offers 100% playback guarantee of CD, CD-Recordable, CD Rewritable and MP3 discs over the entire lifetime of the player. Even CD-RW audio recordings on computers can be used.




Digital Power unit included



Bass Reflex Speaker




Remote Control



Click fit connections

### remote control



### version matrix

	/21	/21M	/22	/30	/33
<b>AP/Middle East/Africa</b>		•			
<b>Australia/NZ</b>					
<b>Korea</b>					
<b>Latam/Mexico</b>		•			
<b>W Europe</b>				•	
<b>E Europe</b>					•
<b>tuner</b>					
FM87.5-108MHz		•	•	•	
MW522-1602kHz		•	•	•	
LW153-279kHz				•	
FM75 Ohm coaxial		•	•	•	
<b>mains supply</b>					
120/230V 50-60Hz		•	•		
230V/50Hz				•	
<b>general</b>					
made in sticker		•		•	

### physical info

EAN: 87 10895 73920 7 (/21)  
 EAN: 87 10895 73921 4 (/21M)  
 EAN: 87 10895 71926 1 (/22)

Product Dimensions:  
 112 mm W x 245 mm H x 235 mm D (center unit)  
 112 mm W x 245 mm H x 235 mm D (speakers)

Package Dimensions:  
 572 mm W x 362 mm H x 330 mm D

Product weight: 10.2 kg

Carton contains: CD Micro, Power Box, Remote Control, Cables, Operating instructions and Warranty Information

Printed in Singapore  
 Date Printed : Jul 2002  
 Specifications subject to change without notice.  
 © 2002 Kloninklijke Philips Electronics N.V.  
 All rights reserved.

Incredible Surround™ is a Trademark of Philips Consumer Electronics Company

<http://www.audio.philips.com>

Let's make things better.



PHILIPS