

Micro Hi-Fi System

MZ-3

Compact Hi-Fi System with Premium Performance and Design

- 2 x 15 watts RMS Stereo
- Ultra Design with premium finishings
- Incredible Surround
- Digital Sound Control (optimal, jazz, classic, rock)
- Dynamic Bass Boost
- Coaxial 2-way speaker system
- Detachable Speaker Grilles
- CD Player with motorized tray load
- CD-Rewritable Compatible
- Digital Recording Ready (digital cord line out)
- AM/FM Stereo Digital Tuning with 40 Presets
- Bedroom Clock with Wake-up Alarm & Sleep-timer
- 24-Button Remote Control
- 4-Color Packaging

Incredible
Surround



Let's make things better.



PHILIPS

Sound Enhancement

2 x 15 Watts RMS Stereo

15 watts continuous RMS power output per channel, at 8 Ohms, from 120Hz-15kHz, with no more than 10% Total Harmonic Distortion (THD).

Incredible Surround™

An exciting new, psycho-acoustic method of widening the stereo spatial image especially suited for applications with limited separation of left and right speakers.

Digital Sound Control

(Optimal, Jazz, Classic, Rock)
Digital sound control (or DSC) offers different sound settings tailored for specific musical styles.

Dynamic Bass Boost

Boosting bass response as much as 6 decibels (nearly 2 times more than normal) Dynamic Bass Boost yields full, rich tonal quality at all volume levels.

Coaxial 2-way speaker system

In the coaxial 2-way speaker system the tweeter is concentrically mounted in front of the main driver. This assures that all sound waves originate from the same point giving a very stable stereo image. The magnet material of the tweeter is made of a composite called neodymium. This compact neodymium material has a very strong magnetic field creating a high sound pressure level.

2-Way Dual Cone neodymium speaker

The 2-way speaker is a dual cone speaker, meaning that the tweeter is concentrically mounted within the main driver. This assures that all sound waves originate from the same point giving a very stable stereo image. The magnet material of the speaker is made of a composite called 'neodymium'. The neodymium magnet material is very strong allowing high power currents and strong speaker performance.

AM/FM Stereo Digital Tuner

State-of-the-art precision tuning system insures precise, accurate station selection every time, along with the greatest performance and reliability available.

Design

Contemporary Design

A combination of bright anodised aluminium and clear lacquered MDF on the loudspeakers give a fresh and light appearance blending in smoothly with a modern interior design.

FTD Display

This large display is easy to read at any distance with no distortion or distraction makes it easy to recognize different functions at a glance.

Ergonomic Control Layout

Convenient grouping of related functions along with positive tactile feedback from front-mounted controls optimize this model for comfort and convenience.

Cloth Speaker Grilles

Cloth covered perforated grilles protect delicate speaker

Convenience

Motorized Drawer loading

For convenient, safe loading of your CD.

CD-Rewritable Compatible

The player offers 100% playback guarantee of CD-Rewritable CD's over the entire lifetime of the player. Even CD-RW audio recordings on computers can be used.

24-Button Remote Control

40-Random Channel Presets

Random memory presets allow pre-programming of up to 40 AM and FM station frequencies into the tuner memory.

Auto Store

Automatically stores up to 40 preset FM or AM stations.

40-Track CD Random Program

Store up to 40 of your favorite CD track selections, from one or multiple discs, to be played back in the order in which they are programmed anytime you like.

AUX Input

For connection of audio accessory pieces such as a LD or DVD player, television, or external cassette deck.

Demo Mode

To activate: Press stop for longer than 5 seconds. To deactivate: Press standby.

Repeat

Repeat your favorite track.

Pause

Interrupts playback of a CD without returning to the beginning of the disc, so when play resumes, the music begins exactly where it stopped.

Shuffle Disc

Plays all selections on a particular disc in random order, ignoring the sequential order in which they were originally recorded.

Next/Previous Skip


This two button feature offers you the opportunity to skip back to the previous track or skip up to the next track instantly.

Clock/Timer and Sleep-timer

Set the alarm portion of a built-in digital clock to wake you to music from your favorite CD or an AM/FM radio station at any desired time of the day Sleep timer settings of 60, 45, 30 or 15 minutes.

Stereo Headphone Jack

Plug in a set of stereo headphones and enjoy your favorite CD, cassette, or radio station without disturbing other family members in the room. This convenient feature allows different people in your household to use different electronic entertainment media without interference.



UPC Code: 0 37849 89385 2

Product Dimensions:

6.5" W x 6.2" H x 9.9" D (electronics)

6.5" W x 6.2" H x 9.4" D (speakers)

Package Dimensions:

19.5" W x 9.6" H x 14.6" D

Product weight: 15.9 lbs.

Carton contains: Micro Hi-Fi System, Multi-Function Remote Control, Batteries, Operating instructions, Warranty information

Printed in Singapore

Date printed: Oct 1999

©1999 Royal Philips Electronics N.V.

All rights reserved.

A Division of Philips Electronics North America Corp.

Specifications subject to change without notice.