

Compact audio system

- **Contemporary design**

A striking mirror coated square lense dominates the design.

The lense is surrounded by a simple control layout and elegant use of materials to complete the feeling of sophistication.

- **Motorised CD tray**

For convenient and safe loading of your CD.

- **Digital recording ready**

To connect, with the digital or analogue out terminals, to a CD-Recordable player to compile your favourite songs into a recordable CD.

- **CD-Rewritable compatible**

- **RDS radio data system with News & Traffic Announcement (I22/I25)**

- **Clock/timer with sleep function**

- **Remote control with mute function**

- **2-way bass reflex speaker system**

- **Coaxially mounted neodymium tweeter**

- **Optional pair of blue speaker grilles included**



Standard product information

Amplifier

- 2 x 15W RMS
- 2 x 30W music power
- Incredible surround
- Dynamic bass boost
- Digital sound control (optimal, jazz, classic, pop)
- Rotary volume control
- Mute function
- Tuner, CD, CD-RW and Aux sources

Compact disc player

- CD-Rewritable compatible
- Motorised tray loader
- Digital servo technology
- Programmable memory for 40 tracks
- Programme review facility
- Play mode (repeat, shuffle, programme)
- Repeat track/disc/all

Tuner

- FM/MW/LW stereo digital tuner with 40 presets (LW /22/25)
- Autostore facility
- Up/down single step and search tuning
- RDS - station name, programme type, RDS text, clock set, news and traffic announcement (/22/25)

Loudspeaker boxes

- Bass reflex system
- 4 inch woofer
- 18mm neodymium tweeter
- Coaxially mounted tweeter
- Detachable speaker grilles

Connections

- Stereo headphones : 3.5 mm stereo jack
- Aux-in : cinch type sockets
- Digital-out : cinch type socket
- Line-out : cinch type sockets
- Loudspeakers : click-fit connectors
- Antenna : FM coaxial socket 75 Ohm
AM JST2pM

Interface

- FTD display
- Digital clock/timer
- Wake up with CD or tuner
- Sleptimer 60, 45, 30 and 15 min.
- Automatic standby
- 24 Key remote control
- Demo mode

General

- Weight of product : 7.3 kg
- Dimensions electronics : 164 mm W x 158 mm H x 254 mm D
- Dimensions speakers : 164 mm W x 158 mm H x 239 mm D
- Packaging dimensions : 494 mm W x 244 mm H x 370 mm D
- Weight including packaging : 8.5 kg

Product highlights

- **Incredible Surround**
Feature unique to Philips that creates the illusion of the speakers being much further apart than they actually are, resulting in an enhanced, room-filled stereo effect.
- **Dynamic bass boost**
Enhances bass tone frequencies to give deep, rich sounds.
- **Digital sound control**
Digital sound control (or DSC) offers different sound settings tailored for specific musical styles.
- **Bass reflex speaker system**
Acoustic system that enhances the upper bass tones to provide a warmer, punchier bass sound.
- **2-way speaker system**
With a 4" woofer and a 18mm coaxially mounted neodymium tweeter.
- **Coaxially mounted tweeters**
The coaxially mounted tweeters enhance the stability of the stereo effect.
- **Cloth speaker grilles**
Grilles covered with acoustically neutral cloth to protect the speakers.
- **Mute**
This feature allows you to switch off the volume instantly to allow for interruptions. The system will continue playing in silence until you are ready to resume listening.
- **Digital tuner with 40 presets**
Provides fast, accurate tuning to your favourite stations. You can store up to 40 stations in memory for fast, easy access.
- **News & Traffic Announcement (I22/I25)**
The tuner can be set in such a way that listening to a CD is interrupted by the news or traffic info broadcast of a RDS station.
- **Autostore of tuner presets**
Automatically stores up to 40 preset radio stations.
- **Compact disc digital audio player**
Compact Disc technology that combines superb digital sound quality with the convenience of random track access and CD functions like CD programme, Shuffle Play and Repeat.
- **Digital recording ready**
With the Digital-out and Analogue-out terminals, it enables users to connect a CD-Recordable player to compile all their favourite songs into a recordable CD.
- **CD-Rewritable compatible**
The super-smooth CD plays you normal, recordable and rewritable audio CD's
- **40-track programmable**
Stores up to 40 of your favourite CD tracks for playing back in your order of preference.
- **Sleptimer**
The set will automatically switch off the chosen function after a preset period of time with a choice of 60, 45, 30 15 or 10 minutes setting.
- **Stereo headphone socket**
Enables stereo headphones to be used for private listening pleasure. Automatically switches off speakers when used.
- **Automatic standby**
As a power-saving feature, the unit automatically switches to standby 15 minutes after a CD has reached the end and no control is operated.
- **Demo mode**
In standby, press the CD-stop button on the set for more than 5 seconds. Repeat this step to deactivate the demo mode.

2000-02-18
Printed in Hong Kong
Subject to modification without notice
© 2000 Royal Philips Electronics
All Rights Reserved.

<http://www.philips.com>