

Lifestyle

MZ-7

3 CD Changer Mini System

- 2 x 100 watts Music Power
- 2 x 50 watts RMS Stereo
- Incredible Surround™
- Loudness
- Treble and Bass Rotary Control
- Flat mode for CD direct music
- 7-band Spectrum Analyzer with 4 Display Modes
- 3-way Bass Reflex Speaker System with Detachable Grilles
- 6.5" G-cone Woofer
- CD-Rewritable compatible
- Full RDS suite including 'NEWS' & Traffic Announcement
- Dual Logic Tape Deck with Auto Reverse (R+1)
- Digital Recording Ready
- Subwoofer Ready
- Easy set for tuner and clock
- 2 timer modes (wake-up/sleep)



2x100
wattsMPO



Let's make things better.



PHILIPS

3 CD Changer Mini System

standard product information

amplifier

- 2 x 100 watts Music Power
- 2 x 50 watts RMS, $\pm 10\%$ THD, 6 Ohm, 1 kHz
- G-Sound Technology:
 - Super Class G Amplifier
 - Gyros switching
 - G-Bass port
 - G-cone
 - Ferro Fluid Tweeter
- Incredible Surround™
- Loudness
- Treble and Bass Rotary Control
- Flat mode for CD direct music

compact disc player

- motorized front loading 3 CD changer
- CD-Rewritable compatible
- digital servo technology
- bit-check D/A converter
- 40-track CD Random Program
- play modes (repeat/shuffle/program)
- repeat track/disc/all
- change 2 discs while playing 1

tuner

- RDS: station name, program type, RDS text, clock set
- RDS: 'NEWS' & Traffic Announcement
- FM/MW/LW Digital Tuner with 40 presets (LW /22)

tape deck

- Dual Logic Tape Deck
- Auto Reverse (R+1)
- high and normal speed dubbing
- CD synchro recording
- automatic recording level control
- automatic tape type selection
- electronic speed control and full auto stop

loudspeaker boxes

- 3-way Bass Reflex
- 6 1/2" G cone woofer
- 2 1/2" Ferro Fluid Tweeter
- 1" polydome Tweeter


connections

- stereo headphones: 3.5mm stereo jack
- CDR/aux: cinch type sockets
- subwoofer out: cinch type socket
- Digital Recording Ready:
 - digital out: cinch type socket
 - line out: cinch type socket

general

- 4 display modes incl. NITE mode
- multicolor FTD display
- 7-band Spectrum Analyzer
- clock/timer
- 2 timer modes (wake-up/sleep)
- wake-up with CD, tuner or tape

	/21M	/21	/22	/30	/34
Asia Pacific					
Australia/NZ					
Middle East/S Africa					
Latam					
Europe			•		
E Europe					•
Mexico					
tuner					
FM65.81-74MHz					(•)
FM87.5-108MHz			•	•	
MW522-1602kHz			•	•	
LW153-279kHz			•		
FM75 ohm clickfit			•	•	
mains supply					
120/230V 50-60Hz					
230V/50Hz			•	•	
general					
made in sticker					•



EAN : 8710 1016 1795 4 (/22)
8710 1016 1796 1 (/34)

Product Dimensions:
265mmW x 310mmH x 310mmD (electronics)
240mmW x 310mmH x 305mmD (speakers)
Package Dimensions:
777mmW x 410mmH x 654mmD
Product weight: 23.5 kg
Carton contains: CD Mini System, Multi-Function Remote Control, Batteries (2 x AA), Operating instructions, Warranty information, FM antenna, AM antenna

Printed in Singapore
Date printed : Dec 1998
Specifications subject to change without notice.
© 1998 Koninklijke Philips Electronics N.V.
All rights reserved.

<http://www.philips.com>