

USB PC Video Camera

Toucam XS



- **Access your family and friends via the Internet**
Use brilliant blazing video to communicate and give your message impact.
- **Capture video and still images**
Up to 30 frames per second streaming video can be captured. Still images up to 640x480.
- **Easy to install - simple to use**
Fully automated tools make your PC-camera a cool and easy to use peripheral.



Let's make things better.



PHILIPS

USB PC Video Camera

Toucam XS



Video made easy

With the Toucam range, Philips sets the pace for how PC video cameras should look and perform in the future. Each camera in the Toucam range has highly integrated components built into a stylish, compact housing that is easy to mount on laptops or desktop CDs. Everything about the Toucam XS is easy. From its versatile design and easy installation to the flawless operation, the Toucam XS has it all.

Included Applications for Microsoft Windows

Application	Name	By
Web cam + broadcast	Spotlife	Spotlife
Video conferencing	NetMeeting 3.01	Microsoft
Video mail Videolink	Mail 4.0	Smith-Micro
Image capture	Photo Explorer 6.0	Ulead
Image album	Photo Explorer 6.0	Ulead
Video capture	V-record	Philips
Game I	Vball	Reality Fusion
Game II	Karate	Reality Fusion
Screensaver game I	Bounce-It 2	Reality Fusion
Screensaver game II	Pop the Bubbles 2	Reality Fusion
Internet update tool	V-download	Philips
Configuration check	V-check	Philips
Application launcher	V-lounge	Philips
Camera settings	V-property	Philips
PDF reader	Acrobat Reader 4.05	Adobe

Packaging contents

- Toucam XS PC-camera
- Quick install guide
- Installation CD-ROM
- Desktop/laptop attachment base



Snapshot button

Technical specifications

Optical

- Sensor 1/4" CMOS
- Video Resolution 352 x 288 pixels (CIF)
- Snapshot resolution 640 x 480 pixels (VGA)
- Min illumination < 10 Lux
- Auto white balance 2500 – 7500 K
- Integrated lens 5.2mm f2.6 H40°
- Max. frame rate 30 fps @ 352 x 288
- Color depth 24 bits

Camera controls

- Full automatic control
- Video format
- Frame rate
- Brightness
- Hue
- Saturation
- Contrast
- Sharpness
- White balance
- Exposure

Mechanics

- H x W x D 69mm x 48mm x 48mm (2.72" x 1.89" x 1.89")
- Weight 90 g (3.17 oz.)
- Cable length 2 m (6.56 ft.)
- Built-in snapshot button
- Monitor and LCD mounting attachment base

Power

- In operation 450 mW

System requirements

Processor	Intel Pentium II or AMD K6-2
RAM	32 MB
Free hard disk space	50 MB
# colors display	64K
Operating system	Windows 98, 2000, or Me
1 free USB port	
CD-ROM or DVD-ROM drive	
Audio recording and playback capability	
Internet connection	

Packaging information

- H x W x D 285mm x 160mm x 88mm (11.22" x 6.3" x 3.47")
- Packaging weight 312 g (11 oz.)

www.philipsusa.com
www.pcstuff.philips.com

Printed in USA
Date printed: January 2001
Specifications subject to change without notice.
© 2000 Philips Consumer Electronics Co.
A Division of Philips Electronics North America Corp.

Let's make things better.



PHILIPS