

# PHILIPS

## PC Camera

PCVC840K



## Simply see you online

### Top-quality video and images

The ToUcam PRO II incorporates the latest digital imaging technology to give you top-quality images for video conferencing and video mail.

#### **Stay in touch by sharing your experiences**

- On-line video chatting over the Internet
- Comes with free v-mail software

#### **High picture & video quality**

- VGA (640x480) @ 60 fps video quality
- Take 1.3 megapixel (1280x960) resolution snapshots
- High-sensitivity sensor for low light environments

#### **Easy to use**

- XP Plug & Play
- Vloung control panel for quick access to applications
- Built-in digital microphone for quality sound

# Highlights

**Video chatting**

On-line video chatting (communication) over a distance

**V-mail software**

Get started with sending video clips to friends and family in v-mails made using the software supplied.

**VGA @ 60 fps video quality**

VGA (640x480) resolution at 30 frames per second video quality

**1.3 MP resolution snapshots**

An image taken at 1.3-megapixels resolution creates an image of 1280 by 960 pixels, a good size for web pages and e-mails.

**High-sensitivity sensor**

The high-sensitivity sensor enables you to record videoclips in low-light environments

**XP Plug & Play**

If you're a Windows XP end-user, you do not need to install product drivers before starting to use this PC peripheral / product.

**VLounge control panel**

VLounge control panel for quickly access your PC camera applications

**Built-in digital microphone**

The built-in digital microphone allows you to talk naturally and freely or to add sound to a video clip recording.

# Specifications

**Cameras**

Image sensor type: CCD

Sensitivity: 1 lx

