

Institutional Television

PL9119C

19" Philips Commercial Television

(screen size measured diagonally)

- **Smart Plug™ Two-Way Addressable Port**
- **Clone Programming Capability**
- **Front Control Lockout**
- **Local Preview - Channel Guide**
- **SmartMute™**
- **Programmable Channel Blanking**
- **Auto Power On**
- **Volume Limiter**
- **Marquee Channel™**
- **Audio/Video Muting**
- **SmartSound™**
- **ESP™ (Energy Savings Programmability)**
- **Spill-Resistant Cabinet**
- **Security Mountable**
- **Consumer Television Convertible**
- **External Speaker Connection**
- **Includes 20-Button Remote**
- **V-Chip Compliant**



20 PB Remote

Setting Industry Standards™

Let's make things better.



PHILIPS

The PL9119C is a full-featured commercial television designed and manufactured exclusively for applications utilizing interactive services and entertainment systems.

Technical Specifications:

- System: 525 lines per picture, 60 fields per second, interlaced for NTSC 3.58 systems
- Power Source: 90 - 150Vac, 50/60Hz
- Power Consumption: 56W (avg.)
- Picture Tube: 19" Diagonal, 90°
- Speaker Size: 2" x 4" oval
- Resolution: Rf - 370+ TV lines (per picture width - horizontal)
- Operating Temperature: 32°F - 104°F (0°C - 40°C)
- Weight: 41.9 lbs.
- Operating Humidity: 5% - 100%
- Dimensions (WxHxD): 20" x 18" x 19"
- Power Cord: 13', 2 Prong Polarized
- Closed-Captioning: Compatible with all FCC recognized modes
- Channel Capability: 181 channels
- Audio: 1 x 1.0 Watts, @ 16Ω, @ 5% THD, 50Hz - 12kHz frequency response

Input/Output Capabilities:

- Antenna Input: 75Ω VHF/UHF
- Smart Plug™ Two-way Addressable Interface Port: RJ11 Type Connector
- External Speaker: 1/8" mini-jack

Special Features:

Smart Plug™ Two-Way Addressable Port

Compatible with all major premium entertainment services, the Philips "Smart Plug" eliminates confusing set-top boxes and makes it easy for guests to use interactive guest services.

Clone Programming Capability

Provides the ability to copy all programming settings from one set into additional sets. This feature ensures uniformity between sets and significantly reduces installation time.

Front Control Lockout

Provides the ability to selectively or completely disable front control panel buttons.

Local Preview™

Automatically displays channel guide every time television is turned on. After choosing the channel to view, channel guide fades off-screen to be displayed again when called up using the remote.

Channel Guide

Provides guests with an onscreen directory listing channel number and network affiliation. Channel guide is accessed via the touch of a single button on the remote.

SmartMute™

Automatically displays Closed Caption service whenever the user activates the mute function.

Programmable Channel Blanking

Provides a means to force the picture to be blanked without affecting the audio. Perfect for audio-only services, such as FM radio.

Volume Limiter

Programmable minimum/maximum and turn-on volume range. Forces the monitor/ receiver to operate within a user defined volume range, preventing volume adjustments that are too high or too low.

Auto Power On

Forces the default power setting to the ON position, preventing sets from being turned off while in use. Additionally, this feature allows all sets to be controlled from a single circuit breaker and forces the set to turn back on automatically after a power interruption.

Marquee Channel™

Forces the television to a specified channel when turned on. Perfect for in-house advertising or information channels.

Audio/Video Muting

Automatically detects a loss of television signal and optionally mutes both audio and video. Prevents annoyance due to snowy picture and static.

SmartSound™

Automatic volume leveler. Automatically detects variations in the audio level and adjusts to acceptable levels, minimizing the excessive volume levels often associated with commercial advertising.

ESP™ (Energy Saving Programmability)

Energy Saving system that powers television off after a specified period of use. A simple countdown clock can be selectively set to operate from 0-99 hours with automatic clock reset at each power up.

Spill-Resistant Cabinet

Reduces the risk of damage to the television in the event liquid is spilled on the cabinet.

Security Mountable

Equipped with heavy-duty blocks on the bottom of the cabinet, designed for safe and secure mounting to security brackets.

Consumer Television Convertible

Easily converts to true consumer television for aftermarket sales.

20-Button Guest Remote

Provides guest access to power, volume, channel selection, mute, closed captioning, channel guide, and sleep timer.

Special Setup Remote Transmitter: RG4172BK (not included)

Used during initial setup of televisions, the setup remote allows limited access to critical TV functions such as power, channel up/down, volume, color, tint, brightness, sharpness, etc. Once setup is complete, the setup transmitter is retained in a secure location.

Smart Loader Clone Programming Device: CLON99BK (not included)

Used to clone program multiple sets, simply plug the Smart Loader into the addressable interface port and follow simple onscreen menus to download programming settings. Smart Loader is then used to upload the information into additional sets.



UL listed for commercial use

PHILIPS ITV WEBSITE: <http://www.philipspro.com>

Philips Institutional TV (ITV)
©1999 Philips Consumer Electronics Company
A Division of Philips Electronics North America Corporation
KID Design, GR99236, Philips Consumer Electronics Co.



Specifications subject to change without notice.

Let's make things better.



PHILIPS