

Compact plain paper telephone-fax-copier with cordless phone management

Plain Paper Fax
magic²primo
4 in 1

- Fax
- Telephone
- Copier
- Cordless Phone Management



Let's make things better.



PHILIPS

Main Features

Fax

Via the automatic document feeder, 10 pages can be sent at a time, instantly or delayed.

- Page header, voice request, automatic redial and polling send
- Printing method: ink film on standard plain paper
- Modem speed: 9600/7200/4800/2400 bps auto fall back
- ITU group 3 compatible
- Horizontal resolution: 8 pixels/mm
Vertical resolution standard: 3.85 lines/mm
Vertical resolution fine: 7.7 lines/mm

Copier

You can make copies of documents that are A4 or smaller.

- 16 grey scales with contrast control
- Fine-/photo quality mode

Telephone

The magic2primo includes a telephone with phone book, 10 ringer melodies and calling line identification (subject to network selection).

- Name dial: up to 50 entries
- Short dial (two touch): 10 entries
- Redial: last 5 numbers
- 3 level volume control

Cordless Phone Management

The Philips intelligent fax switch makes transferring calls between the fax machine and all types of cordless phones possible, while faxes can be received silently.

- Fax transmission is not interrupted by picking up another phone.

Vertical Paper Handling

Through a revolutionary design the original documents, as well as those received come out on top of the machine, making the magic2series machines, the smallest plain paper fax machines in the world.

General Information

Type number (GB)	PPF 441/05B
EAN code (GB)	87 10101 65801 8
Designed for (telephone circuit):	PSTN/PABX
Power Supply:	220 - 240 V AC, 50 - 60 Hz

Power consumption:

Stand by:	< 2 Watt stand by
Transmission:	< 20 W
Reception:	< 30 W
Copy:	< 30 W
Telephone conversation:	3 W

Display:

liquid crystal display,
5x7 dots.
European characters.
3 languages available

Installation:

Easy Install menu driven installation procedure and help pages

Weight

Unpacked	3 kg
Packed	5 kg

Dimensions (WxDxH):

Unpacked	356/240/163 mm
Packed	418/315/225 mm

Temperature range:

Operation	5°C - 40 °C
Storage packed	-25°C - 50°C
Storage unpacked	0°C - 45°C

Relative humidity:

Operation	15% - 85%
Storage packed	5% - 95%
Storage unpacked	15% - 85%

Standard Package includes:

- Fax machine incl. cables
- Starter package, with ink film for 50 pages and A4 paper
- Installation guide
- User manual

PHILIPS

AUTHENTIC
ACCESSORIES

- Ink film PFA 321 for Magic2 series, up to 260 pages

www.pcc.philips.com