



Philips
Fax with telephone and
copier

Magic 5 Eco Primo



PPF631E

Fax it, say it

All Magic 5 ECO faxes have high efficiency. Furthermore these feature-rich fax devices are perfectly adapted to your needs and the stylish design heightens the pleasure of communicating.

Easy to use copier

- Multi-copies up to 15 pages
- Prints in fine/photo resolution

High energy efficiency

- Guarantees low standby power consumption

Plain paper fax

- Provides predefined fax forms
- Stores up to 15 pages

Feature rich telephone

- Allows redial of last 10 numbers
- Features distinctive ringtones

PHILIPS

sense and simplicity

Specifications

Ink-film fax

- 10-page automatic doc feeder
- 9600 bps modem speed: auto fall back
- Cordless phone management
- Easy polling: receive and send
- Group broadcasting
- Horizontal resolution: 8 pixels/mm
- ITU Group 3 compatible: T.30 standard/T.30 new
- Memory: up to 15 pages
- Page header: automatic redial
- Paper tray up to 50 sheets
- Predefined fax forms
- Printing method: thermal transfer
- Sudoku printing with solutions: easy - medium - tough - devil
- Timer function: send later
- Vertical resolution fine: 7.7 lines/mm
- Sending report: with reduced copy first page
- Vertical resolution standard: 3.85 lines/mm

Telephone

- Caller identification (CLIP)*
- Chain dialling
- Distinctive ringtones**
- Name dial entries: 50
- On-hook dialling
- Outgoing call log print
- Redial of the last 10 numbers
- Ringer melodies: 10
- Short dial keys: 10

Copier

- Fine/photo resolution
- Grey scales: 16
- Zoom function (enlarge/reduce)
- Multi-copy: up to 15 pages

Accessories

- Philips PFA 351: With PLUG'N'PRINT Card/up to 140 pages A4
- Philips PFA 352: With PLUG'N'PRINT Card/up to 90 pages A4

Dimensions

- Packed (W x D x H): 313 x 197 x 129 mm
- Unpacked: 377 x 247 x 200 mm

Power use

- Copy: typ. 15 W
- Reception: typ. 15 W
- Stand by: typ. 1.4 W
- Telephone conversation: typ. 4 W
- Transmission: typ. 15 W

Weight

- Packed (including country kit): 2.3 kg
- Unpacked (without accessories): 3 kg

Features

- Printing method: thermal transfer
- Corded handset
- Monthly Fax volume: 1 to 15 pages

Highlights

Multi-copies up to 15 pages

Multi-copies up to 15 pages

Prints in fine/photo resolution

Prints in fine/photo resolution

Provides predefined fax forms

Provides predefined fax forms

Stores up to 15 pages

Stores up to 15 pages

Guarantees low standby power

Philips is 43% better on energy efficiency compared to the average of the competitors

10 numbers redial function

Allows redial of last 10 numbers

Distinctive ringtones

Features distinctive ringtones



Issue date 2013-01-10

Version: 2.0.1

12 NC: 8670 000 62694
EAN: 34 25160 26544 6

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com

* Depends on the availability of the service on the local operator's network

** Depends on the availability of caller identification